


LPT 60

60 WATTS

LPT 60 Series

Total Power	60 - 80 Watts
Input Voltages	85 - 264 VAC 120 - 370 VDC
# of Outputs	Triple



SPECIAL FEATURES

- Universal input
- High efficiency
- Remote sense on main output
- Built-in EMI filter
- Low output ripple
- Adjustable 5V output
- Overvoltage protection
- Overload protection
- Enclosure kit available (see page 36 or PowerFAX Doc. no 1025)

ENVIRONMENTAL

Operating temperature: 0° to 50°C ambient
derate each output at 2.5% per degree from
50° to 70°C

Electromagnetic susceptibility: designed to
meet IEC 801,-2, -3, -4, -5, -6, Level 3


Humidity: Operating; non-condensing
5% to 95%

Vibration: Three orthogonal axes, sweep at 1
oct/min, 5 min. dwell at four major resonances
0.75G peak 5 Hz to 500 Hz, operational

Storage temperature: -40° to 85°C

Temperature coefficient: $\pm .04\%$ per degree C

MTBF demonstrated: > 550,000 hours at full
load and 25°C ambient conditions



ELECTRICAL SPECIFICATIONS

Input

Input range 85 - 264 VAC
120 - 370 VDC

Frequency 47 - 440 Hz

Inrush current < 18 A peak @ 115 VAC
< 36 A peak @ 230 VAC
cold start @ 25°C

Input current 1.5 A max. (RMS) @ 115 VAC

Efficiency 70% typical at full load (60% for LPT61)

EMI filter FCC Class B conducted
CISPR 22 Class B conducted
EN55022 Class B conducted
VDE 0878 PT3 Class B conducted

Safety ground
leakage current < 0.5mA @ 50/60Hz, 264 VAC input

Output

Maximum power 60 W for convection (LPT61, 35W)
80 W with 30 CFM forced air (LPT61, 55W)

Adjustment range - 5, +10% minimum

Cross regulation $\pm 2\%$ on output 1; $\pm 5\%$ on outputs 2,3

Hold-up time 20 ms at 60 watt load and 115 VAC
nominal line

Overload protection Short circuit protection on all outputs.
Case overload protected @ 110% to 145
above peak rating

Overvoltage protection 5.7 to 6.7 VDC on main output

SAFETY


VDE	0805/EN60950 (IEC950)	11774-3336-1255 (LC #86665)
UL	UL1950	E132002
CSA	CSA 22.2-234 Level 3	LR53982C
NEMKO	EN 60950/EMKO-TUE (74-sec) 203	P95100123
BABT	EN60950/BS7002	PS / 605273
CB	Certificate and report	1518, 1519, 1520
CE	Mark	

ORDERING INFORMATION

Model Number	Output Voltage	Minimum Load	Maximum Load with Convection Cooling	Maximum Load with 30 CFM Forced Air	Peak Load ¹	Regulation ²	Ripple P/P (PARD) ³
LPT61	+3.3 V	0.7A	5 A	8.5 A	9.5 A	±2%	50mV
	+5 V	0 A	2.5 A	3.0 A	3.3 A	±2%	50mV
	+12 V	0 A	0.5 A	1.0 A	1 A	±5%	120mV
LPT62	+5 V	0.7 A	7 A	8 A	10 A	± 2%	50 mV
	+12 V	0.3 A	3 A	3.5 A	6 A	± 5%	120 mV
	-12 V	0 A	0.7 A	1 A	1.5 A	± 5%	120 mV
LPT63	+5 V	0.7 A	7 A	8 A	10 A	± 2%	50 mV
	+15 V	0.3 A	2.8 A	3.3 A	4 A	± 5%	150 mV
	-15 V	0 A	0.7 A	1 A	1.5 A	± 5%	150 mV
LPT64	+5 V	0.7 A	7 A	8 A	10 A	± 2%	50 mV
	+12 V	0.3 A	3 A	3.5 A	6 A	± 5%	120 mV
	-5 V	0 A	0.7 A	1 A	1.5 A	± 5%	50 mV
LPT65	+5 V	0.7 A	7 A	8 A	10 A	± 2%	50 mV
	+24 V	0.1 A	1.5 A	2.0 A	3 A	± 7%	240 mV
	+12 V	0 A	0.7 A	1 A	1.5 A	± 5%	120 mV
LPT66	+5 V	0.7 A	7 A	8 A	10 A	± 2%	50 mV
	+24 V	0.1 A	1.5 A	2.0 A	3 A	± 7%	240 mV
	-12 V	0 A	0.7 A	1 A	1.5 A	± 5%	120 mV
LPT67	+5 V	0.7 A	7 A	8 A	10 A	± 2%	50 mV
	+24 V	0.1 A	1.5 A	2.0 A	3 A	± 7%	240 mV
	-5 V	0 A	0.7 A	1 A	1.5 A	± 5%	50 mV

1. Peak current lasting < 30 seconds with a maximum 10% duty cycle.
2. At 25°C including initial tolerance, line voltage, load currents and output voltages adjusted to factory settings.
3. Peak-to-peak with 20 MHz bandwidth and 10 µF in parallel with a 0.1 µF capacitor at rated line voltage and load ranges.
4. **Minimum Loads are required.**

DRAWINGS



MATING CONNECTORS

AC Input: Molex 09-50-8031 (USA)
09-91-0300 (UK)
PINS: 08-58-0111

DC Outputs: Molex 09-50-8061 (USA)
09-91-0600 (UK)
PINS: 08-58-0111

Remote Sense: Molex 22-01-2025

NOTES

1. Specifications subject to change without notice.
2. All dimensions are in inches and (mm), tolerance is ±.02".
3. Mounting holes M1 and M2 should be grounded for EMI purposes.
4. Mounting hole M1 is safety ground connection.
5. Specifications are for convection rating unless otherwise stated.
6. Warranty: 1 year
7. Weight: 0.75 lb./0.34 kg

PIN ASSIGNMENTS

Connector	LPT61	LPT62	LPT63	LPT64	LPT65	LPT66	LPT67
SK1-1	Neutral	Neutral	Neutral	Neutral	Neutral	Neutral	Neutral
SK1-3	Line	Line	Line	Line	Line	Line	Line
SK2-1	5V	+12 V	+15 V	+12 V	+24V	+24V	+24V
SK2-2	3.3V	+5 V	+5 V	+5 V	+5V	+5V	+5V
SK2-3	3.3V	+5 V	+5 V	+5 V	+5V	+5V	+5V
SK2-4	Common	Common	Common	Common	Common	Common	Common
SK2-5	Common	Common	Common	Common	Common	Common	Common
SK2-6	+12V	-12 V	-15 V	-5 V	+12V	-12V	-5V
SK201-1	+Sense	+Sense	+Sense	+Sense	+Sense	+Sense	+Sense
SK201-2	-Sense	-Sense	-Sense	-Sense	-Sense	-Sense	-Sense