

REVISIONS			
REV	ECN, ERN NO.	DATE	APPRD.
D	PRODUCT DRAWING (EAR 14157)	APR25/13	K.L.

ORDERING CODE: F C E 1 7 - B 2 5 A D - 4 0 0 G

SERIES
FCE17=FILTERED D-SUB, RoHS

SIZE/NUMBER OF CONTACTS
E09, A15, B25, OR C37

CONNECTOR STYLE
AD=PIN/SOCKET ADAPTER

MOUNTING
2=.120 [3.05] DIA. THROUGH HOLE
WITH #4-40 MOUNTING POST
4=#4-40 UNC THREAD
6=M3 x 0.5 THREAD
K=.120 [3.05] DIA. THROUGH HOLE
WITH M3 x 0.5 MOUNTING POST

CONTACT FINISH/GOLD THICKNESS
NO DIGIT=STANDARD 15 MICROINCHES
[0.38 MICRONS] GOLD ON
MATING AREA

G=50 MICROINCHES [1.27 MICRONS]
GOLD ON MATING AREA

MODIFIER
0=STANDARD





FILTER CAPACITANCE
D=50 pF 5=1000 pF
B=100 pF 7=1200 pF
O=180 pF 6=1300 pF
T=220 pF J=1500 pF
F=330 pF E=2200 pF
L=380 pF 9=5600 pF
1=470 pF 8=47000 pF
2=680 pF N=NO FILTERS
4=820 pF

REFER TO AMPHENOL CATALOGUE
FOR FILTER PERFORMANCE
CHARACTERISTICS


NOTES:

- MATERIALS: — ALL MATERIALS ARE RoHS COMPLIANT
— SHELLS: TIN PLATED STEEL
— CONTACTS: PHOSPHOR BRONZE
PLATED WITH GOLD OVER 50µ" [1.27 MICRONS]
NICKEL ON MATING AREA. SEE ORDERING CODE.
— INSULATOR: ENGINEERING THERMOPLASTIC, GLASS
REINFORCED, FLAMMABILITY RATING UL94V-0, BLACK.
— OUTSIDE SHELLS: ZINC DIECAST, NICKEL PLATED
— MOUNTING HARDWARE: STEEL OR COPPER ALLOY,
TIN OR NICKEL PLATED
- CONTACT RESISTANCE: 30 MILLIOHMS MAXIMUM
- INSULATION RESISTANCE: 3000 MEGOHMS MINIMUM
- CURRENT RATING: 5 AMPS MAXIMUM
- OPERATING TEMPERATURE: -40°C TO 85°C.
- TOLERANCE, UNLESS INDICATED OTHERWISE, ±.005 [0.13].

SIZE	A±.015 [0.38]	B±.005 [0.13]	C±.005 [0.13]	D±.005 [0.13]
E09	1.213 [30.81]	.643 [16.33]	.666 [16.92]	.984 [24.99]
A15	1.541 [39.14]	.971 [24.66]	.994 [25.25]	1.312 [33.32]
B25	2.088 [53.04]	1.511 [38.38]	1.534 [38.96]	1.852 [47.04]
C37	2.729 [69.32]	2.159 [54.84]	2.182 [55.42]	2.500 [63.50]



CAPACITANCE SCHEMATIC
FOR EACH POSITION



DRAWN S.BUENAVIDES	DATE DEC08/05
DESIGNED	
CHECKED K.LAMBIE	DATE DEC08/05
I. E. APPRD.	
Q. A. APPRD.	
DWG. APPRD.	
ENG. REL. NO.	
REF. EAR 12888	
DIMENSIONS ARE IN INCHES [mm]	CODE ID. NO. 03554

Amphenol Canada Corp.

FCE17 SERIES FILTERED D-SUB
CONNECTOR, MALE/FEMALE
ADAPTER, RoHS COMPLIANT

DWG	DRAWING NO.	REV.
C	P-FCE17-XXXAD-XX0X	D
SCALE 2/1	WT. -----	SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[FCE17-A15AD-290](#) [FCE17-C37AD-210](#) [FCE17-C37AD-290](#) [FCE17-E09AD-240](#) [FCE17-E09AD-290](#) [FCE17-B25AD-390](#) [FCE17-A15AD-210](#) [FCE17-E09AD-210](#) [FCE17-B25AD-240](#) [FCE17-B25AD-410](#) [FCE17-E09AD-250](#) [FCE17-E09AD-410](#) [FCE17-B25AD-210](#) [FCE17-A15AD-250](#) [FCE17-B25AD-250](#) [FCE17E09AD2D0](#)
[FCE17C37AD2E0](#) [FCE17E09AD400](#) [FCE17C37AD410](#) [FCE17E09AD4D0](#) [FCE17A15AD2D0](#) [FCE17B25AD490](#)
[FCE17C37AD280](#) [FCE17A15AD450](#) [FCE17B25AD480](#) [FCE17E09AD4E0](#) [FCE17A15AD480](#) [FCE17C37AD250](#)
[FCE17A15AD2E0](#) [FCE17B25AD440](#) [FCE17A15AD200](#) [FCE17B25AD290](#) [FCE17E09AD200](#) [FCE17E09AD450](#)
[FCE17B25AD200](#) [FCE17A15AD410](#) [FCE17B25AD4D0](#) [FCE17C37AD200](#) [FCE17C37AD480](#) [FCE17E09AD2E0](#)
[FCE17A15AD4D0](#) [FCE17B25AD4E0](#) [FCE17A15AD240](#) [FCE17A15AD4E0](#) [FCE17B25AD280](#) [FCE17C37AD450](#)
[FCE17C37AD440](#) [FCE17C37AD2D0](#) [FCE17B25AD400](#) [FCE17B25AD450](#) [FCE17C37AD4E0](#) [FCE17E09AD440](#)
[FCE17E09AD490](#) [FCE17C37SM250](#) [FCE17E09AD280](#) [FCE17C37AD400](#) [FCE17B25AD2D0](#) [FCE17B25AD2E0](#)
[FCE17A15AD490](#) [FCE17C37AD4D0](#) [FCE17A15AD400](#) [FCE17A15AD280](#) [FCE17A15AD440](#) [FCE17C37AD490](#)
[FCE17C37AD240](#) [FCE17E09AD480](#)