

Product SKU: C1364.41.90

Product Description: Speaker Wire, Superflex®[®], No. of Conductors: 2, Gauge Size (AWG): 12, Conductor/Strands: 7x37/36, Jacket: Premium Grade Clear Superflex®[®] PVC, Temperature Range: -20°C to +60°C - Clear - 1000 Ft. Reel

Product Category: Electronics - Special Applications - Audio, Video, and Entertainment Cable - Superflex®[®] Speaker Wire - Parallel Construction



Product Construction:

- | | |
|--------------------|--|
| Conductor: | <ul style="list-style-type: none">• 12 AWG fully-annealed, stranded bare copper conductor per ASTM B-3 |
| Insulation/Jacket: | <ul style="list-style-type: none">• Premium grade clear Superflex®[®] PVC• Temperature range: -20°C to +60°C |

Product Specification:

- | | |
|------------------------------------|---|
| No. of Conductors: | <ul style="list-style-type: none">• 2 |
| Conductor Size (AWG): | <ul style="list-style-type: none">• 12 |
| Conductor/Strands: | <ul style="list-style-type: none">• 7x37/36 |
| Jacket Color: | <ul style="list-style-type: none">• Clear |
| Nominal Insulation Thickness (in): | <ul style="list-style-type: none">• 0.060 |
| Nominal Insulation Thickness (mm): | <ul style="list-style-type: none">• 1.52 |
| Nominal Outside Diameter (in): | <ul style="list-style-type: none">• 0.230 x 0.470 |
| Nominal Outside Diameter (mm): | <ul style="list-style-type: none">• 5.84 x 11.94 |
| Standard Packaging: | <ul style="list-style-type: none">• 1000' Non-returnable Wood Reels |
| Standard Package Quantity: | <ul style="list-style-type: none">• 1 |

UPC #:	079407762606
Put-up:	1000
SCC-14:	50079407762600
Cube:	960
Weight Per Unit of Measure:	.079
ColorOption:	Clear

Product Information:

Applications:	- Hi-fi and stereo speaker wire - Juke boxes - Lamps - Radios - Suggested voltage rating: 120 Volts - Not for in-wall use
Compliances:	UL Misc. (UL: 120V)
Packaging:	1000' (305 m) Spools 500' (152 m) Spools - Other put-ups available- consult Customer Service

Technical Specifications

[Unit Conversion Factors](#)

[Cable Design Equations - Balanced Pair](#)

[Insulation and Jacket Properties](#)

[Temperature Conversion Chart](#)

[Decimal and Unit Conversion Factors](#)

[Cable Design Equations - Braid Shield](#)

[AWG Conductor Chart](#)

[Conduit Capacity Chart](#)

[Cable Design Equations - Coaxial Cable](#)

[Engineering Prefixes](#)

[Coax Connector Cross Reference](#)

[Glossary](#)

**CAROL
BRAND**