




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		H	REVISED PER ECR-12-013219	08JAN13	KH	KR

- 1 FASTON TERMINALS, BASE
P/N 1742110, ARE USED IN THIS PRODUCT.
- 2


TIN PLATE PER MIL-T-10727
0.001016 [.000040] MIN.
- 3 MATING TAB THK TO BE 0.51±0.025 [.020±.001]
- 4 WIRE SIZE IS [#18-#16 OR TWO #18'S] AWG.
- 5 INSULATION RANGE IS 2.67-5.33 OR TWO AT
2.67 MAX, [.105-.210 OR TWO AT .105 MAX].



SECTION A-A
SCALE 8:1



SECTION B-B
SCALE 8:1



6/6 NYLON, VO - NAT(WHITE)	BRASS - TIN PL 2	521586-2
6/6 NYLON, VO - NAT(WHITE)	BRASS - PLAIN	521586-1
HOUSING MATERIAL & COLOR	TERMINAL MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 17DEC02	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK N DEIBERT 17DEC02				
		APVD N DEIBERT 17DEC02	NAME ASSEMBLY, RECEPTACLE, ULTRA-POD, 4.8 [.187] SERIES			
		PRODUCT SPEC 108-1285				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-2124	SIZE A2			
MATERIAL SEE TABLE		WEIGHT -	CAGE CODE 00779			
FINISH SEE TABLE		DRAWING NO C=521586				RESTRICTED TO -
		CUSTOMER DRAWING				SCALE 5:1
		SHEET 1 OF 1				REV H