

Trade name: edding 8850 Carpenter Pen

Version: 2.1.0 / GB

Status: 07.08.2007

1.) Identification of the substance/preparation and of the company/undertaking

Identification of the substance or preparation

Trade name

edding 8850 Carpenter Pen

Use of the substance/preparation

Refilling ink

Company/undertaking identification

Address

edding Aktiengesellschaft
Bookkoppel 7
D-22926 Ahrensburg

Telephone no. +49 (0) 41 02 / 80 8-0

Information provided by / telephone

+49 (0)4102 - 808-0

Emergency telephone

+49 (0)30 192 40 (Toxic Substance Emergency Call Centre Berlin)

Advice on Safety Data Sheet

sdb_info@umco.de

2.) Hazards identification

Classification

R10	Flammable.
Xi; R36	Irritating to eyes.
R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Hazard symbols

Xi	Irritant
----	----------

R phrases

10	Flammable.
36	Irritating to eyes.
52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

3.) Composition / information on ingredients

Chemical characterization

Mixture (preparation)

Hazardous ingredients

ETHANOL

EC no.	200-578-6	Index no.	603-002-00-5	CAS no.	64-17-5
Concentration	> 30	<	50	%-b.w.	
Classification	F; R11				
Hazard symbols	F	R phrases	11		

2-(2-ETHOXYETHOXY)ETHANOL

EC no.	203-919-7	Index no.	-	CAS no.	111-90-0
Concentration	> 10	<	30	%-b.w.	
Classification	Xi; R36				
Hazard symbols	Xi	R phrases	36		

hydrogen bis[1-[(2-hydroxy-5-nitrophenyl)azo]-2-naphtholato(2

Trade name: edding 8850 Carpenter Pen

Version: 2.1.0 / GB

Status: 07.08.2007

]]chromate(1-)

EC no.	256-606-2	Index no.	-	CAS no.	50497-83-1
Concentration	> 10	< 20	%-b.w.		
Classification	N; R51/53				
Hazard symbols	N	R phrases	51/53		

4.) First aid measures

General information

In case of persisting adverse effects consult a physician. Remove contaminated clothing and shoes immediately, and launder thoroughly before reusing.

After inhalation

Remove affected person from the immediate area. Ensure supply of fresh air.

After skin contact

Wash off immediately with soap and water. Do NOT use solvents or thinners !

After eye contact

Separate eyelids, wash the eyes thoroughly with water (15 min.).

After ingestion

Rinse mouth thoroughly with water. Summon a doctor immediately. Never give anything by mouth to an unconscious person.

5.) Fire-fighting measures

Suitable extinguishing media

Alcohol-resistant foam; extinguishing powder; Carbon dioxide; Water spray jet

Extinguishing media that must not be used for safety reasons

Full water jet

Special exposure hazards arising from the substance or preparation itself, combustion products, resulting gases

In the event of fire, the following can be released:

Carbon dioxide (CO₂)

Carbon monoxide (CO)

Special protective equipment for fire-fighters

Use self-contained breathing apparatus. Wear protective clothing.

Other information

Cool endangered containers with water spray jet.

6.) Accidental release measures

Personal precautions

Refer to protective measures listed in sections 7 and 8. Avoid contact with skin, eyes and clothing. Ensure adequate ventilation. Keep away sources of ignition.

Environmental precautions

Do not discharge into the drains/surface waters/groundwater.

Methods for cleaning up/taking up

Take up with absorbent material (e.g., sand, kieselguhr, universal binder). When picked up, treat material as prescribed under heading "Disposal considerations".

7.) Handling and storage

Handling

Advice on safe handling

Provide good ventilation of working area (local exhaust ventilation if necessary). If workplace exposure

Trade name: edding 8850 Carpenter Pen

Version: 2.1.0 / GB

Status: 07.08.2007

limits are exceeded, respiratory protection approved for this particular job must be worn. Product inherent handling risks must be minimised taking the appropriate measures for protection and preventive actions. The working process should be designed to rule out the release of hazardous substances or skin contact as far it is possible by the by the state of the art

Advice on protection against fire and explosion

Vapours can form an explosive mixture with air. Take precautionary measures against static charges. Keep away from sources of heat and ignition.

Storage**Requirements for storage rooms and vessels**

Containers which are opened must be carefully resealed and kept upright to prevent leakage. Always keep in containers of same material as the original one.

Advice on storage assembly

Do not store together with:
Oxidizing agents

Further information on storage conditions

Keep container tightly closed and dry in a cool, well-ventilated place. Protect from heat and direct sunlight.

8.) Exposure controls / personal protection**Exposure limit values****ETHANOL**

CAS no.	64-17-5
EC no.	200-578-6

Occupational Exposure Standards (OESs) / EH40

Ethanol				
TWA	1920	mg/m ³	1000	ml/m ³

Personal protective equipment**Respiratory protection**

If workplace exposure limits are exceeded, a respiration protection approved for this particular job must be worn. In case of aerosol and mist formation, take appropriate measures for breathing protection in the event workplace threshold values are not specified.

Hand protection

Sufficient protection is given wearing suitable protective gloves checked according to i.e. EN 374, in the event of risk of skin contact with the product. Before use, the protective glove should be tested in any case for its specific work-station suitability (i.e. mechanical resistance, product compatibility and antistatic properties). Adhere to the manufacturer's instructions and information relating to the use, storage, care and replacement of protective gloves. Protective gloves shall be replaced immediately when physically damaged or worn. Design operations thus to avoid permanent use of protective gloves.

Eye protection

Safety glasses with side protection shield (EN 166)

Skin protection

Clothing as usual in the chemical industry.

General protective and hygiene measures

Do not eat, drink or smoke during work time. Keep away from foodstuffs and beverages. Avoid contact with eyes and skin. Remove soiled or soaked clothing immediately. Do not inhale vapours. Clean skin thoroughly after work; apply skin cream.

Trade name: edding 8850 Carpenter Pen

Version: 2.1.0 / GB

Status: 07.08.2007

9.) Physical and chemical properties**General information**

Form	liquid
Colour	black
Odour	alkohol-like

Important health, safety and environmental information**Changes in physical state**

Type	Boiling point		
Value		82	°C

Flash point

Value	40	°C
-------	----	----

Vapour pressure

Value	appr.	77	mm Hg
-------	-------	----	-------

Density

Value	0,95	g/cm ³
-------	------	-------------------

Solubility in water

Remarks	insoluble
---------	-----------

10.) Stability and reactivity**Materials to avoid**

Oxidizing agents

Hazardous decomposition products

No hazardous decomposition products known.

11.) Toxicological information**Experience in practice**

Inhalation of solvent vapours in higher concentration may lead to nausea, headache, drowsiness and dizziness.

Repeated and prolonged skin contact may cause removal of natural fat from the skin and irritation of the skin.

Other information (chapter 11.)

Product specific toxicological data are not known.

12.) Ecological information**Other adverse effects**

Ecological data are not available.

Do not discharge product unmonitored into the environment.

13.) Disposal considerations**Product**

Allocation of a waste code number, according to the European Waste Catalogue, should be carried out in agreement with the regional waste disposal company.

Packaging

Residuals must be removed from packaging and when emptied completely disposed of in accordance with the regulations for waste removal. Incompletely emptied packaging must be disposed of in the form of disposal specified by the regional disposer.

Trade name: edding 8850 Carpenter Pen

Version: 2.1.0 / GB

Status: 07.08.2007

14.) Transport information**Land transport ADR/RID**

Class	3	Classification code	F1
Packaging group	III		
Hazard id. no.	30		
Label	3		
UN number	1263		
Technical name	Paint related material		
Special Provision 640	E		

Marine transport IMDG

Class	3
Packaging group	III
UN number	1263
Proper shipping name	Paint related material
EmS	F-E, S-E
MARPOL	--
Label	3

Air transport ICAO/IATA

Class	3
Packaging group	III
UN number	1263
Proper shipping name	Paint related material
Label	3

15.) Regulatory information**Labelling in accordance with EC directives**

The product is classified and labelled in accordance with EC Directive 1999/45/EC.

Hazard symbols

Xi	Irritant
----	----------

R phrases

10	Flammable.
36	Irritating to eyes.
52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

S phrases

24/25	Avoid contact with skin and eyes.
61	Avoid release to the environment. Refer to special instructions / Safety data sheets.

Council Directive 96/82/EC on the control of major-accident hazards involving dangerous substances

Remarks	Annex I, part 2, category 6
---------	-----------------------------

16.) Other information**Sources of key data used to compile the data sheet:**

EC Directive 67/548/EC resp. 99/45/EC as amended in each case.
 Regulation (EC) No 1907/2006 (REACH) as amended in each case.
 EC Directives 2000/39/EC, 2006/15/EC as amended in each case.
 National Threshold Limit Values of the corresponding countries as amended in each case.
 Transport regulations according to ADR, RID, IMDG, IATA as amended in each case.
 The data sources used to determine physical, toxic and ecotoxic data, are indicated directly in the corresponding chapter.

Trade name: edding 8850 Carpenter Pen

Version: 2.1.0 / GB

Status: 07.08.2007

Relevant R-phrases (chapter 3):

- | | |
|-------|---|
| 11 | Highly flammable. |
| 36 | Irritating to eyes. |
| 51/53 | Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. |

Department issuing safety data sheet

UMCO Umwelt Consult GmbH

Georg-Wilhelm-Str. 183 b, D-21107 Hamburg

Tel.: +49 40 / 41 92 13 00 Fax: +49 40 / 41 92 13 57 e-mail: umco@umco.de

This information is based on our present state of knowledge. However, it should not constitute a guarantee for any specific product properties and shall not establish a legally valid relationship.

Alterations/supplements:

Alterations to the previous edition are marked in the left-hand margin.