





**NOTES:****ELECTRICAL:**

1. VOLTAGE RATING : 125 VAC RMS MIN.
2. CURRENT RATING : 1.5 AMP MIN.
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi=0.46\text{mm}$
3. PLATING : GOLD PLATING OVER NICKEL.
4. OPERATING LIFE : 750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER : 1 LB MIN.
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO $+85^{\circ}\text{C}$.
2. OPERATION: -40°C TO $+85^{\circ}\text{C}$.
3. WAVE SOLDERING TEMPERATURE: 230°C TO 250°C (3-5SECOND).

MATES WITH MODULAR PLUG CONFORMING TO

FCC PART 68, SUBPART F.

CUL FILE NO. E163191

PART NUMBER: E526X-E000XX-L

2- 2 CONTACTS
4- 4 CONTACTS
6- 6 CONTACTS

1- 3u" 2- 6u" 3-15u"
4-30u" 5-50u" 6-Pd20u"
3-W/ PANEL STOP SPLIT FOOT
4-W/O PANEL STOP SPLIT FOOT

DETACHED LISTS	MM (INCH)		DFTO SAMMY	DATE 05/27/05	FULL RISE ELECTRONIC CO., LTD		
	TOLERANCES EXCEPT AS NOTED		CHKD ANKUE	DATE 2005/5/28			
			MFO	DATE	TITLE		
			APPV LUSHENG	DATE 2005/5/28			
			MATERIAL :		TOP ENTRY PCB JACK		
	ANGLES ±		QT'Y :		DRAWING NO. GE523027-LC /PART NO. SEE NOTE		
		FINISH :		SIZE A3			
THIRD ANGLE PROJECTION		SCALE : 3:1					REV 0
				DO NOT SCALE DRAWING			
							SHEET OF