


Types MCH and MCHN Multilayer High RF Power Capacitors

2500 & 4000 Volt RF Capacitors for Medical Imaging Coils, Plasma Generators, VHF/UHF Power Amplifiers and Antenna Tuning with Nonmagnetic Option



The flexible aluminum silicate dielectric eliminates cracking and permits soldering to 260 °C. These high voltage, RF capacitors need no voltage derating at temperatures up to 125 °C and voltages to 4000 Vdc. Exceptionally low ESR and superior thermal qualities set the MCH/MCHN chip capacitors apart from ordinary RF capacitors.

Highlights

- No thermal cracking
- FR4 compatible and wave solderable
- Extremely high Q above 50 MHz
- Nonmagnetic option available
- Ultra stable: no change with (t), (V) and (f)
- Excellent for tuning and impedance matching
- High flashover level
- Withstands 2 mm bend test
- Better than porcelain

Specifications

Capacitance and Voltage Ratings:

10 – 220 pF at 4kVdc and 270 – 1000 pF at 2500 Vdc (other ratings available)

±5% standard (±2% available)

–55 °C to +125 °C (with no voltage derating)

3838 (9.7 x 9.7 mm)

Capacitance Tolerance:

Temperature Range:

Case Size:

Temperature Characteristics:

Applications


- MRI Coils
- RF Ablation Systems
- Transmitters
- RF Generators
- Antenna Tuning
- Lasers
- RF Power Amplifiers
- MRI Generators

RoHS Compliant

Engineering Design Kits

MCH2500VKIT8, MCH4000VKIT10


Nonmagnetic MCHN2500VKIT9, MCHN4000VKIT11



2500 V kits 5 each of 8 values 270 to 1000 pF


4000 V kits 5 each of 10 values 10 – 220 pF

High Q, Low ESR Multilayer Construction for RF Power Applications




Types MCH and MCHN Multilayer High RF Power Capacitors

Outline Drawing



Soldering Pattern



Part Numbering System

| MCH Type | 38 Case Code | F Temperature Coefficient | K Voltage | 271 Capacitance | J Tolerance | -Y Package |
|--------------------|--------------------|---------------------------------|--------------|--------------------|------------------|-------------------------------|
| MCH = Standard | 38 = .380x.380 | Coef | K = 2500 Vdc | 100 = 10 pF | J = $\pm 5\%$ | Blank = Bulk (100 per bag) |
| MCHN = Nonmagnetic | | F=0 to +50 ppm/ $^{\circ}$ C | M=4000 Vdc | 271 = 270 pF | G = $\pm 2\%$ | -Y = Tray pack (100 per tray) |
| | | | | 102 = 1000 pF | D = ± 0.5 pF | |

Ratings (additional ratings available)

RoHS Compliant


| Cap (pF) | Catalog Part Number* | Voltage (Vdc) | Length Inches (mm) | Width Inches (mm) | T max Inches (mm) |
|-------------|-------------------------|------------------|--|--|----------------------|
| 10 | MCH38FM100D-Y | | | | 0.080 (2.03 mm) |
| 12 | MCH38FM120J-Y | | | | |
| 15 | MCH38FM150J-Y | | | | |
| 18 | MCH38FM180J-Y | | | | |
| 22 | MCH38FM220J-Y | | | | |
| 27 | MCH38FM270J-Y | | | | |
| 33 | MCH38FM330J-Y | | | | |
| 39 | MCH38FM390J-Y | | | | |
| 47 | MCH38FM470J-Y | 4000 Vdc | | | 0.120 (3.05 mm) |
| 56 | MCH38FM560J-Y | | | | |
| 68 | MCH38FM680J-Y | | 0.380 | 0.380 | |
| 82 | MCH38FM820J-Y | | +0.025 / -0 (9.65 mm +0.64 / -0) | +0.015 / -0 (9.65 mm +0.38 / -0) | 0.160 (4.06 mm) |
| 100 | MCH38FM101J-Y | | | | |
| 120 | MCH38FM121J-Y | | | | |
| 150 | MCH38FM151J-Y | | | | |
| 180 | MCH38FM181J-Y | | | | |
| 220 | MCH38FM221J-Y | | | | 0.240 (6.10 mm) |
| 270 | MCH38FK271J-Y | | | | 0.160 (4.06 mm) |
| 330 | MCH38FK331J-Y | | | | |
| 390 | MCH38FK391J-Y | | | | |
| 470 | MCH38FK471J-Y | 2500 Vdc | | | 0.240 (6.10 mm) |
| 560 | MCH38FK561J-Y | | | | |
| 680 | MCH38FK681J-Y | | | | |
| 820 | MCH38FK821J-Y | | | | |
| 1000 | MCH38FK102J-Y | | | | 0.270 (6.86 mm) |

*For nonmagnetic version change P/N prefix to MCHN


Types MCH and MCHN Multilayer High RF Power Capacitors

Typical Performance Data

ESR vs. Frequency for 470 pF




Current Rating (IRMS) for 470 pF at 60 °C Rise




Types MCH and MCHN Multilayer High RF Power Capacitors

Typical Performance Data

Q vs. Frequency 470 pF @ 25 °C




Impedance vs. Frequency for 470 pF @ 25 °C



Types MCH and MCHN Multilayer High RF Power Capacitors

Typical Performance Data

MCH vs. Porcelain (3838) Breakdown Voltage (BDV)



Environmental Specifications

Humidity (No Load): $+40^{\circ}\text{C} \pm 2^{\circ}\text{C}$ @ 90% to 95% RH, 500 hrs. Measure after 24 hrs, cap is $\pm 3\%$ of initial, DF $\leq 150\%$ of original, IR $3 \times 10^4 \text{ M}\Omega$, no visual damage

Storage Method: Store at 0 to $+40^{\circ}\text{C}$ at $\leq 60\%$ RH, use within 6 months of receipt, if 6 months is exceeded, check solderability

Electrical Specifications

Dielectric Strength: **2500 Vdc:** 1.5 x Rated Voltage for 5 seconds
4000 Vdc: 1.2 x Rated Voltage for 5 seconds

Dissipation Factor (DF): $\leq 0.1\%$ @ 1 MHz and $\leq 5 \text{ Vrms}$


Insulation Resistance: 100K $\text{M}\Omega$ minimum @ 500 Vdc $\pm 10\%$

Types MCH and MCHN Multilayer High RF Power Capacitors

Mechanical Specifications


Bending Test:

Mount the capacitor as shown below and press the ram bar until a 2.0 mm deflection is achieved. There will be no visual damage and the capacitors will meet the limits of methods JIS 5102 8.11 and AEC-Q200-005 without cracking or visual damage.




Soldering Specifications

Reflow Solder Profile




Wave Solder Profile



Hand Soldering Method

- SnPb or SnAgCu recommended solder
- Do not use strong acid type flux with RM or RMS
- Soldering iron tip temperature should be 280 °C to 350 °C ≤ 5 sec.
- 80 Watt iron or less
- Iron tip should not touch chip terminals



Notice and Disclaimer: All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.