

Thermally-Enhanced High Power RF LDMOS FET 60 W, P_{3dB} @ 28 V, 2620 – 2690 MHz

Description


The PXAC260602FC is a 60-watt LDMOS FET with an asymmetrical design intended for use in multi-standard cellular power amplifier applications in the 2620 to 2690 MHz frequency band. Features include dual-path design, high gain and thermally-enhanced package with earless flanges. Manufactured with Infineon's advanced LDMOS process, this device provides excellent thermal performance and superior reliability.

PXAC260602FC
Package H-37248-4



Features

- Main: Input matched
Peak: Input and output matching
- Asymmetric Doherty design
 - Main: P_{1dB} = 15 W Typ
 - Peak: P_{1dB} = 50 W Typ
- Typical Pulsed CW performance, 2690 MHz, 28 V, 10 µs pulse width, 10% duty cycle, class AB, Doherty Configuration
 - Output power at P_{1dB} = 50 W
 - Efficiency = 50%
 - Gain = 15 dB
- Typical two-carrier WCDMA performance, 2690 MHz, 28 V, 8 dB PAR @ 0.01% CCDF, Doherty Configuration
 - Output power = 5 W
 - Efficiency = 40%
 - Gain = 15.7 dB
 - IMD = -30 dBc
- Capable of handling 10:1 VSWR @ 28 V, 50 W (CW) output power
- Integrated ESD protection : Human Body Model, Class 1B (per JESD22-A114)
- Low thermal resistance
- Pb-free and RoHS compliant



RF Characteristics

Single-carrier WCDMA Specifications (tested in Infineon Doherty test fixture)

V_{DD} = 28 V, I_{DQ} = 85 mA, P_{OUT} = 5 W avg, V_{GS(PK)} = V_{GS} at 300 mA -1.0V, f = 2620 – 2690 MHz, 3GPP signal, channel bandwidth = 3.84 MHz, peak/average = 10 dB @ 0.01% CCDF

Characteristic	Symbol	Min	Typ	Max	Unit
Linear Gain	G _{ps}	14	15.7	—	dB
Drain Efficiency	η _D	35	39	—	%
Adjacent Channel Power Ratio	ACPR	—	-31	-28	dBc

All published data at T_{CASE} = 25°C unless otherwise indicated

ESD: Electrostatic discharge sensitive device—observe handling precautions!

DC Characteristics (each side)





Characteristic	Conditions	Symbol	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage	$V_{GS} = 0\text{ V}$, $I_{DS} = 10\text{ mA}$	$V_{(BR)DSS}$	65	—	—	V
Drain Leakage Current	$V_{DS} = 28\text{ V}$, $V_{GS} = 0\text{ V}$	I_{DSS}	—	—	0.1	μA
	$V_{DS} = 63\text{ V}$, $V_{GS} = 0\text{ V}$	I_{DSS}	—	—	1.0	μA
Gate Leakage Current	$V_{GS} = 10\text{ V}$, $I_{DS} = 0\text{ V}$	I_{GSS}	—	—	—	μA
On-State Resistance (main)	$V_{GS} = 10\text{ V}$, $V_{DS} = 0.1\text{ V}$	$R_{DS(on)}$	—	0.8	—	Ω
	(peak) $V_{GS} = 10\text{ V}$, $V_{DS} = 0.1\text{ V}$	$R_{DS(on)}$	—	0.22	—	Ω
Operating Gate Voltage (main)	$V_{DS} = 28\text{ V}$, $I_{DQ} = 85\text{ mA}$	V_{GS}	2.5	2.75	3.0	V
	(peak) $V_{DS} = 28\text{ V}$, $I_{DQ} = 300\text{ mA}$	V_{GS}	2.3	2.7	3.1	V

Maximum Ratings


Parameter	Symbol	Value	Unit
Drain-Source Voltage	V _{DSS}	65	V
Gate-Source Voltage	V _{GS}	−6 to +10	V
Operating Voltage	V _{DD}	0 to +32	V
Junction Temperature	T _J	225	°C
Storage Temperature Range	T _{STG}	−65 to +150	°C
Thermal Resistance (main, T _{CASE} = 70°C, 5 W CW)	R _{θJC}	4.1	°C/W
(doherty, T _{CASE} = 70°C, 20 W CW)	R _{θJC}	2.0	°C/W

Ordering Information

Type and Version	Order Code	Package Description	Shipping
PXAC260602FC V1 R0	PXAC260602FCV1R0XTMA1	H-37248-4, earless flange	Tape & Reel, 50 pcs
PXAC260602FC V1 R250	PXAC260602FC V1R250XTMA1	H-37248-4, earless flange	Tape & Reel, 250 pcs

Typical Performance (data taken in a production test fixture)


Typical Performance (cont.)



Load Pull Performance


Main Side Load Pull Performance – Pulsed CW signal: 10 μs , 10% duty cycle, 28 V, 80 mA

		P _{1dB}									
		Max Output Power					Max PAE				
Freq [MHz]	Z _s [Ω]	Z _L [Ω]	Gain [dB]	P _{OUT} [dBm]	P _{OUT} [W]	PAE [%]	Z _L [Ω]	Gain [dB]	P _{OUT} [dBm]	P _{OUT} [W]	PAE [%]
2490	9.0 – j33	12.8 – j9.5	19.2	42.84	19.2	54.2	5.8 – j4.4	21.9	41.49	14.1	68.7
2620	25 – j47	13.9 – j10.6	18.8	43.15	20.6	58.7	8.9 – j6.8	20.4	42.24	16.7	66.4
2690	35 – j52	12.7 – j13.0	18.6	42.76	18.9	55.4	6.8 – j9.2	20.6	41.73	14.9	65.6

Peak Side Load Pull Performance – Pulsed CW signal: 10 μs , 10% duty cycle, 28 V, 250 mA

		P _{1dB}									
		Max Output Power					Max PAE				
Freq [MHz]	Z _s [Ω]	Z _L [Ω]	Gain [dB]	P _{OUT} [dBm]	P _{OUT} [W]	PAE [%]	Z _L [Ω]	Gain [dB]	P _{OUT} [dBm]	P _{OUT} [W]	PAE [%]
2490	4.1 – j13.1	3.7 – j5.2	16.7	48.44	70	56.0	6.2 – j1.3	18.9	46.59	46	63.4
2620	6.5 – j14.8	3.7 – j6.5	17	48.28	67	55.4	5.9 – j3.7	19.1	46.96	50	63.1
2690	9.0 – j17.8	3.7 – j6.1	17.6	48.11	65	56.2	5.7 – j2.4	20.9	46.30	43	64.6

Reference Circuit , 2620 – 2690 MHz



Reference circuit assembly diagram (not to scale)

Reference Circuit (cont.)


Reference Circuit Assembly

DUT	PXAC260602FC V1
Test Fixture Part No.	LTA/PXAC260602FC V1
PCB	Rogers 4350, 0.508 mm [0.020"] thick, 2 oz. copper, $\epsilon_r = 3.66$, $f = 2620 - 2690$ MHz
Find Gerber files for this test fixture on the Infineon Web site at http://www.infineon.com/rfpower	

Components Information


Component	Description	Suggested Manufacturer	P/N
Input			
C101, C103, C106, C108	Capacitor, 18 pF	ATC	ATC800A180JT250T
C102, C104	Capacitor, 10 μ F	Panasonic Electronic Components	EEE-HB1H100AP
C105, C107	Capacitor, 10 μ F	Taiyo Yuden	UMK325C7106MM-T
R101, R103	Resistor, 10 Ω	Panasonic Electronic Components	ERJ-3GEYJ100V
R102	Resistor, 50 Ω	Anaren	C16A5024
R104	Resistor, 20 Ω	Panasonic Electronic Components	ERJ-8GEYJ200V
S1	Directional Coupler, 5dB	Anaren	X3C25P1-05S
Output			
C201, C202, C204, C208	Capacitor, 18 pF	ATC	ATC800A180JT250T
C203, C207	Capacitor, 100 μ F	Panasonic Electronic Components	EEE-FP1V101AP
C205, C206	Capacitor, 10 μ F	Taiyo Yuden	UMK325C7106MM-T

Pinout Diagram (top view)



Lead connections for PXAC260602FC

Package Outline Specifications



Find the latest and most complete information about products and packaging at the Infineon Internet page
<http://www.infineon.com/rfpower>

Revision History

Revision	Date	Data Sheet Type	Page	Subjects (major changes since last revision)
01	2013-10-14	Advance	All	Data Sheet reflects advance specification for product development
02	2013-12-02	Production	All	Data Sheet reflects released product specification
02.1	2013-12-12	Production	1	Revised ESD classification
02.2	2014-05-14	Production	2 6	Revised junction temperature in Maximum Ratings table Corrected naming typo in Pinout Diagram
02.3	2015-12-23	Production	2	DC Characteristic table
02.4	2016-06-22	Production	2	Updated ordering information

We Listen to Your Comments

Any information within this document that you feel is wrong, unclear or missing at all?

Your feedback will help us to continuously improve the quality of this document.

Please send your proposal (including a reference to this document) to:

highpowerRF@infineon.com

To request other information, contact us at:

+1 877 465 3667 (1-877-GO-LDMOS) USA

or +1 408 776 0600 International



Edition 2016-06-22

Published by

Infineon Technologies AG

85579 Neubiberg, Germany

© 2015 Infineon Technologies AG

All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com/rfpower).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.