




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING

DIMENSIONS IN METRIC - []



NOTES:

1. TUSONIX STANDARD PART NUMBER: 513-012 A 5.0-30. TUSONIX RoHS COMPLIANT PART NUMBER: 513-012 A 5.0-30 LF. CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. TERMINALS AND ROTOR ARE COPPER ALLOY RoHS COMPLIANT MATERIALS WITH SILVER PLATING.
3. PART MARKING: TUSONIX TRADEMARK, CAPACITANCE RANGE AND DIELECTRIC TYPE CODE: STANDARD PART: BLACK INK. RoHS PART: DARK GREEN INK.
4. DIMENSION TOLERANCES
 $\leq .125" [3.18] = \pm .005 [0.13]$
 $\geq .126" [3.20] = \pm .015 [0.38]$

SPECIFICATIONS

Tusonix Style.	513 - 012
Value:	5.0 - 30 pF
Value Tol.:	MIN. +10%, MAX. -10% +100%
Rating:	100 VDC
Diel. Code:	A (NP0)
Operating Range:	-55°C TO + 85°C
To Tusonix Spec Unless Stated Otherwise	

X-2015 Rev-0

REVISION RECORD

A
Original Release
C.O. ECO-785

TOLERANCES
unless otherwise specified

2 PLC.
DECIMAL ± $\frac{\quad}{\quad}$
3 PLC.
DECIMAL ± $\frac{\quad}{\quad}$

ANGLES ± $\frac{\quad}{\quad}$

TUSONIX
TUCSON, ARIZONA

Title

**LOW PROFILE
CERAMIC TRIMMER**

Drawn L.E. 06-04-09

Scale 5 X

Approved R.L. 06-04-09

A

513-012 A 5.0-30

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

[0513-012-A-5.0-30LF](#)