



English | 简体中文 | 日本語

Search by Part Number



Search Site by keyword



Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Calculators | Cross Reference | Green Initiative | Military | Parametric Search | Search by Part Number, Keyword, Document, Green/Pb-Free, Package

Home > Products > Clock / Timing Devices > PC-Notebook-Server Clocks > Clock Synthesizer by Chipset Vendor > Desktop Chipsets > 952926 > 952926CFLF

You may also like...

952926CFLF

Category: Desktop Chipsets


Generic Part: 952926

Market Group: PC CLOCK

Description: ICS
ICS952926 is a 48 pin clock chip for VIA VX/CX 700 style chipsets. When used with a fanout DDR buffer, such as the 93788, it provides all the necessary clock signals for such a system.

Output Features: 3 - 0.7V current-mode differential CPU pairs

- 10 - PCI, 3 free running, 33MHz
- 2 - REF, 14.318MHz
- 3 - 3V66, 66.66MHz
- 1 - 48MHz
- 1 - 24/48MHz
- 2 - 25MHz, 2 free running @2.5V or 3.3V



Parameters

Temperature	C
Voltage	3.3 V
Package	SSOP 48
Speed	NA
Status	Active
Sample	Yes
Minimum Order Quantity	120
Factory Order Increment	30

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Misc	PC Clocks Contact Info	61 KB	05/29/2007

Package

Package	SSOP 48 (PVG48)
Description	SSOP 300 MIL
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Mark	F
Package Type	SSOP
Lead Count	48
Length	15.9 mm
Width	7.5 mm
Thickness	2.3 mm
Pitch	0.64 mm
Tube / Tray	TUBE
Quantity per Tube/Tray	30
Quantity per Reel	1000
Moisture Sensitivity Level (MSL)	1
Moisture Exposure Floor Life	Unlimited@<30C/85% RH
Peak Reflow Temperature	260Å°C
Rebake Conditions	NA
Related Package Documents	view documents