

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [30700-1168](#)
Status: **Active**
Overview: H-DAC 64™ Dual-Row High Density Automotive Connectors
Description: 2.54mm Pitch, 0.64mm Width H-DAC 64™ High Density Automotive Connectors, Dual Row, Female Harness Assembly, 16 Circuits, Polarization Option 2, Black

Documents:

3D Model	Product Specification PS-34646-001 (PDF)
Drawing (PDF)	Application Specification AS-30700-000 (PDF)
Product Specification PS-30700-0001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-30968-0001 (PDF)	



General

Product Family	Crimp Housings
Series	30700
Application	Power, Wire-to-Wire
Comments	Polarization Option 2
Overview	H-DAC 64™ Dual-Row High Density Automotive Connectors
Product Name	H-DAC 64™
UPC	822348517237

Physical

Circuits (maximum)	16
Color - Resin	Black, Red
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy, Polyester
Net Weight	4.513/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	7A
-------------------------------	----

Material Info

Reference - Drawing Numbers

Application Specification	AS-30700-000
Product Specification	PS-30700-0001, PS-30968-0001, PS-34646-001
Sales Drawing	SD-30700-120

EU RoHS

ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[30700Series](#)

Mates With

[30700 Header](#), [30968 Crimp Housing](#)

Use With

[34230 Terminal](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[30700-1168](#)