







Copyright FCI.

PRODUCT NO.
SEE TABLE



mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		FCI  www.fciconnect.com		
ltr	ecn no	dr	date	linear	.X ± 0.1			projection 	title DUAL POLARIZED QUICKIE II ASSEMBLY			
P	V22169	MSC	1992-05-21		.XX ± 0.05							
R	N05-0368	GUL	2005-12-27									
S	N09-0400	AZ	2010-01-18	angles	±2°			 INCH/MM	product family		QUICKIE	code
				dr	GuLing	12/27/05	size		dwg no	NT		
				enr	TaoDeniel	12/27/05	scale 1:1		A4	66901	sheet 1 of 2	
				chr	TaoDeniel	12/27/05						
				appd	Jason Zhou	12/27/05						
sheet	revision	s										
index	sheet	1-2										

PDM: Rev:S

STATUS: Released



Printed: Apr 12, 2011



Copyright FCI.

1					2		3		4		5		6
PRODUCT NO.	SIZE	DIM L	DIM S	DIM C	DASH NO	COVER ORIENTATION	POLARIZATION		STRAIN RELIEF				
66901-X10/X10LF	2X5	17.27	13.21	10.16	-0XX	THRU	DUAL ENTRY		DUAL POL.		YES		
-X14/X14LF	2X7	22.35	18.29	15.24	-1XX	THRU	DUAL ENTRY		DUAL POL.		NO		
-X16/X16LF	2X8	24.89	20.83	17.78	-2XX	THRU	DUAL ENTRY		CENTER KEY & DUAL POL.		YES		
-X20/X20LF	2X10	29.97	25.91	22.86	-3XX	THRU	DUAL ENTRY		CENTER KEY & DUAL POL.		NO		
-X24/X24LF	2X12	35.05	30.99	27.94	-4XX	BLIND	RIGHT		DUAL POL.		YES		
-X26/X26LF	2X13	37.59	33.53	30.48	-5XX	BLIND	RIGHT		DUAL POL.		NO		
-X30/X30LF	2X15	42.67	38.61	35.56	-6XX	BLIND	LEFT		DUAL POL.		YES		
-X34/X34LF	2X17	47.75	43.69	40.64	-7XX	BLIND	LEFT		DUAL POL.		NO		
-X40/X40LF	2X20	55.37	51.31	48.26	-8XX	BLIND	RIGHT		CENTER KEY & DUAL POL.		YES		
-X44/X44LF	2X22	60.45	56.39	53.34	-9XX	BLIND	LEFT		CENTER KEY & DUAL POL.		YES		
-X50/X50LF	2X25	68.07	64.01	60.96									
66901-X60/X60LF	2X30	80.77	76.71	73.66									A

COVER ORIENTATION



NOTES:

1. TERMINAL MATERIAL: FULL HARD PHOS. BRONZE ALLOY. UNS-C51000.
2. TERMINAL PLATING: 50u"/1.27um MIN Ni UNDERPLATE OVER ENTIRE TERMINAL AND 50u"/1.27um MIN Au OR GXT IN CONTACT AREA ONLY.
3. MOLDING MATERIAL: BASE & COVER-GLASS FILLED POLYESTER. FLAME RETARDANT PER UL94V-0. COLOR-BLUE.
4. CONNECTOR ASSEMBL ES PACKAGED IN TUBES.
5. THE FIST TWO CAVITY POSITIONS AND THE LAST TWO. ARE IDENTIFIED BY NUMBER.
6. POLARIZING FEATURES ARE DESCRIBED IN TABLE.
7. MOLDING MATERIAL: STRAIN RELIEF-NYLON, FLAME RETARDANT PER UL 94V-0,COLOR-BLUE.
8. STRAIN RELIEF DIM APPLIES WHEN DATUM -Z- IS HELD IN A RESTRAINED CONDITION.
9. THE POLARIZING FEATURE ON THIS END IS NON-EXISTANT ON 2X5 AND 2X7 POSITION CONNECTORS.
10. 2X5 POSITION NOT AVAILABLE WITH POLARIZATION SLOT ON CENTER KEY STYLE.
11. PRODUCT NUMBER 66901-XXX ^{LF} LEAD FREE OPTION
12. WITH "LF" MARK, TERMINAL PLATING: 50u"/1.27um MIN Ni UNDERPLATE OVER ENTIRE TERMINAL AND 50u"/1.27um MIN Au OR GXT IN CONTACT AREA ONLY.
13. FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
14. FOR LEAD FREE P/N, THE PLASTIC PART WILL WITHSTAND EXPOSURE TO 260°C PEAK TERMERATURE FOR 10 SECONDS IN A WAVE SOLDER REFLOW.
15. PRODDUCT SPEC. BUS-12-082
16. PLATING OPTIONS: MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

tolerances unless otherwise specified			CUSTOMER COPY		FCI www.fciconnect.com	
linear	.X ± 0.1		projection	title DUAL POLARIZED QUICKIE II ASSEMBLY		
	.XX ± 0.05					
angles	±2°					
dir	GuLing	12/27/05		product family QUICKIE		code
engr	TaoDeniel	12/27/05		size	dwg no	NT
chr	TaoDeniel	12/27/05	scale 1:1	A4	66901	sheet
appd	Jason Zhou	12/27/05				2 of 2