


Capacitor, film, 0.1 uF, +/-10% Tol, General Purpose, 100VDC@100C, Not for new design. Use F161PU104K100V (series F161)



Note: '()' correspond to the letters used in the product bulletin

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	5.7	+/-0.2
W	5	+/-0.2
T	4	+/-0.2
F	0.5	NOM

Packaging Specifications	
Package Kind:	T&R
Package Quantity:	2100

General Information	
Supplier:	KEMET
Miscellaneous Electrical:	Not for new design. Use F161PU104K100V (series F161)

Specifications	
Capacitance:	0.1 uF
Dielectric:	Metallized Polyester
Rated Temperature:	100C
Voltage @ rated temp:	100VDC
Voltage AC:	63VAC
Tolerance:	+/-10%
Body Type:	Surface Mount
Chip Size:	2220 (5750 metric)
Application:	General Purpose
Temperature Range:	-55/+100C
Dissipation Factor @ 1 kHz:	0.8%
Dissipation Factor @ 10 kHz:	1.2%
Dissipation Factor @ 100kHz:	2.5%
Insulation Resistance:	15 GOhm
Maximum dVdT:	30 v/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006-2014 IntelliData.net