

DESCRIPTION: 2MM DUAL ROW RECEPTACLE

"L" = NO. OF CONTACTS PER ROW X .079

MATERIAL:
HOUSING: NYLON 6T (UL 94V-0) BLACK
CONTACT: PHOSPHOR BRONZE
PLATING: GOLD FLASH MATING SIDE
100µ" TIN ON BOARD SIDE
RoHS COMPLIANT


ELECTRICAL:
CURRENT RATING: 1 AMP
CONTACT RESISTANCE: 20 mΩ MAX.
INSULATOR RESISTANCE: 5000 MEGOHMS MIN.
DWV: 500V AC
OPERATING TEMP:
-40°C TO +105°C
PROCESS TEMP: 260°C FOR 10 SECONDS

SERIES 2564 YY 01RP2
2564 = DUAL ROW

POSITIONS 2
DUAL = INCREMENTS OF 2
(06 TO 80)

TYPE: 01
01 = STRAIGHT

PLATING: P2
P2 = GOLD FLASH



	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 1-30-06	
		CHECKED:		DATE:	
		SCALE: NTS	SHEET 1 OF 1		REV 2
		DWG NO. 2564YY01RP2			