



(1,27 mm) .050"

TFSDT-05-30-G-05.00-D-NUS

TFSD-15-30-G-05.00-D-NUX

TFSS-07-30-G-05.00-D-NUS

TFSS, TFSST, TFSD, TFSDT SERIES

TIGER EYE™ DISCRETE CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications
see www.samtec.com?TFSS,
www.samtec.com?TFSD,
www.samtec.com?TFSDT, or
www.samtec.com?TFSST

Insulator Material:

Black LCP

Contact Material:

BeCu

Plating:

Au over 50μ" (1,27 μm) Ni

Operating Temp Range:

-10°C to +80°C (PVC)
10°C to +105°C (*T=5)

-40°C
Wire

Wire:
28 or 30 AWG

28 of 30 AWG
RoHS Compliant:


Yes

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality



Mates with:
SFM, SFC (-TR requires
TFM-WT option),
SFML (-XL end option
required)



TYPE STRIP	POSITIONS PER ROW	WIRE GAUGE	PLATING OPTION	ASSEMBLED LENGTH	END OPTION	END 2 OPTION
TFSS = Single Row PVC Cable TFSST = Single Row *Teflon® Cable TFSD = Double Row PVC Cable TFSDT = Double Row *Teflon® Cable	-03, -04, -05, -07, -10, -15, -20, -25, -40, -50 (Standard sizes)	-30 = 30 AWG -28 = 28 AWG	-G = 10μ" (0,25 μm) Gold on contact	-"XX.XX" = Assembled Length in Inches (76,20 mm) 03.00" min. for -S end option 03.25" min. for -D end option	-S = Single Ended -D = Double Ended -T = Transfer End Terminal on End 1 Socket on End 2 (See chart for End 2 option) -TF* = Transfer End with Friction Lock -TR = Transfer End with Retention Latch (TFM -WT option required for mating) * -05 & -07 positions not available. TFSD, TFSDT only	Requires -D, -TF or -TR (End 1 Notch Down). -NUS = Notch up, straight (Pin 1 to Pin 2) -NDS = Notch down, straight (Pin 1 to Pin N-1) -NUS = Notch up, crossed (Pin 1 to Pin 1) (TFSD/TFSDT only) -NDS = Notch down, crossed (Pin 1 to Pin N) (TFSD/TFSDT only)

END 2	END OPTION
T-NUS	Pin 1 to Pin N
T-NDS	Pin 1 to Pin 1
T-NUX	Pin 1 and Pin N-1
T-NDX	Pin 1 to Pin 2

Technical drawings illustrating the dimensions and end options for the cable assemblies:

- TFSD:** Dimensions include (6.10) .240, (14.26) .562, and Assembled Length ± (3.18) .125.
- TFSS:** Dimensions include No. of Positions x (1.27) .050 + (2.54) .100, (1.27) .050, (4.83) .190, and Assembled Length ± (3.18) .125.
- NDS or -NUS:** Shows End 1 Notch (Always Down) and End 2 Notch (NUS).
- NDS or -NUS:** Shows End 1 Notch (Always Down) and End 2 Notch (NDS).
- NDX or -NUX:** Shows End 1 Notch (Always Down) and End 2 Notch (NDX).

Due to technical progress, all designs, specifications and components are subject to change without notice

WWW.SAMTEC.COM

SAMTEC USA • Tel.: +1-800-SAMTEC-9 or +1-812-944-6733 **SAMTEC NORTHERN CALIFORNIA** • Tel.: +1-408-395-5900 **SAMTEC SOUTHERN CALIFORNIA** • Tel.: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel.: +55 31 3786 3227 **SAMTEC UNITED KINGDOM** • Tel.: +44 01236 739292 **SAMTEC GERMANY** • Tel.: +49 (0) 89 89460-0
SAMTEC FRANCE • Tel.: +33 1 60 95 06 60 **SAMTEC ITALY** • Tel.: +39 039 6890337 **SAMTEC NORDIC/BALTIC** • Tel.: +46 8 4477280 **SAMTEC BENELUX** • Tel.: +44 01236 739292
SAMTEC ISRAEL • Tel.: +972 7526600 **SAMTEC INDIA** • Tel.: +91 80 3272 1612 **SAMTEC ANZ** • Tel.: +613 9580 0663 **SAMTEC SINGAPORE** • Tel.: +65 6745 595 **SAMTEC JAPAN** • Tel.: +81 45 475 1385
SAMTEC SHANGHAI • Tel.: +86 21 6083 3766 **SAMTEC SHENZHEN** • Tel.: +86 755 83776780 **SAMTEC TAIWAN** • Tel.: +886 2 2735 6109 **SAMTEC HONG KONG** • Tel.: +852 26904058 **SAMTEC KOREA** • Tel.: +82 31 717 5685