

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF BUD INDUSTRIES INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF BUD INDUSTRIES INC. IS PROHIBITED.

MATERIAL:
REAR DOOR, SIDES - 20 GA. STEEL
FRONT DOOR, DOOR SUPPORTS - 18 GA. STEEL
TOP, BOTTOM, RAIL SUPPORTS, DOOR STOPS - 16 GA. STEEL
VERTICAL RAILS - 14 GA. STEEL
PANEL MOUNTING RAILS - 12 GA. STEEL


FINISH:
FRAME ASSEMBLY, SIDES, DOORS, MALE
HINGES - #4083-P BLACK TEXTURE "BT"
PANEL MOUNTING RAILS - #1895-P SMOOTH BLACK "EBL"

PANEL MOUNTING RAILS HAVE .343 SQ. HOLES ON E.I.A.
UNIVERSAL SPACING AND ARE FULLY ADJUSTED.


EACH PANEL MOUNTING RAIL IS SHIPPED MOUNTED TO
FRAME USING (4) #295 NUTS AND (4) #7346 SCREWS.

SWING HANDLES AND STRIKERS SHIPPED ASSEMBLED.


MOUNTING HOLES PIERCED IN BASE FOR CASTERS.





TOP VIEW




DETAIL C
SCALE 1 : 2




SECTION B-B




SECTION A-A




FRONT VIEW




FRONT VIEW
(LESS DOOR)




RIGHT SIDE VIEW



REAR VIEW



BOTTOM VIEW



DETAIL D
SCALE 1 : 2

21	1	55524	HARDWARE KIT
20	4	1034-L	SCREW #10-32 x 3/8 (LOCKING)
19	4	6488	FLAT WASHER #8
18	4	9159	SCREW #10-32 x 1/4 LG.
17	1	8106-STF	STRIKER FRONT
16	1	8106-STR	STRIKER REAR
15	1	8125-H	SWING HANDLE
14	1	8106-RDA	REAR DOOR ASSEMBLY
13	4	F-9653	RUBBER FOOT
12	32	7346	SCREW #10-32 x 5/8 LG.
11	2	3435-A	SCREW #8-32 x 3/8 LG.
10	4	316	SCREW #10-32 x 5/8 LG.
9	32	295	NUT RETAINER #10-32
8	2	8106-DS	DOOR STOP
7	4	8106-PMR	PANEL MOUNTING RAIL
6	2	8106-S	SIDE
5	1	9131	HINGE - MALE
4	1	9130	HINGE - MALE
3	1	8106-DA	DOOR ASSEMBLY
2	2	TP-1232	LIFT-OFF HINGE
1	1	8106-FA	FRAME ASSEMBLY

ITEM QTY. PART NO. DESCRIPTION

PARTS LIST

BUD INDUSTRIES INC.

SERVER CABINET RACK
w/VENTILATED STEEL DOOR

DATE 12-12-05

AS NOTED

AS NOTED

DO NOT SCALE DRAWING

SCALE

1

QTY.	USED ON	DO NOT SCALE DRAWING	SCALE	DC-8106	REV.
2					