




REF -50 OPTION SCREW
(WHERE APPLICABLE)




NOTES:

1. MATERIAL: SEE TABLE
2. INCH DIMENSIONS ARE SHOWN IN BRACKETS [XXX].
3. "XX" REFERS TO THE QUANTITY OF CIRCUITS.
4. ALL COMPONENTS ARE ROHS COMPLIANT.



4 CIRCUIT SHOWN



XX	SCREW&WASHER, 6-32X.250, PAN, PH/SL (-50 OPTION)	STEEL	ZN, CLEAR CHROMATE	
XX	SCREW, 6-32X.250, BHD, PHIL-SLOT (-49 OPTION)	BRASS	NICKEL	
XX	SCREW, 6-32X.250, BHD, PHIL-SLOT (STANDARD)	STEEL	ZN, CLEAR CHROMATE	
XX	TERMINAL, SOLDER TURRET	BRASS	TIN	
XX	MOUNTING PLATE	BRASS	NICKEL	
1	INSULATOR, SR, W/MTG	THERMOPLASTIC	BLACK	
M	QTY	DESCRIPTION	MATERIAL	FINISH

INITIAL RELEASE EC NO: ETC2007-0073 DRAWN: EHILE 2006/09/28 CHKD: JMACNEIL 2006/09/28 APPR: JMACNEIL 2006/09/29	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
					MM/IN		2:1	INCH		
					DRAWN BY DATE		9.53MM [.375] SR BTS ASSY, INSULATED TURRET TERMINAL W/MTG			
					EHILE 2006/09/13					
					CHECKED BY DATE					
				JMACNEIL 2006/09/13		MOLEX MOLEX INCORPORATED				
				APPROVED BY DATE						
				JMACNEIL 2006/09/13		MATERIAL NO.		DOCUMENT NO.		SHEET NO.
				ANGULAR ± 2 °		SD-38720-010				1 OF 2
				DRAFT WHERE APPLICABLE		SEE CHART				
				MUST REMAIN WITHIN DIMENSIONS						
				SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
				B						

