



PMT200B-81015

**DryLine® Dehydrator, Low-pressure membrane, wall mountable, 3.0 psig, with summary alarm, 115 Vac, 50/60 Hz, includes four individually-valved output ports**

- See related products for dc options, sold separately

## **OBSOLETE**

**This product was discontinued on: October 27, 2016**

### **Replaced By**

MT050C


DryLine® Dehydrator, Low-pressure membrane, 19 in rack mountable, Wall mountable, 3.0 psig (2-6 adjustable), with summary and discrete alarms, 115/230 Vac, 50/60 Hz

# Product Specifications

COMMSCOPE®

PMT200B-81015

## Outline Drawing-Front



**PMT200B FRONT VIEW**


DIMENSIONS ARE AS FOLLOWS: [ ] MILLIMETERS, INCHES

# Product Specifications

COMMSCOPE®

PMT200B-81015

## Outline Drawing-Side




PMT200B SIDE VIEW

# Product Specifications

COMMSCOPE®

PMT200B-81015

## Outline Drawing-Back




# Product Specifications

COMMSCOPE®

PMT200B-81015

## Outline Drawing-Top



PMT200B TOP VIEW

## Alarm

Alarm Type	Summary
Low-Pressure Alarm	68 mbar   7 kPa   1 psig

## Dimensions

Net Weight	16.6 kg   36.5 lb
Product Depth	177.8 mm   7.0 in
Product Height	457.2 mm   18.0 in
Product Width	444.5 mm   17.5 in
Gross Weight, Packed	21.8 kg   48.1 lb
Product Depth, Packed	406.4 mm   16.0 in
Product Height, Packed	558.8 mm   22.0 in
Product Width, Packed	533.4 mm   21.0 in

## Electrical Specifications

Power Cord	Europe power cord with stripped leads   USA power cord
Voltage	115 Vac $\pm 10\%$
Alarm Contact Rating	Form C dry contacts, 2 amps at 30 Vdc
Operating Temperature	-10 °C to +50 °C (+14 °F to +122 °F)
Power Consumption, average	190.0 W
Power Frequency	60/50 Hz
Power Phase	Single
Suggested Circuit Breaker Size	15 A
Circuit Breaker Requirement	Electrical connections require separate circuits for dehydrator installation

# Product Specifications

COMMSCOPE®

PMT200B-81015

## General Specifications

Dehydrator Type	Automatic Membrane
Voltage Type	ac
Volume Capacity, minimum	0.3 L   0.0 ft <sup>3</sup>
Volume Capacity, maximum	1699.0 L   60.0 ft <sup>3</sup>
Brand	DryLine®
Dew Point	Better than -45 °C (-50 °F) at 95% RH at +40 °C (+104 °F)
Flow Rate, nominal	5.66 SLPM   0.20 SCFM
Includes	3/8 in polyethylene tubing   Drill template   Instruction sheet   Male connector fitting   Power cord   Power cord connector lock   Street tee fitting   Union tee
Mount Type	Floor   Shelf   Wall
Port Count	4
Port Type	3/8 in PE tube
Regulated Output Pressure Type	factory set
Regulated Output Pressure, maximum	20.7 kPa   3.0 psig

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
China RoHS SJ/T 11364-2006	Below Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

