






FCIconnect.com

Copyright FCI

PRODUCT NO.
SEE TABLE

68683 - XXX - LF
LEAD FREE OPTION
PACKAGING OPTIONS .OMIT IF NOT REQUIRED.
NO. OF POSITIONS PER ROW
PLATING CODE
BASE PART NUMBER



mat'l. code				surface		tolerance	projection	product family			
-				ISO 1302		ISO 406 ISO 1101		DUBOX			
								title			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		INCH/MM	DUBOX DBL. ROW VERT.			
K	V10122	GIP	01/08/02		angles	linear		CARD CONNECTOR ASS'Y.			
L	V11677	GIP	01/22/02			.XX ±.01/.3 .XXX ±.005/.13 .XXXX ±.0020/.051	scale 4:1	dwg no			
M	V03-0309	HTB	04/29/03	0'±2'				sheet 1 of 4 size			
N	V05-0463	DPU	06/28/05	dr	J. SHREINER	02/05/91		68683			
P	M06-0237	MN	06/19/06	enr	M. HAHN	02/05/91		A3			
R	M06-0433	AGS	10/31/06	chr	M. HAHN	02/05/91		type Product Customer Drawing			
S	M07-0203	MHT	5/01/07	appd	M. HAHN	02/05/91					
sheet	revision	S	S	S	S						
index	sheet	1	2	3	4						

form: A3

PRODUCT NO NOTE 8	PLATING CONTACT AREA	PLATING SOLDER TAIL	
68683-2XX	15u"/.38u Au MIN OVER 50u"/1.27u Ni MIN	100μ"/160μ" SN 2.54μ/4.06μ	SEE NOTE 11
68683-3XX	30u"/.76u Au MIN OVER 50u"/1.27u Ni MIN	100μ"/160μ" SN 2.54μ/4.06μ	SEE NOTE 11
68683-4XX	100μ"/160μ" SN 2.54μ/4.06μ	100μ"/160μ" SN 2.54μ/4.06μ	
68683-6XX	30u"/.76u Au MIN OVER 50u"/1.27u Ni MIN	100μ"/160μ" SN 2.54μ/4.06μ	SEE NOTE 11
68683-8XX	30u"/.76u Au MIN OVER 50u"/1.27u Ni MIN	100μ"/160μ" SN 2.54μ/4.06μ	OBSOLETE




FIGURE A

NOTES:

- MATERIAL TERMINAL: PHOSPHOR BRONZE,
- RECOMMENDED APPLICATION DATA:
 - RECOMMENDED HOLE PATTERN IS SHOWN IN FIGURE A.
 - ALL MATING PINS TO BE .025/.64 SQUARE ON TRUE CENTER OF GIVEN TERMINAL SPACINGS WITHIN .015/.38 DIA.
 - SUGGESTED MATING PIN LENGTH .210±.020/5.33±.51
 - RECOMMENDED PC BOARD THICKNESS: .062/1.58
- MATERIAL HOUSING P.P.S. FILLED, COLOR BLACK, FLAME RETARDANT PER UL 94V-0
THIS PART WILL WITHSTAND EXPOSURES TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- FCI, FCI FINAL PART NUMBER AND DATE CODE TO BE MARKED ON TUBE LABEL.
- PREPLATED, STAMPED TERMINALS.
- PART NUMBER WITH SUFFIX "U" IS FOR SAWING PURPOSES ONLY.
- STANDARD TUBE PACKAGE PER BUS-14-097/3.
- ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENT".
- PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code		surface	tolerance	projection	product family
-		ISO 1302 ✓	ISO 406 ISO 1101	ISO 1101	DUBOX
ltr	ecn no	dr	date	tolerances unless otherwise specified	title
S				angles linear .XX ±.01/.3 .XXX ±.005/.13 .XXXX ±.0020/.051	DUBOX DBL. ROW VERT. CARD CONNECTOR ASS'Y.
				0'±2'	scale 4:1
		dr	J. SHREINER	02/05/91	dwg no
		enr	M. HAHN	02/05/91	sheet 2 of 4 size
		chr	M. HAHN	02/05/91	68683 A3
		appd	M. HAHN	02/05/91	type Product Customer Drawing
sheet index	revision sheet				



FCIconnect.com

Copyright FCI

PRODUCT NUMBER ↓	NO. OF POSITION ↓	C DIM	D DIM	LF OPTION
68683-Y26	2 X 26	2.500/63.50	2.617/66.47	NOTE 8
-Y27	2 X 27	2.600/66.04	2.717/69.01	
-Y28	2 X 28	2.700/68.58	2.817/71.55	
-Y29	2 X 29	2.800/71.12	2.917/74.09	
-Y30	2 X 30	2.900/73.66	3.017/76.63	
-Y31	2 X 31	3.000/76.20	3.117/79.17	
-Y32	2 X 32	3.100/78.74	3.217/81.71	
-Y33	2 X 33	3.200/81.28	3.317/84.25	
-Y34	2 X 34	3.300/83.82	3.417/86.79	
-Y35	2 X 35	3.400/86.36	3.517/89.33	
-Y36	2 X 36	3.500/88.90	3.617/91.87	
-Y37	2 X 37	3.600/91.44	3.717/94.41	
-Y38	2 X 38	3.700/93.98	3.817/96.95	
-Y39	2 X 39	3.800/96.52	3.917/99.49	
-Y40	2 X 40	3.900/99.06	4.017/102.03	
-Y41	2 X 41	4.000/101.60	4.117/104.57	
-Y42	2 X 42	4.100/104.14	4.217/107.11	
-Y43	2 X 43	4.200/106.68	4.317/109.65	
-Y44	2 X 44	4.300/109.22	4.417/112.19	
-Y45	2 X 45	4.400/111.76	4.517/114.73	
-Y46	2 X 46	4.500/114.30	4.617/117.27	
-Y47	2 X 47	4.600/116.84	4.717/119.81	
-Y48	2 X 48	4.700/119.38	4.817/122.35	
-Y49	2 X 49	4.800/121.92	4.917/124.89	
68683-Y50	2 X 50	4.900/124.46	5.017/127.43	SEE NOTE 6
68683-Y50U	2 X 50	4.900/124.46	5.017/127.43	

mat'l. code -				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family DUBOX
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
S					angles linear .XX ±.01/.3 .XXX ±.005/.13 .XXXX ±.0020/.051		DUBOX DBL. ROW VERT. CARD CONNECTOR ASS'Y.
					0'±2'	scale 4:1	dwg no sheet 4 of 4 size
				dr	J. SHREINER	02/05/91	68683 A3
				enr	M. HAHN	02/05/91	
				chr	M. HAHN	02/05/91	
				appd	M. HAHN	02/05/91	
sheet index	revision sheet						type Product Customer Drawing

form: A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[68683-342](#) [68683-632LF](#)