



DETAIL "A"
CHAMFER
SCALE=15:1

**UNCONTROLLED
DOCUMENT**

IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	43 Ω	127 Ω	280 Ω
Minimum	- Ω	102 Ω	- Ω

Z vs. FREQUENCY
(REF. ONLY)



AGILENT E4981A Impedance/Material Analyzer
HP 16092A-Test Fixture TEST REF. 2969

FERRITE CORE DIMENSIONS (SPEC): mm [in.]

A	22.80 [.898]	+	0.34 [.013]
B	18.70 [.736]	+	0.28 [.011]
C	16.00 [.630]	+	0.35 [.014]
D	2.80 [.110]	+	0.28 [.011]
E	0.70 [.028]	+	0.15 [.006]

WEIGHT/1000 3.95 kgs [8.70 Lbs]

SCALE DRAWING 1:1



28R0898-200

DIMENSIONS ARE IN mm[INCHES].				THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY AND CONFIDENTIAL TO STEWARD. NO PRODUCTION OR PUBLICATION OF THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT WRITTEN AUTHORIZATION FROM STEWARD.			
E	UPDATE Z SPECS & COMPANY LOGO	07/27/07	JRK	 			
D	CHG D DIM TOL TO ±.011	03/13/06	TMB				
C	UPDATE Z SPECS ADJUST C DIM TOL & ADD TEST REF #	07/27/04	TMB	PROJECT/PART NUMBER:	28R0898-200	REV	E
B	CHANGE PRINT FORMAT CHANGE Z SPECS	05/15/03	TMB	DATE:	10/17/02	SCALE:	3 : 1
A	ORIGINAL DRAFT	10/17/02	TMB	CAD #	28R0898-200-E	TOOL #	R0898
REV	DESCRIPTION	DATE	INT	MATERIAL: NiZn Ferrite			