





PRODUCT NO.

10126116-XYHLF

LEAD FREE OPTION
NOTE 6, 7 & 8
NO. OF POSITIONS
SEE TABLE
PIN PLATING
BASE P/N



mat'l. code		surface		tolerance		projection		product family	
ISO 1302		ISO 1302		ISO 1302		ISO 1302		HEADER	
l'tecn n'dr		date		tolerances unless otherwise specified		INCH/MM		title	
A	NEW	ZK	06/14/13	angles	linear	scale 3:1		FRICTION LATCH HEADER	
								SINGLE ROW, R/A	
								dwg no	
								10126116	
								sheet 1 of 2	
								A3	
								type	
								Product Customer Drawing	
sheet		revision		A					
index		sheet		1		2			



FCIconnect.com

Copyright FCI

PRODUCT NO.	NO.OF POS.	DIM K	DIM L	TAIL LENGTH DIM M
10126116-X03	1 X 3	.300/7.62	.200/5.08	.120/3.05
-X04	1 X 4	.400/10.16	.300/7.62	
-X05	1 X 5	.500/12.70	.400/10.16	
-X06	1 X 6	.600/15.24	.500/12.70	
-X07	1 X 7	.700/17.78	.600/15.24	
-X08	1 X 8	.800/20.32	.700/17.78	
-X09	1 X 9	.900/22.86	.800/20.32	
-X10	1 X 10	1.000/25.40	.900/22.86	
-X11	1 X 11	1.100/27.94	1.000/25.40	
-X12	1 X 12	1.200/30.48	1.100/27.94	
-X13	1 X 13	1.300/33.02	1.200/30.48	
-X14	1 X 14	1.400/35.56	1.300/33.02	
10126116-X15	1 X 15	1.500/38.10	1.400/35.56	.120/3.05
10126116-X43	1 X 3	.300/7.62	.200/5.08	.190/4.83

PIN PLATING CODES	
-1YY	30u"/.76u Au MIN. ON 50u"/1.27u Ni
-2YY	15u/.38u Au MIN. ON 50u"/1.27u Ni

- NOTES:
1. MOLDING MAT'L: GLASS REINFORCED PCT OR MINRAL FILLED LCP, COLOR: BLACK
FLAME RETARDANT PER UL-94V-0
MAXIMUM OPERATING TEMPERATURE 130° C.
 2. PIN MATERIAL: 3/4 HD PHOS. BRZ.
 3. NO SLOTS ON 1 X 5 POSITION OR SMALLER PRODUCT. THE CENTER KEY SLOT WILL BE ON ALL HEADERS REGARDLESS OF SIZE.
 4. TWO NON-CRITICAL SIDES OF PIN TIP NOT PLATED, BOTH ENDS.
 5. COMPANY LOGO MAY APPEAR IN THIS AREA.
 6. ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
 7. PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.
 8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family HEADER	
ltr ecn nodr date		tolerances unless otherwise specified				title			
A		angles	linear	XXX±.01/XXX±.03 XXX±.005/XXX±.013 XXX±.0020/XXX±0.05		FRICION LATCH HEADER SINGLE ROW, R/A			
		0°±2'			scale 3:1		dwg no		sheet 2 of 2
		dr	ZK HU	06/14/13		FCI		size A3	
		engr	ZK HU	06/14/13				10126116	
		chr	RICK BIAN	06/14/13				type Product Customer Drawing	
		appd	RICK BIAN	06/14/13					
sheet index	revision sheet								