

# DUAL-IN-LINE SOCKETS

## SERIES 110 • SELECTIVELY LOADED RELAY DIP SOCKET, SOLDER TAIL





Fig. 1




Fig. 2




Fig. 3




Fig. 4




Fig. 5





Fig. 6

○ = Loaded Position ● = Empty Position

- Relay sockets accept devices with I/O pins on .100" grid
- Additional Relay DIP socket patterns are available on Page 134
- Series 110 use MM #1001 receptacles. See page 165 for details
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



## ORDERING INFORMATION

<b>FIG. 1</b>	<b>Series 110...002</b>	<b>8 Position Relay Socket</b>
	110-XX-210-10-002000	
<b>FIG. 2</b>	<b>Series 110...002</b>	<b>8 Position Relay Socket</b>
	110-XX-314-10-002000	
<b>FIG. 3</b>	<b>Series 110...003</b>	<b>8 Position Relay Socket</b>
	110-XX-316-10-003000	
<b>FIG. 4</b>	<b>Series 110...004</b>	<b>4 Position Relay Socket</b>
	110-XX-316-10-004000	
<b>FIG. 5</b>	<b>Series 110...005</b>	<b>8 Position Relay Socket</b>
	110-XX-316-10-005000	
<b>FIG. 6</b>	<b>Series 110...002</b>	<b>14 Position Relay Socket</b>
	110-XX-328-10-002000	

XX=Plating Code  
See Below

RoHS-2  
2011/65/EU

SPECIFY PLATING CODE XX=	13	93	43
Sleeve (Pin)	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn
Contact (Clip)	30 μ" Au	30 μ" Au	30 μ" Au

