

## 132-00006

Button Head Tie w/ Pilot Bushings , 105lb, 9.63", Max Bun Dia 2.62" PA66HIRHS Black  
50/pk

Article Number: 132-00006

Part Number: 132-00006

Type: BT105RP

Material: PA66HIRHSUV



### 1. Base Data

---

**Part No.** 132-00006

**Type** BT105RP


**Color** Black (BK)

**Features** The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains serrations on both sides and has two opposed pawls recessed within a domed head. This design allows the strap to be directed clockwise or counter-clockwise.

## Application

Using a single hole these 'chassis ties' are widely used in the automotive, truck and heavy equipment markets. Ideal for applications which have access to both sides of the hole - example truck frame rails.

## 2. Product Dimensions



**Min. Tensile Strength** 105 lbs / 467 N

**Length (L)** 9.63 " / 244.4 mm

**Width (W)** .22 " / 5.6 mm

**Min. Ø Bundle** .06 " / 1.5 mm

**Max. Ø Bundle** 2.62 " / 66.7 mm

## 4. Material and Specifications

**Material** Polyamide 6.6 high impact modified, heat-/UV-stabilized (PA66HIRHSUV)

**Material Shortcut** PA66HIRHSUV

<b>Cable Tie</b>	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
<b>Flammability</b>	UL94 HB
<b>Material Head</b>	PA66HS
<b>Operating Temperature</b>	-40 °F to +185 °F (-40 °C to +85 °C) continuous

### Logistic and Packaging

---

<b>Packaging Type</b>	bag
<b>Pkg. Qty.</b>	50
<b>UPC</b>	08930627174

---

### Button Head Ties


The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains serrations on both sides and has two opposed pawls recessed within a domed head.

This design allows the strap to be directed clockwise or counter-clockwise prior to insertion into the head, enabling bi-directional looping.




### New and Improved Features

The button head tie offers many new and improved features for added durability and installation ease.




**Button Head Ties *continued***



Material Data	
Cable Tie Material	<b>Polyamide 6.6 high impact modified, heat stabilized (PA66HIRHS)</b>
Button Head Material	<b>Polyamide 6.6 heat stabilized (PA66HS)</b>
Operating Temperature	<b>-40 °F to +221 °F (-40 °C to +105 °C) continuous</b>
Color	<b>Black</b>
Flammability	<b>UL94 HB</b>

RoHS



Product Selection			Min. Tensile Strength	Length (L)	Max. Ø Bundle	Width (W)	Pkg. Qty.
Article No.	Part No.	Type					
<b>BT105 Button Head Ties</b>							
132-00010	<b>132-00010</b>	BT105R	105 lbs (467)	9.63" (244.4)	2.62" (66.7)	.22" (5.6)	Black 50
132-00011	<b>132-00011</b>	BT105L	105 lbs (467)	15" (381.5)	4.33" (110)	.22" (5.6)	Black 50
<b>BT105 Button Head Ties with Pilot Bushings</b>							
132-00006	<b>132-00006</b>	BT105RP	105 lbs (467)	9.63" (244.4)	2.62" (66.7)	.22" (5.6)	Black 50
132-00007	<b>132-00007</b>	BT105LP	105 lbs (467)	15" (381.5)	4.33" (110)	.22" (5.6)	Black 50
<b>BT130 Button Head Ties with Retainers and Pilot Bushings</b>							
132-00008	<b>132-00008</b>	BT130RDP	130 lbs (578)	10.51" (267.0)	2.87" (73)	.30" (7.6)	Black 50
132-00009	<b>132-00009</b>	BT130LDP	130 lbs (578)	15" (381.5)	4.33" (110)	.30" (7.6)	Black 50

Installation tools - MK9, MK9HT, MK9P. Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.