

C1608X5R1A335K080AC (TDK item description : C1608X5R1A335KT****)

Applications



Commercial Grade



Please refer to Part No. CGA3E1X5R1A335K080AC for automotive use.


Feature

General

General (Up to 50V)

Series

C1608 [EIA CC0603]




Size	
Length(L)	1.60mm +/-0.10mm
Width(W)	0.80mm +/-0.10mm
Thickness(T)	0.80mm +/-0.10mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	0.30mm Min.
Recommended Land Pattern(PA)	0.70 to 1.00mm (Flow Soldering) 0.60 to 0.80mm (Reflow Soldering)
Recommended Land Pattern(PB)	0.80 to 1.00mm (Flow Soldering) 0.60 to 0.80mm (Reflow Soldering)
Recommended Land Pattern(PC)	0.60 to 0.80mm (Flow Soldering) 0.60 to 0.80mm (Reflow Soldering)
Recommended Slit Pattern(SD)	

Electrical Characteristics	
Capacitance	3.3uF +/-10%
Rated Voltage	10Vdc
Temperature Characteristic	X5R(+/-15%)
Dissipation Factor	10% Max.
Insulation Resistance	30MΩ Min.


Other	
Soldering Method	Reflow, Flow
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.

C1608X5R1A335K080AC


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




C1608X5R1A335K080AC




C1608X5R1A335K080AC




C1608X5R1A335K080AC



C1608X5R1A335K080AC



C1608X5R1A335K080AC(DC Bias = 0V) C1608X5R1A335K080AC(DC Bias = 5V)



C1608X5R1A335K080AC(100kHz) C1608X5R1A335K080AC(500kHz)
C1608X5R1A335K080AC(1MHz)