



MBH-TLR




- For applications that require various bundle diameters
- Supplied in reels of 82.50 feet (25.0m), 200.00 feet (60.9m), 250.00 feet (76.2m) or 1000.00 feet (304.8m)
- Provides job site versatility with minimum inventory
- Packaging speeds removal of steel and includes bundle diameter cut-off guide
- Available in AISI 304 stainless steel for general-purpose applications
- Available in AISI 316 stainless steel for the most corrosive environments
- Note: For the recommended installation tools, select from the list of part number in the table below

Part Number	MBH-TLR
RoHS Compliancy Status	Compliant
Part Description	Custom length continuous banding, heavy, .50 in. (12.7mm) min. bundle diameter.
Material	Stainless Steel Type 304
Color	natural
Length (ft.)	250
Length (m)	76
Width (In.)	.31
Width (mm)	7.9
Banding Head	MTHH-C
Cross Section	Heavy
Max. Bundle Diameter (In.)	Any
Max. Bundle Diameter (mm)	Any
Min. Bundle Diameter (In.)	.50
Min. Bundle Diameter (mm)	12.7
Min. Loop Tensile Strength (Lbs.)	250
Min. Loop Tensile Strength (N)	1112
Pricing Description	Custom Banding, 304 Steel, Heavy 250ft (76m)
Thickness (In.)	.010
Thickness (mm)	.25
Tool	GS4MT, HTMT, PPTMT, ST2MT
Used with Buckle	MTHH-C
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	

(A)

BANDING PART NUMBER	COIL BAND WIDTH ±.010" [0.25]	MAT'L. TYPE	MAT'L. COATING	REQ'D. BANDING HEAD PART NUMBER	MAT'L LENGTH	MAT'L. THICKNESS ±.001" [0.03]	MAT'L. EDGES
MBS-TLR	.173 [4.39]	304	-----	MTHS-C	250.0' [76.2m]	.010" [.25]	NOTE 5
MBH-TLR	.312 [7.92]	304	-----	MTHH-C	250.0' [76.2m]	.010" [.25]	NOTE 5
MBS-TLR316	.173 [4.39]	316	-----	MTHS-C316	250.0' [76.2m]	.010" [.25]	NOTE 5
MBH-TLR316	.312 [7.92]	316	-----	MTHH-C316	250.0' [76.2m]	.010" [.25]	NOTE 5
MBCH-QR316	.312" [7.93]	316	POLYESTER	MTHCH-C316	82.5' [25.0m]	.010" [.25]	NOTE 6



NOTES:

1. INSTALLATION TOOLS:
PPTMT,GS4MT,ST2MT,HTMT & ST3MT.
2. UNLESS OTHERWISE SPECIFIED,
DIMS IN [] ARE IN mm
3. SEE TABLE FOR COMPATIBLE
BANDING HEAD PART NUMBERS.
4. TOLERANCES UNLESS OTHERWISE SPECIFIED:
.X ± .13[3.30]
5. FULLY ROUNDED EDGES.
6. FULLY COATED MATERIAL.
COATING THICKNESS: .003"/.007" [.08/.18] PER SIDE

02	5/05	JAMB	EJD	REQ'D.BANDING HEAD PART NO.MTHCH-C316 WAS PART NO.MTHCHD-C316	12678	CCH	JJB
01	11/04	JAMB	EJD	ADDED PART NO.'S MBCH-QR316 TO TABLE	12175	CCH	JJB
00	10/04	JAMB	EJD	DRAWING RELEASED	12064	CCH	JJB
REV	10/03	BY	CHK	DESCRIPTION	ECN#	PM	CUST

S41194_02



TINLEY PARK, ILLINOIS

STAINLESS STEEL METAL BANDING
CONTINUOUS

DRAWN BY JAMB	CHK'D EJD	SCALE NO SCALE	DRAWING NO. S41194
------------------	--------------	-------------------	-----------------------