




ACTUATOR MARKING: NONE
ACTUATOR COLOR: WHITE

HOUSING COLOR: WHITE



PANEL THICKNESS	X dimension
0.75-1.25 [.030-.049]	19.2-.01 [.756]
1.25-2.0 [.049-.079]	19.4-.01 [.764]
2.0-3.0 [.079-.118]	19.8-.01 [.780]




PANEL CUTOUT
NOT TO SCALE

SWITCH FUNCTION	
POS. 1	POS. 2
DN	OFF
1-1a	OPEN



CIRCUIT: SPST

- NOTES:
1. ALL DIMENSIONS IN MM
 2. GENERAL TOLERANCE: X.X=±0.4; X.XX=±0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 4. RATING: 4(1)A @250VAC, 6A @250VAC
10A @125VAC
 5. MATERIALS: TERMINALS: COPPER ALLOY W/SILVER PLATING
CONTACTS: COIN SILVER
 6. MECHANICAL LIFE: >50,000 CYCLES
 7. ELECTRICAL LIFE: >10,000 CYCLES
 8. CONTACT RESISTANCE: < 20 MEGA-OHMS (INITIAL)
 9. INSULATION RESISTANCE: > 1000 MEGA-OHMS @ 500VDC
 10. DIELECTRIC STRENGTH: >1500VAC 1 MINUTE (INITIAL)
>3000V BETWEEN POLES



E-SWITCH®

B	15318	CHANGED TITLE TO MATCH QAD	9/23/05	PH
A	13004	RELEASED FOR PRODUCTION	4/7/03	AR
REV.	ECN NO.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

TITLE				
R6A/WH/WHITE				
SCALE	DATE	DR	DWG	REV
1.5:1	4/7/03	AR	M060306	B