




4

3

2

1



NOTES:

1. Unless otherwise noted, all dimensions are in inches.
2. Foil Material: .002 thick 1145 aluminum
3. Interface Material: .0005 thick phase-change thermal compound, both sides.
Maximum shipping & storage temperature – 40°C
Reflow temperature – 60°C
Maximum recommended service temperature – 200°C
4. Thermal impedance: .030 °C/W-in² (.194 °C/W-cm²) @ 20psi
5. Thermal washers shall be packaged in quantities of 10 with oversize separators between them.
6. Used with 18-pin DIP package (Apex designator: EL).
7. Power Devices part no. AL-103-103-APX
8. Supplier is to label each plastic box with the Cirrus Logic part number.

TOLERANCES – UNLESS OTHERWISE SPECIFIED	
.XX	= ±.01
.XXX	= ±.005
ANG.	= ±.5°



TITLE THERMAL WASHER, DIP				PART NO. TW09			
SUBJECT MECHANICAL DRAWING							
ENG. D-M	TECH/DRAW. P.ECK	DCA 11077	SH. OF 1 1	FILENAME TW09	REV E	DATE 28FEB11	

4

3

2

1