



SCALE 5:1



NOTES.

1. MATERIAL: (0.20)/.008 PHOSPHOR BRONZE
2. PLATING: HOT TIN DIP
3. TERMINAL WILL ACCOMMODATE
22 AWG SOLID OR FUSED WIRE
24 AND 26 AWG SOLID, STRANDED OR FUSED WIRE
WITH (1.52)/.060 MAX. INSULATION DIA.
4. P.C.B. MOUNTING HOLE:
22 AWG DIA (1.23/1.30)-.048/.051
24 AND 26 AWG DIA (1.17/1.25)-.046/.049
5. MAX. P.C.B. THICKNESS (1.19±0.20)/.047±.008

UPDATED BORDER EC NO: E2007-0844 DRWN:DMAHER CHKD: APPR:EFOLAN 2007/04/05 2007/04/12 2007/04/13	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
				mm	INCH	DRAWN BY CTOB IN	DATE 98/07/06	TITLE PCM CRIM TERM BRD-IN STAND ALONE 1TNL	MOLEX INCORPORATED	SHEET NO. 2 OF 2			
			4 PLACES	± ---	± ---	CHECKED BY TMAHON	DATE 98/07/06						
			3 PLACES	± ---	±.008	APPROVED BY MWILHITE	DATE 98/07/06						
			2 PLACES	± 0.20	±.015	MATERIAL NO. 901980002		DOCUMENT NO. SD-90198					
			1 PLACE	± 0.38	± ---	SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
			ANGULAR ± .5 °										
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
			REV	M									