


**SN54195, SN54LS195A, SN54S195,  
SN74195, SN74LS195A, SN74S195  
4-BIT PARALLEL-ACCESS SHIFT REGISTERS**  
MARCH 1974—REVISED MARCH 1988


- Synchronous Parallel Load
- Positive-Edge-Triggered Clocking
- Parallel Inputs and Outputs from Each Flip-Flop
- Direct Overriding Clear
- J and  $\bar{K}$  Inputs to First Stage
- Complementary Outputs from Last Stage
- For Use in High Performance:  
Accumulators/Processors  
Serial-to-Parallel, Parallel-to-Serial  
Converters

SN54195, SN54LS195A, SN54S195 . . . J OR W PACKAGE  
SN74195 . . . N PACKAGE  
SN74LS195A, SN74S195 . . . D OR N PACKAGE

(TOP VIEW)



SN54LS195, SN54S195 . . . FK PACKAGE  
(TOP VIEW)



NC - No internal connection

### description

These 4-bit registers feature parallel inputs, parallel outputs, J- $\bar{K}$  serial inputs, shift/load (SH/ $\bar{LD}$ ) control input, and a direct overriding clear. All inputs are buffered to lower the input drive requirements. The register has two modes of operation:

Parallel (broadside) load

Shift (in the direction  $Q_A$  toward  $Q_D$ )

Parallel loading is accomplished by applying the four bits of data and taking SH/ $\bar{LD}$  low. The data is loaded into the associated flip-flop and appears at the outputs after the positive transition of the clock input. During loading, serial data flow is inhibited.

Shifting is accomplished synchronously when SH/ $\bar{LD}$  is high. Serial data for this mode is entered at the J- $\bar{K}$  inputs. These inputs permit the first stage to perform as a J- $\bar{K}$ , D-, or T-type flip-flop as shown in the function table.

The high-performance 'S195, with a 105-megahertz typical maximum shift-frequency, is particularly attractive for very-high-speed data processing systems. In most cases existing systems can be upgraded merely by using this Schottky-clamped shift register.

| TYPE    | TYPICAL<br>MAXIMUM CLOCK<br>FREQUENCY | TYPICAL<br>POWER<br>DISSIPATION |
|---------|---------------------------------------|---------------------------------|
| '195    | 39 MHz                                | 195 mW                          |
| 'LS195A | 39 MHz                                | 70 mW                           |
| 'S195   | 105 MHz                               | 350 mW                          |

FUNCTION TABLE

| CLEAR |   | SHIFT/<br>LOAD |  | CLOCK |  | INPUTS |           |   |   | OUTPUTS |       |                |          |             |
|-------|---|----------------|--|-------|--|--------|-----------|---|---|---------|-------|----------------|----------|-------------|
|       |   |                |  |       |  | SERIAL | PARALLEL  |   |   | $Q_A$   | $Q_B$ | $Q_C$          | $Q_D$    | $\bar{Q}_D$ |
|       |   |                |  |       |  | J      | $\bar{K}$ | A | B | C       | D     |                |          |             |
| L     | X | X              |  | X     |  | X      | X         | X | X | X       | X     | L              | L        | L           |
| H     | L |                |  | ↑     |  | X      | X         | a | b | c       | d     | a              | b        | c           |
| H     | H | L              |  |       |  | X      | X         | X | X | X       | X     | $Q_{A0}$       | $Q_{B0}$ | $Q_{C0}$    |
| H     | H |                |  | ↑     |  | L      | H         | X | X | X       | X     | $Q_{A0}$       | $Q_{A0}$ | $Q_{Bn}$    |
| H     | H |                |  | ↑     |  | L      | L         | X | X | X       | X     | L              | $Q_{An}$ | $Q_{Bn}$    |
| H     | H |                |  | ↑     |  | H      | H         | X | X | X       | X     | H              | $Q_{An}$ | $Q_{Bn}$    |
| H     | H |                |  | ↑     |  | H      | L         | X | X | X       | X     | $\bar{Q}_{An}$ | $Q_{An}$ | $Q_{Bn}$    |

H = high level (steady state)

L = low level (steady state)

X = irrelevant (any input, including transitions)

↑ = transition from low to high level

a, b, c, d = the level of steady-state input at A, B, C, or D, respectively

$Q_{A0}$ ,  $Q_{B0}$ ,  $Q_{C0}$ ,  $Q_{D0}$  = the level of  $Q_A$ ,  $Q_B$ ,  $Q_C$ , or  $Q_D$ , respectively, before the indicated steady-state input conditions were established

$Q_{An}$ ,  $Q_{Bn}$ ,  $Q_{Cn}$  = the level of  $Q_A$ ,  $Q_B$ , or  $Q_C$ , respectively, before the most-recent transition of the clock


PRODUCTION DATA documents contain information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

**SN54195, SN54LS195A, SN54S195,  
SN74195, SN74LS195A, SN74S195  
4-BIT PARALLEL-ACCESS SHIFT REGISTERS**


logic diagram (positive logic)




† This connection is made on '195 only.  
Pin numbers shown are for D, J, N, and W packages.

**SN54195, SN54LS195A, SN54S195,  
SN74195, SN74LS195A, SN74S195  
4-BIT PARALLEL-ACCESS SHIFT REGISTERS**

typical clear, shift, and load sequences



logic symbols†




†These symbols are in accordance with ANSI/IEEE Std. 91-1984 and IEC Publication 617-12.  
Pin numbers are for D, J, N, and W packages.


**SN54195, SN54LS195A, SN54S195, SN74195, SN74LS195A, SN74S195**  
**4-BIT PARALLEL-ACCESS SHIFT REGISTERS**

schematics of inputs and outputs


'195



'LS195A



'S195



**TEXAS**  
**INSTRUMENTS**

POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

# SN54195, SN74195 4-BIT PARALLEL-ACCESS SHIFT REGISTERS

## absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

|                                               |                |
|-----------------------------------------------|----------------|
| Supply voltage, $V_{CC}$ (see Note 1)         | 7 V            |
| Input voltage                                 | 5.5 V          |
| Operating free-air temperature range: SN54195 | -55°C to 125°C |
| SN74195                                       | 0°C to 70°C    |
| Storage temperature range                     | -65°C to 150°C |

NOTE 1: Voltage values are with respect to network ground terminal.

## recommended operating conditions

|                                                          |                          |  | SN54195 |     |     | SN74195 |     |      | UNIT    |             |
|----------------------------------------------------------|--------------------------|--|---------|-----|-----|---------|-----|------|---------|-------------|
|                                                          |                          |  | MIN     | NOM | MAX | MIN     | NOM | MAX  |         |             |
| Supply voltage, $V_{CC}$                                 |                          |  | 4.5     | 5   | 5.5 | 4.75    | 5   | 5.25 | V       |             |
| High-level output current, $I_{OH}$                      |                          |  | -800    |     |     | -800    |     |      | $\mu A$ |             |
| Low-level output current, $I_{OL}$                       |                          |  | 16      |     |     | 16      |     |      | mA      |             |
| Clock frequency, $f_{clock}$                             |                          |  | 0       | 30  |     | 0       | 30  |      | MHz     |             |
| Width of clock input pulse, $t_{w(clock)}$               |                          |  | 16      |     |     | 16      |     |      | ns      |             |
| Width of clear input pulse, $t_{w(clear)}$               |                          |  | 12      |     |     | 12      |     |      | ns      |             |
| Setup time, $t_{su}$ (see Figure 1)                      | Shift/load               |  | 25      |     |     | 25      |     |      | ns      |             |
|                                                          | Serial and parallel data |  | 20      |     |     | 20      |     |      |         |             |
|                                                          | Clear inactive-state     |  | 25      |     |     | 25      |     |      |         |             |
| Shift/load release time, $t_{release}$ (see Figure 1)    |                          |  | 10      |     |     | 10      |     |      | ns      |             |
| Serial and parallel data hold time, $t_H$ (see Figure 1) |                          |  | 0       |     |     | 0       |     |      | ns      |             |
| Operating free-air temperature, $T_A$                    |                          |  | -55     |     |     | 125     |     | 0    | 70      | $^{\circ}C$ |

## electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER                                    | TEST CONDITIONS†                                                                                           | MIN     | TYP‡ | MAX  | UNIT    |
|----------------------------------------------|------------------------------------------------------------------------------------------------------------|---------|------|------|---------|
| $V_{IH}$ High-level input voltage            |                                                                                                            | 2       |      |      | V       |
| $V_{IL}$ Low-level input voltage             |                                                                                                            |         |      | 0.8  | V       |
| $V_{IK}$ Input clamp voltage                 | $V_{CC} = \text{MIN}$ , $I_I = -12 \text{ mA}$                                                             |         |      | -1.5 | V       |
| $V_{OH}$ High-level output voltage           | $V_{CC} = \text{MIN}$ , $V_{IH} = 2 \text{ V}$ ,<br>$V_{IL} = 0.8 \text{ V}$ , $I_{OH} = -800 \mu\text{A}$ | 2.4     | 3.4  |      | V       |
| $V_{OL}$ Low-level output voltage            | $V_{CC} = \text{MIN}$ , $V_{IH} = 2 \text{ V}$ ,<br>$V_{IL} = 0.8 \text{ V}$ , $I_{OL} = 16 \text{ mA}$    |         | 0.2  | 0.4  | V       |
| $I_I$ Input current at maximum input voltage | $V_{CC} = \text{MAX}$ , $V_I = 5.5 \text{ V}$                                                              |         |      | 1    | mA      |
| $I_{IH}$ High-level input current            | $V_{CC} = \text{MAX}$ , $V_I = 2.4 \text{ V}$                                                              |         |      | 40   | $\mu$ A |
| $I_{IL}$ Low-level input current             | $V_{CC} = \text{MAX}$ , $V_I = 0.4 \text{ V}$                                                              |         |      | -1.6 | mA      |
| $I_{OS}$ Short-circuit output current§       | $V_{CC} = \text{MAX}$                                                                                      | SN54195 | -20  | -57  | mA      |
|                                              |                                                                                                            | SN74195 | -18  | -57  |         |
| $I_{CC}$ Supply current                      | $V_{CC} = \text{MAX}$ , See Note 2                                                                         |         | 39   | 63   | mA      |

†For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

‡All typical values are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

§Not more than one output should be shorted at a time.

NOTE 2: With all outputs open, shift/load grounded, and 4.5 V applied to the J, K, and data inputs,  $I_{CC}$  is measured by applying a momentary ground, followed by 4.5 V, to clear and then applying a momentary ground, followed by 4.5 V, to clock.

## switching characteristics, $V_{CC} = 5 \text{ V}$ , $T_A = 25^\circ\text{C}$

| PARAMETER                                                             | TEST CONDITIONS                                                 | MIN | TYP | MAX | UNIT |
|-----------------------------------------------------------------------|-----------------------------------------------------------------|-----|-----|-----|------|
| $f_{max}$ Maximum clock frequency                                     | $C_L = 15 \text{ pF}$ ,<br>$R_L = 400 \Omega$ ,<br>See Figure 1 | 30  | 39  |     | MHz  |
| $t_{PHL}$ Propagation delay time, high-to-low-level output from clear |                                                                 |     | 19  | 30  | ns   |
| $t_{PLH}$ Propagation delay time, low-to-high-level output from clock |                                                                 |     | 14  | 22  | ns   |
| $t_{PHL}$ Propagation delay time, high-to-low-level output from clock |                                                                 |     | 17  | 26  | ns   |



POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

# SN54LS195A, SN74LS195A

## 4-BIT PARALLEL-ACCESS SHIFT REGISTERS

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

|                                                  |                |
|--------------------------------------------------|----------------|
| Supply voltage, $V_{CC}$ (see Note 1)            | 7 V            |
| Input voltage                                    | 7 V            |
| Operating free-air temperature range: SN54LS195A | -55°C to 125°C |
| SN74LS195A                                       | 0°C to 70°C    |
| Storage temperature range                        | -65°C to 150°C |

NOTE 1: Voltage values are with respect to network ground terminal.

recommended operating conditions

|                                                                   |                          | SN54LS195A |     |     | SN74LS195A |     |      | UNIT |
|-------------------------------------------------------------------|--------------------------|------------|-----|-----|------------|-----|------|------|
|                                                                   |                          | MIN        | NOM | MAX | MIN        | NOM | MAX  |      |
| Supply voltage, V <sub>CC</sub>                                   |                          | 4.5        | 5   | 5.5 | 4.75       | 5   | 5.25 | V    |
| High-level output current, I <sub>OH</sub>                        |                          | -400       |     |     | -400       |     |      | μA   |
| Low-level output current, I <sub>OL</sub>                         |                          | 4          |     |     | 8          |     |      | mA   |
| Clock frequency, f <sub>clock</sub>                               |                          | 0          | 30  |     | 0          | 30  |      | MHz  |
| Width of clock or clear pulse, t <sub>w</sub> (clock)             |                          | 16         |     |     | 16         |     |      | ns   |
| Width of clear input pulse, t <sub>w</sub> (clear)                |                          | 12         |     |     | 12         |     |      | ns   |
| Setup time, t <sub>su</sub> (see Figure 1)                        | Shift/load               | 25         |     |     | 25         |     |      | ns   |
|                                                                   | Serial and parallel data | 15         |     |     | 15         |     |      |      |
|                                                                   | Clear inactive-state     | 25         |     |     | 25         |     |      |      |
| Shift/load release time, t <sub>release</sub> (see Figure 1)      |                          | 10         |     |     | 20         |     |      | ns   |
| Serial and parallel data hold time, t <sub>h</sub> (see Figure 1) |                          | 0          |     |     | 0          |     |      | ns   |
| Operating free-air temperature, T <sub>A</sub>                    |                          | -55 125    |     |     | 0 70       |     |      | °C   |

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER                                             | TEST CONDITIONS†                                                                                                  | SN54LS195A             |      |      | SN74LS195A |          |      | UNIT |
|-------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------|------------------------|------|------|------------|----------|------|------|
|                                                       |                                                                                                                   | MIN                    | TYP‡ | MAX  | MIN        | TYP‡     | MAX  |      |
| V <sub>IH</sub> High-level input voltage              |                                                                                                                   | 2                      |      |      | 2          |          |      | V    |
| V <sub>IL</sub> Low-level input voltage               |                                                                                                                   |                        |      | 0.7  |            |          | 0.8  | V    |
| V <sub>IK</sub> Input clamp voltage                   | V <sub>CC</sub> = MIN, I <sub>I</sub> = -18 mA                                                                    |                        |      | -1.5 |            |          | -1.5 | V    |
| V <sub>OH</sub> High-level output voltage             | V <sub>CC</sub> = MIN, V <sub>IH</sub> = 2 V,<br>V <sub>IL</sub> = V <sub>IL</sub> max, I <sub>OH</sub> = -400 μA | 2.5                    | 3.4  |      | 2.7        | 3.4      |      | V    |
| V <sub>OL</sub> Low-level output voltage              | V <sub>CC</sub> = MIN, V <sub>IH</sub> = 2 V,<br>V <sub>IL</sub> = V <sub>IL</sub> max                            | I <sub>OL</sub> = 4 mA |      | 0.25 | 0.4        | 0.25 0.4 |      | V    |
|                                                       |                                                                                                                   | I <sub>OL</sub> = 8 mA |      |      |            | 0.35 0.5 |      |      |
| I <sub>I</sub> Input current at maximum input voltage | V <sub>CC</sub> = MAX, V <sub>I</sub> = 7 V                                                                       |                        |      | 0.1  |            |          | 0.1  | mA   |
| I <sub>IH</sub> High-level input current              | V <sub>CC</sub> = MAX, V <sub>I</sub> = 2.7 V                                                                     |                        |      | 20   |            |          | 20   | μA   |
| I <sub>IL</sub> Low-level input current               | V <sub>CC</sub> = MAX, V <sub>I</sub> = 0.4 V                                                                     |                        |      | -0.4 |            |          | -0.4 | mA   |
| I <sub>OS</sub> Short-circuit output current §        | V <sub>CC</sub> = MAX                                                                                             | -20                    |      | -100 | -20        |          | -100 | mA   |
| I <sub>CC</sub> Supply current                        | V <sub>CC</sub> = MAX, See Note 2                                                                                 |                        | 14   | 21   |            | 14       | 21   | mA   |

† For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

‡ All typical values are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

§ Not more than one output should be shorted at a time, and duration of the short-circuit should not exceed one second.

NOTE 2: With all outputs open, shift/load grounded, and 4.5 V applied to the J, K, and data inputs,  $I_{CC}$  is measured by applying a momentary ground, followed by 4.5 V, to clear and then applying a momentary ground, followed by 4.5 V, to clock.

switching characteristics,  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^\circ\text{C}$

| PARAMETER                                                             | TEST CONDITIONS                                                        | MIN | TYP | MAX | UNIT |
|-----------------------------------------------------------------------|------------------------------------------------------------------------|-----|-----|-----|------|
| $f_{max}$ Maximum clock frequency                                     | $C_L = 15 \text{ pF}$ ,<br>$R_L = 2 \text{ k}\Omega$ ,<br>See Figure 1 | 30  | 39  |     | MHz  |
| $t_{PHL}$ Propagation delay time, high-to-low-level output from clear |                                                                        |     | 19  | 30  | ns   |
| $t_{PLH}$ Propagation delay time, low-to-high-level output from clock |                                                                        |     | 14  | 22  | ns   |
| $t_{PHL}$ Propagation delay time, high-to-low-level output from clock |                                                                        |     | 17  | 26  | ns   |

TEXAS  
INSTRUMENTS

POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

# SN54S195, SN74S195

## 4-BIT PARALLEL-ACCESS SHIFT REGISTERS

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

|                                                |                |
|------------------------------------------------|----------------|
| Supply voltage, $V_{CC}$ (see Note 1)          | 7 V            |
| Input voltage                                  | 5.5 V          |
| Operating free-air temperature range: SN54S195 | -55°C to 125°C |
| SN74S195                                       | 0°C to 70°C    |
| Storage temperature range                      | -65°C to 150°C |

NOTE 1: Voltage values are with respect to network ground terminal.

recommended operating conditions

|                                                          |                          | SN54S195 |     |     | SN74S195 |     |      | UNIT |
|----------------------------------------------------------|--------------------------|----------|-----|-----|----------|-----|------|------|
|                                                          |                          | MIN      | NOM | MAX | MIN      | NOM | MAX  |      |
| Supply voltage, $V_{CC}$                                 |                          | 4.5      | 5   | 5.5 | 4.75     | 5   | 5.25 | V    |
| High-level output current, $I_{OH}$                      |                          | -1       |     |     | -1       |     |      | mA   |
| Low-level output current, $I_{OL}$                       |                          | 20       |     |     | 20       |     |      | mA   |
| Clock frequency, $f_{clock}$                             |                          | 0        |     | 70  | 0        |     | 70   | MHz  |
| Width of clock input pulse, $t_w(clock)$                 |                          | 7        |     |     | 7        |     |      | ns   |
| Width of clear input pulse, $t_w(clear)$                 |                          | 12       |     |     | 12       |     |      | ns   |
| Setup time, $t_{su}$ (see Figure 1)                      | Shift/load               | 11       |     |     | 11       |     |      | ns   |
|                                                          | Serial and parallel data | 5        |     |     | 5        |     |      |      |
|                                                          | Clear inactive-state     | 9        |     |     | 9        |     |      |      |
| Shift/load release time, $t_{release}$ (see Figure 1)    |                          | 2        |     |     | 6        |     |      | ns   |
| Serial and parallel data hold time, $t_h$ (see Figure 1) |                          | 3        |     |     | 3        |     |      | ns   |
| Operating free-air temperature, $T_A$                    |                          | -55      |     | 125 | 0        |     | 70   | °C   |

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER       |                                        | TEST CONDITIONS†                                   |                                                   |          | MIN | TYP‡ | MAX  | UNIT |
|-----------------|----------------------------------------|----------------------------------------------------|---------------------------------------------------|----------|-----|------|------|------|
| V <sub>IH</sub> | High-level input voltage               |                                                    |                                                   |          | 2   |      |      | V    |
| V <sub>IL</sub> | Low-level input voltage                |                                                    |                                                   |          |     |      | 0.8  | V    |
| V <sub>IK</sub> | Input clamp voltage                    | V <sub>CC</sub> = MIN,                             | I <sub>I</sub> = -18 mA                           |          |     |      | -1.2 | V    |
| V <sub>OH</sub> | High-level output voltage              | V <sub>CC</sub> = MIN,<br>V <sub>IL</sub> = 0.8 V, | V <sub>IH</sub> = 2 V,                            | SN54S195 | 2.5 | 3.4  |      | V    |
|                 |                                        |                                                    | I <sub>OH</sub> = -1 mA                           | SN74S195 | 2.7 | 3.4  |      |      |
| V <sub>OL</sub> | Low-level output voltage               | V <sub>CC</sub> = MIN,<br>V <sub>IL</sub> = 0.8 V, | V <sub>IH</sub> = 2 V,<br>I <sub>OL</sub> = 20 mA |          |     |      | 0.5  | V    |
| I <sub>I</sub>  | Input current at maximum input voltage | V <sub>CC</sub> = MAX,                             | V <sub>I</sub> = 5.5 V                            |          |     |      | 1    | mA   |
| I <sub>IH</sub> | High-level input current               | V <sub>CC</sub> = MAX,                             | V <sub>I</sub> = 2.7 V                            |          |     |      | 50   | µA   |
| I <sub>IL</sub> | Low-level input current                | V <sub>CC</sub> = MAX,                             | V <sub>I</sub> = 0.5 V                            |          |     |      | -2   | mA   |
| I <sub>OS</sub> | Short-circuit output current §         | V <sub>CC</sub> = MAX                              |                                                   |          | -40 |      | -100 | mA   |
| I <sub>CC</sub> | Supply current                         | V <sub>CC</sub> = MAX,                             | See Note 2                                        | SN54S195 | 70  | 99   |      | mA   |
|                 |                                        |                                                    |                                                   | SN74S195 | 70  | 109  |      |      |

†For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

‡All typical values are at  $V_{CC} = 5 \text{ V}, T_A = 25^\circ\text{C}.$

§Not more than one output should be shorted at a time, and duration of the short-circuit should not exceed one second.

NOTE 2: With all outputs open, shift/load grounded, and 4.5 V applied to the J, K, and data inputs,  $I_{CC}$  is measured by applying a momentary ground, followed by 4.5 V, to clear, and then applying a momentary ground, followed by 4.5 V, to clock.

switching characteristics,  $V_{CC} = 5 \text{ V}, T_A = 25^\circ\text{C}$


| PARAMETER                                                             | TEST CONDITIONS                                               | MIN | TYP  | MAX  | UNIT |
|-----------------------------------------------------------------------|---------------------------------------------------------------|-----|------|------|------|
| $f_{max}$ Maximum clock frequency                                     | $C_L = 15 \text{ pF},$<br>$R_L = 280 \Omega,$<br>See Figure 1 | 70  | 105  |      | MHz  |
| $t_{PHL}$ Propagation delay time, high-to-low-level output from clear |                                                               |     | 12.5 | 18.5 | ns   |
| $t_{PLH}$ Propagation delay time, low-to-high-level output from clock |                                                               |     | 8    | 12   | ns   |
| $t_{PHL}$ Propagation delay time, high-to-low-level output from clock |                                                               |     | 11   | 16.5 | ns   |

TEXAS  
INSTRUMENTS


POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

**SN54195, SN54LS195A, SN54S195,  
SN74195, SN74LS195A, SN74S195  
4-BIT PARALLEL-ACCESS SHIFT REGISTERS**

**PARAMETER MEASUREMENT INFORMATION**



**LOAD FOR OUTPUT UNDER TEST**



- NOTES: A. The clock pulse generator has the following characteristics:  $Z_{out} \approx 50 \Omega$  and  $PRR \leq 1 \text{ MHz}$ . For '195,  $t_r \leq 7 \text{ ns}$  and  $t_f \leq 7 \text{ ns}$ . For 'LS195A,  $t_r \leq 15 \text{ ns}$  and  $t_f \leq 6 \text{ ns}$ . For 'S195,  $t_r = 2.5 \text{ ns}$  and  $t_f = 2.5 \text{ ns}$ . When testing  $f_{max}$ , vary the clock PRR.
- B.  $C_L$  includes probe and jig capacitance.
- C. All diodes are 1N3064 or equivalent.
- D. A clear pulse is applied prior to each test.
- E. For '195 and 'S195,  $V_{ref} = 1.5 \text{ V}$ ; for 'LS195A,  $V_{ref} = 1.3 \text{ V}$ .
- F. Propagation delay times ( $t_{PLH}$  and  $t_{PHL}$ ) are measured at  $t_{n+1}$ . Proper shifting of data is verified at  $t_{n+4}$  with a functional test.
- G. J and K inputs are tested the same as data A, B, C, and D inputs except that shift/load input remains high.
- H.  $t_n$  = bit time before clocking transition.  
 $t_{n+1}$  = bit time after one clocking transition.  
 $t_{n+4}$  = bit time after four clocking transitions.

**FIGURE 1—SWITCHING TIMES**

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655012 • DALLAS, TEXAS 75265



## IMPORTANT NOTICE

Texas Instruments (TI) reserves the right to make changes to its products or to discontinue any semiconductor product or service without notice, and advises its customers to obtain the latest version of relevant information to verify, before placing orders, that the information being relied on is current.

TI warrants performance of its semiconductor products and related software to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

Certain applications using semiconductor products may involve potential risks of death, personal injury, or severe property or environmental damage ("Critical Applications").

TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS.

Inclusion of TI products in such applications is understood to be fully at the risk of the customer. Use of TI products in such applications requires the written approval of an appropriate TI officer. Questions concerning potential risk applications should be directed to TI through a local SC sales office.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards should be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein. Nor does TI warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used.

## **IMPORTANT NOTICE**

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.