





- O - L - O - +
▲ LAMP INDICATOR
CONTACT CONFIGURATION



- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. OPERATING TEMP.: -20°C to 55°C
 4. ▲ DENOTES CRITICAL PARAMETER.
 5. ILLUMINATION COLOR: BLUE
 6. HARDWARE SUPPLIED: O-RING AND HEXNUT (NOT SHOWN)
 7. ILLUMINATION BASE RATING: 20mA 2.8V
 8. 2002/95/EC (ROHS) COMPLIANT



C	21422	REMOVE DUMMY SWITCH TERMINALS	3/31/14	EBP					
B	20885	ADD DUMMY SWITCH TERMINALS	11/15/12	EBP					
A	20713	RELEASE FOR PRODUCTION	8/21/12	rc	TITLE PV6F2PXSS-241				
REV	PCR NO	DESCRIPTION	DATE	BY	SCALE	DATE	DR	DWG	REV
					2:1	8/21/2012	rc	52-PV6F2PXSS241	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED