



LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					H	REVISED PER ECO-14-000068	25APR2014	NK	MM

- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 3

THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 4

POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



5 OBSOLETE	3.984	3.900	39	40	4-103185-0
	3.884	3.800	38	39	3-103185-9
	3.784	3.700	37	38	3-103185-8
	3.684	3.600	36	37	3-103185-7
5 OBSOLETE	3.584	3.500	35	36	3-103185-6
	3.484	3.400	34	35	3-103185-5
	3.384	3.300	33	34	3-103185-4
	3.284	3.200	32	33	3-103185-3
	3.184	3.100	31	32	3-103185-2
	3.084	3.000	30	31	3-103185-1
	2.984	2.900	29	30	3-103185-0
	2.884	2.800	28	29	2-103185-9
5 OBSOLETE	2.784	2.700	27	28	2-103185-8
	2.684	2.600	26	27	2-103185-7
5 OBSOLETE	2.584	2.500	25	26	2-103185-6
	2.484	2.400	24	25	2-103185-5
5 OBSOLETE	2.384	2.300	23	24	2-103185-4
	2.284	2.200	22	23	2-103185-3
5 OBSOLETE	2.184	2.100	21	22	2-103185-2
	2.084	2.000	20	21	2-103185-1
5 OBSOLETE	1.984	1.900	19	20	2-103185-0
	1.884	1.800	18	19	1-103185-9
	1.784	1.700	17	18	1-103185-8
	1.684	1.600	16	17	1-103185-7
5 SUPERCEDED BY 6-146280-5	1.584	1.500	15	16	1-103185-6
	1.484	1.400	14	15	1-103185-5
5 OBSOLETE	1.384	1.300	13	14	1-103185-4
	1.284	1.200	12	13	1-103185-3
5 SUPERCEDED BY 6-146280-0	1.184	1.100	11	12	1-103185-2
	1.084	1.000	10	11	1-103185-1
5 SUPERCEDED BY 6-146280-0	.984	.900	9	10	1-103185-0
	.884	.800	8	9	103185-9
	.784	.700	7	8	103185-8
	.684	.600	6	7	103185-7
	.584	.500	5	6	103185-6
	.484	.400	4	5	103185-5
	.384	.300	3	4	103185-4
	.284	.200	2	3	103185-3
	.184	.100	1	2	103185-2
	.084	—	—	1	103185-1
	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN H. MOLL	13OCT87	 TE Connectivity						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK T. CLARK	20OCT87							
	0 PLC	±	-	APVD T. CLARK	20OCT87	NAME	HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100CL, VERTICAL, WITH .025 SQUARE POSTS					
	1 PLC	±	-	PRODUCT SPEC								
	2 PLC	±	-	APPLICATION SPEC								
	3 PLC	±	.005									
	4 PLC	±	-									
ANGLES		±				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL: HOUSING: FLAME RETARDANT (UL94V-0) COLOR: BLACK POSTS: COPPER ALLOY		FINISH: POSTS: .00015 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000500 NICKEL		WEIGHT		A1		00779	C103185	-		
CUSTOMER DRAWING						SCALE		4:1	SHEET	1 of 1	REV	H