


Power Panel 6 W Potentiometer






FEATURES


- High power rating 6 W at 50 °C
- Cermet element
- Full sealing
- Mechanical strength
- Industrial and professional grade
- Tests according to CECC 41000 or IEC 60393-1
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT



DIMENSIONS in millimeters (inches) ± 0.5 mm (± 0.02 ')

PE 60 L

PE 60 F

OPTION D: DBAN SHAFT LOCKING




Available only with PE 60 L

OPTION L: PE 60 LPRP - WITH LOCATING PEG


Available on PE 60 L and PE 60 F

Panel sealed version
PE 60 M
OPTION E: Including locating peg (available only for PE 60 M)


Available only with bushing M10 x 0.75 and shafts Ø 6 mm

ELECTRICAL SPECIFICATIONS	
Resistive Element	Cermet
Electrical Travel	$270^\circ \pm 10^\circ$
Resistance Range	Linear Taper Logarithmic Taper
Standard Series e3	1 Ω to 1 $M\Omega$ 100 Ω to 2.2 $M\Omega$
Tolerance	Standard On Request
Taper	
Circuit Diagram	
Power Rating	Linear Logarithmic
	6 W at 50 $^\circ\text{C}$ 3 W at 50 $^\circ\text{C}$
Temperature Coefficient	See Standard Resistance Element Data
Limiting Element Voltage (Linear Taper)	350 V
Contact Resistance Variation (Linear Taper)	3 % R_n or 1 %
End Resistance (Typical)	0.5 Ω or 1 %
Dielectric Strength (RMS)	2500 V
Insulation Resistance (500 VDC)	10^5 $M\Omega$

MECHANICAL SPECIFICATIONS	
Mechanical Travel	$300^\circ \pm 5^\circ$
Operating Torque (Typical)	3 Ncm max.
End Stop Torque	70 Ncm max.
Tightening Torque of Mounting Nut	250 Ncm
Unit Weight	25 g to 35 g max.

ENVIRONMENTAL SPECIFICATIONS	
Temperature Range	- 55 $^\circ\text{C}$ to + 125 $^\circ\text{C}$
Climatic Category	55/125/56
Sealing	Fully sealed - Container IP67

OPTIONS	
Command Shaft	Length is measured from the mounting surface to the free end of the shaft. The screwdriver slot is aligned with the wiper within $\pm 10^\circ$. Special shafts are available, in accordance to drawings supplied by customers. We recommend that customers should not machine shafts, in order to avoid damage.
Panel Sealing: PE60M	The panel sealing device consists of a ring located in a groove on the potentiometer face. Sealing is obtained by tightening the ring against the panel when mounting the potentiometer.
Shaft Locking: DBAN	The shaft locking device consists of a tapered nut tightening a slotted notched washer against both bushing and shaft. DBAN tightening torque is 200 Ncm, shaft locking torque being 30 Ncm. DBAN is also available with all special types. This device is normally supplied in a separate bag. Can be pre-mounted on request.
Locating Peg: LPPR	Location is obtained by fitting a special washer on the potentiometer face. The peg can therefore be positioned at 90°, 180°, 270° and 360°.

PERFORMANCE		TYPICAL VALUES AND DRIFTS		
TESTS		CONDITIONS		OTHER
Electrical Endurance	1000 h at rated power 90'/30' - ambient temp. 25 °C		$\Delta R_T/R_T$ (%)	$\Delta R_{1-2}/R_{1-2}$ (%)
Climatic Sequence	Phase A dry heat 125 °C Phase B damp heat Phase C cold - 55 °C Phase D damp heat 5 cycles		$\pm 3\%$	-
Damp Heat, Staedy State	56 days		$\pm 0.5\%$	$\pm 1\%$
Change of Temperature	5 cycles, - 55 °C at + 125 °C		$\pm (0.5\% \pm 0.1\Omega)$	-
Mechanical Endurance	25 000 cycles		$\pm 3\%$	Contact res. variation: < 5 % Rn
Shock	50 g's at 11 ms, 3 successive shocks in 3 directions		$\pm 0.1\%$	$\pm 0.2\%$
Vibration	10 Hz to 55 Hz, 0.75 mm or 10 g's during 6 h		$\pm 0.1\%$	$\pm 0.2\%$

STANDARD RESISTANCE ELEMENT DATA				
STANDARD RESISTANCE VALUES	LINEAR TAPER			TYPICAL TCR - 55 °C + 125 °C
	MAX. POWER at 50 °C	MAX. WORKING VOLTAGE	MAX. CUR. THROUGH WIPER	
Ω	W	V	mA	ppm/°C
1	6	2.4	2449	
2	6	3.5	1732	
5	6	5.5	1095	± 500
10	6	7.7	775	
20	6	11.0	548	
25	6	12.2	490	
50	6	17.3	346	
100	6	24.5	245	
200	6	34.6	173.2	
250	6	38.7	154.9	
500	6	54.8	109.5	
1K	6	77.5	77.5	
2K	6	110	54.8	
2.5K	6	122	49.0	
5K	6	173	34.64	± 250
10K	6	245	24.49	
20K	6	346	17.32	
25K	4.90	350	14.00	
50K	2.45	350	7.00	
100K	1.23	350	3.50	
200K	0.61	350	1.75	
250K	0.49	350	1.40	
500K	0.25	350	0.70	
1M	0.12	350	0.35	

MARKING	
Printed:	
- Vishay trademark	
- Part number	
- Manufacturing date	

PACKAGING	
- In box of 5 pieces	

ORDERING INFORMATION (part number)														
P	E	6	0	L	0	F	G	W	2	0	4	M	A	
MODEL	BUSHING	OPTION	SHAFT		LEADS	OHMIC VALUE		TOLERANCE		TAPER		SPECIAL NUMBER		
PE60	M = Panel sealed L = STD F = 3/8"	0 = None For L bushing D = DBAN L = LPRP B = DBAN and LPRP For F bushing L = LPRP For M bushing E = Peg	For L bushing FG 16 mm, slotted FL 25 mm, slotted FR 50 mm, plain For F bushing GB 1/2", slotted GJ 7/8", slotted GR 2", slotted For M bushing FD = 13 mm, slotted FJ = 22 mm, slotted FP = 47 mm, plain		W: Wire	204 = 200 kΩ	± 20 % On request: ± 10 % ± 5 %		A = Linear L = Clockwise logarithmic F = Clockwise inverse logarithmic		(if applicable) Given by Vishay for custom design			

PART NUMBER DESCRIPTION (for information only)												
PE60	L	0	FG	W	200 kΩ	20 %	A	BO5				e4
MODEL	BUSHING	OPTION	SHAFT	LEADS	OHMIC VALUE	TOL.	TAPER	PACKAGING	SPECIAL	SPECIAL	SPECIAL	LEAD (Pb)-FREE

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.