

DURA-FLEX

- Resists Snagging
- Prevents Damage From UV, Gasoline, Engine Chemicals And Salt
- Resists Cut, Abrasion And Penetration
- Flexible & Economical General Purpose Protection
- Deflects High Pressure Hose Ruptures
- Custom Lengths Available
- Halogen Free

Put-Ups

Nominal Size	Part #	Wall Thickness	Maxi Coil	Bulk Spool	Shop Spool	Available Colors	Lbs/ 100'
0.71"	DFN0.71BK	.045"	300'	100'	50'	Black	2.57
0.83"	DFN0.83BK	.045"	300'	100'	50'	Black	2.58
0.92"	DFN0.92BK	.045"	300'	100'	50'	Black	3.22
1.00"	DFN1.00BK	.045"	300'	100'	50'	Black	3.66
1.13"	DFN1.13BK	.045"	300'	100'	50'	Black	4.18
1.25"	DFN1.25BK	.045"	300'	100'	50'	Black	4.49
1.34"	DFN1.34BK	.045"	300'	100'	50'	Black	4.84
1.59"	DFN1.59BK	.045"	300'	100'	50'	Black	5.37
1.75"	DFN1.75BK	.045"	300'	100'	50'	Black	6.13
2.07"	DFN2.07BK	.045"	300'	100'	50'	Black	7.26
2.38"	DFN2.38BK	.045"	300'	100'	50'	Black	8.28
2.54"	DFN2.54BK	.045"	300'	100'	50'	Black	8.98
2.86"	DFN2.86BK	.045"	300'	100'	50'	Black	9.89
3.34"	DFN3.34BK	.045"	300'	50'	25'	Black	11.59
3.66"	DFN3.66BK	.045"	300'	50'	25'	Black	12.25



Cut Cleanly
Scissors

Material

Nylon

Grade

DFN

Wall Thickness

.045"

Drawing Number

TF001DF-WD

Industrial Hose And Cable Protection For Harsh Environments


The tightly woven Nylon® makes DF the perfect solution for hose & cable protection. The .045 inch wall thickness will protect cables, hoses and ropes from weather, sunlight and abrasion damage.

When installed over uncoated cable or chains, DF will prevent scraping, chafing and contact damage to painted or other fragile surfaces. DF is resistant to chemicals, UV damage and rot, and is suitable for continuous outdoor use under all weather conditions.

The flexible sleeving cuts with a scissor and the tight construction slides easily over any application.

This is a non-expandable product. Be sure to match your application diameter accurately.

■ **Colors Available:**
Black (BK)



www.techflex.com

800.323.5140 • 973.300.9242 • fax: 973.300.9409
104 Demarest Road • Sparta, NJ 07871

ISO
6945

MSHA



DURA-FLEX



Abrasion Resistance
High

Abrasion Test Machine
Taber 5150

Abrasion Test Wheel
Calibrase H-18

Abrasion Test Load
500g

Room Temperature
80°F

Humidity
70%

Visible Wear And Some
Pulling Of Fibers
500 Test Cycles

Further Wear And Some
Pulling At Seam
550 Test Cycles

Material Wearing
Through At Seam
2,750 Test Cycles

Material Destroyed
3,500 Test Cycles

Pre-Test Weight
7,191.6 mg

Post-Test Weight
6,680.7 mg

Test End Loss Of Mass
Point Of Destruction
510.9 mg



Chemical Resistance

1=No Effect 4=More Affected
2=Little Effect 5=Severely Affected
3=Affected

Aromatic Solvents	1
Aliphatic Solvents	1
Chlorinated Solvents	1
Weak Bases	1
Salts	1
Strong Bases	2
Salt Water 0-S-1926	1
Hydraulic Fluid MIL-H-5606	1
Lube Oil MIL-L-7808	1
De-Icing Fluid MIL-A-8243	1
Strong Acids	5
Strong Oxidants	5
Esters/Keytones	1
UV Light	2
Petroleum	3
Fungus ASTM G-21	2
Halogen Free	Yes
RoHS	Yes

Melt Point
ASTM D-2117
410°F (210°C)

Maximum Continuous
Mil-I-23053
248°F (120°C)

Minimum Continuous
-49°F (-45°C)



PHYSICAL PROPERTIES

Monofilament Diameter	NA
ASTM D-204	
Recommended Cutting	Scissor
Colors	1
Wall Thickness	.045
Specific Gravity ASTM D-792	1.14
Moisture Absorption	2.7
% ASTM D-570	
Hard Vacuum Data ASTM E-595 at 10-5 torr	
TML	1.10
CVCM	.01
WVR	.69
Outgassing	High
Oxygen Index	22
ASTM D-2863	