





- 1 HOUSING MATERIAL: THERMOPLASTIC, COLOR: BLACK
- 2 CONTACT MATERIAL: COPPER ALLOY
- 3 FINISH:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-9063; BASED ON TELCORDIA DR-1217-CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
SOLDER TAILS AREA: TIN-LEAD PLATED.
- 4 SOLDER TAILS MUST FIT HOLE PATTERN AS SHOWN ON THE RECOMMENDED P.C. BOARD LAYOUT
- 5 HOUSINGS WITH CENTER MOUNTING IS RECOMMENDED FOR ASSEMBLIES HAVING 75 CONTACTS PER ROW OR MORE
- 6 SEE SHEET 2 FOR LOADING PATTERN AND P.C. BOARD LAYOUT

OBSELETE	137.16 [5.400]	54	140.31 [5.524]	151.13 [5.950]	158.75 [6.250]	69 [2.71]	532834-2
	137.16 [5.400]	54	140.31 [5.524]	151.13 [5.950]	158.75 [6.250]	107 [4.21]	532834-1
E	D	C	B	A	POSITION	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 23JUL2003	TE Connectivity			
DIMENSIONS: mm		CHK WL MILLHIMES 23JUL2003	NAME			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD WL MILLHIMES 23JUL2003	HDI, 3 ROW, RECEPTACLE ASSEMBLY, SPECIAL LOADING			
0 PLC ± -		PRODUCT SPEC	SIZE			
1 PLC ± -		APPLICATION SPEC	CAGE CODE			
2 PLC ± 0.13[.005]		—	DRAWING NO			
3 PLC ± -		—	RESTRICTED TO			
4 PLC ± -		—	A1 00779			
ANGLES		—	532834			
FINISH		WEIGHT	0			
MATERIAL		CUSTOMER DRAWING	SCALE 4:1			
1/2		3	SHEET 1 OF 2			
			REV G			



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM	23JUL2003	 TE Connectivity	
		CHK WL MILLHIMES	23JUL2003		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD WL MILLHIMES	23JUL2003	NAME HDI, 3 ROW, RECEPTACLE ASSEMBLY, SPECIAL LOADING	
		PRODUCT SPEC -			
	MATERIAL 	APPLICATION SPEC		SIZE A1	
		WEIGHT 0		CAGE CODE 00779	
		CUSTOMER DRAWING		SCALE 4:1	
				SHEET 2 OF 2	
				REV G	