



## VOIDLESS HERMETICALLY SEALED 500mW GLASS ZENER DIODES

Qualified per MIL-PRF-19500/533

Qualified Levels:  
JAN, JANTX, JANTXV  
and JANS

### DESCRIPTION

This Zener voltage regulator series is military qualified and is ideal for high-reliability applications where a failure cannot be tolerated. These industry-recognized 0.5 watt Zener voltage regulators are hermetically sealed with voidless-glass construction using an internal metallurgical bond. It includes Zener selections from 2.4 to 200 volts in standard 5% tolerances as well as 1% and 2% tolerances. They are also available in surface-mount packages. Microsemi also offers numerous other Zener products to meet higher and lower power ratings in both thru-hole and surface mount packages.

**Important:** For the latest information, visit our website <http://www.microsemi.com>.

### FEATURES

- JEDEC registered 1N6309 thru 1N6355 series.
- Voltage tolerances of 1%, 2% and 5% are available. (See [part nomenclature](#).)
- Voidless hermetically sealed glass package.
- Internal "Category 1" metallurgical bonds for 1N6321 thru 1N6355 and "Category III" for 1N6309 thru 1N6320.
- JAN, JANTX, JANTXV, and JANS reliability levels are available per MIL-PRF-19500/533.
- RoHS compliant versions available (commercial grade only).


### APPLICATIONS / BENEFITS

- Small DO-35 size package (or "D" Package).
- Regulates voltage over a broad operating current and temperature range.
- Extensive selection from 2.4 to 200 volts.
- Standard and tight voltage tolerances available.
- Extremely robust construction.
- Flexible axial-lead mounting terminals.
- Non-sensitive to ESD per MIL-STD-750 method 1020.
- Inherently radiation hard as described in Microsemi "[MicroNote 050](#)".

### MAXIMUM RATINGS

| Parameters/Test Conditions                                | Symbol              | Value       | Unit |
|-----------------------------------------------------------|---------------------|-------------|------|
| Junction and Storage Temperature                          | $T_J$ and $T_{STG}$ | -65 to +175 | °C   |
| Thermal Resistance Junction-to-Lead <sup>(1)</sup>        | $R_{\theta JL}$     | 150         | °C/W |
| 1N6309 – 1N6320                                           |                     | 95.5        |      |
| 1N6321 – 1N6355                                           |                     |             |      |
| Thermal Resistance Junction-to-Ambient <sup>(2)</sup>     | $R_{\theta JA}$     | 240         | °C/W |
| Steady-State Power Dissipation @ $T_L = 75^\circ\text{C}$ | $P_D$               | 0.5         | W    |
| Forward Voltage @ 1.0 A                                   | $V_F$               | 1.4         | V    |
| Solder Temperature @ 10 s                                 | $T_{SP}$            | 260         | °C   |

- Notes:**
1. At 3/8 inch (10 mm) from body. See [Figure 1](#) and [Figure 2](#) for derating.
  2.  $T_A = +55^\circ\text{C}$  before derating on printed circuit board (PCB), PCB = FR4 .0625 inch (1.59 mm) 1-layer 1-Oz Cu, horizontal, still air, pads = .092 inch (2.34 mm) diameter, strip = .030 inch (0.76 mm) x 1 inch (25.4 mm) long, axial lead length  $L \leq .187$  inch ( $\leq 4.75$  mm);  $R_{\theta JA}$  with a defined thermal resistance condition included is measured at  $I_Z =$  as defined in the characteristics and ratings table herein.



DO-35 or  
"D" Package

Also available in:

"B" SQ MELF package  
(surface mount)  
 [1N6309US – 1N6355DUS](#)


**MSC – Lawrence**  
6 Lake Street,  
Lawrence, MA 01841  
Tel: 1-800-446-1158 or  
(978) 620-2600  
Fax: (978) 689-0803

**MSC – Ireland**  
Gort Road Business Park,  
Ennis, Co. Clare, Ireland  
Tel: +353 (0) 65 6840044  
Fax: +353 (0) 65 6822298

**Website:**  
[www.microsemi.com](http://www.microsemi.com)

**MECHANICAL and PACKAGING**

- CASE: Hermetically sealed voidless hard glass with tungsten slugs.
- TERMINALS: Axial-leads are tin/lead (Sn/Pb) or RoHS compliant matte/tin (commercial grade only) over copper clad steel.
- MARKING: Body painted and part number.
- POLARITY: Cathode indicated by band.
- TAPE & REEL option: Standard per EIA-296. Consult factory for quantities.
- WEIGHT: 150 milligrams.
- See [Package Dimensions](#) on last page.

**PART NOMENCLATURE**

**SYMBOLS & DEFINITIONS**


| Symbol                | Definition                                                                                                                                                                                                                                      |
|-----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| $I_R$                 | Reverse Current: The maximum reverse (leakage) current that will flow at the specified voltage and temperature.                                                                                                                                 |
| $I_Z, I_{ZT}, I_{ZK}$ | Regulator Current: The dc regulator current ( $I_Z$ ), at a specified test point ( $I_{ZT}$ ), near breakdown knee ( $I_{ZK}$ ).                                                                                                                |
| $I_{ZM}$              | Maximum Regulator (Zener) Current: The maximum rated dc current for the specified power rating.                                                                                                                                                 |
| $I_{ZSM}$             | Maximum Zener Surge Current: The non-repetitive peak value of Zener surge current at a specified wave form.                                                                                                                                     |
| $V_F$                 | Maximum Forward Voltage: The maximum forward voltage the device will exhibit at a specified current.                                                                                                                                            |
| $V_{WM}$              | Working Peak Voltage: The maximum peak voltage that can be applied over the operating temperature range. This is also referred to as Standoff Voltage.                                                                                          |
| $V_Z$                 | Zener Voltage: The Zener voltage the device will exhibit at a specified current ( $I_Z$ ) in its breakdown region.                                                                                                                              |
| $Z_{ZT}$ or $Z_{ZK}$  | Dynamic Impedance: The small signal impedance of the diode when biased to operate in its breakdown region at a specified rms current modulation (typically 10% of $I_{ZT}$ or $I_{ZK}$ ) and superimposed on $I_{ZT}$ or $I_{ZK}$ respectively. |

**ELECTRICAL CHARACTERISTICS @ 25°C**


| TYPE<br>Note 1 | V <sub>Z2</sub><br>NOM.<br>+/-5%<br>@ I <sub>Z2</sub> | V <sub>Z1</sub><br>MIN.<br>@ I <sub>Z1</sub><br>250 µA | Test<br>Current<br>I <sub>Z2</sub> | Dynamic<br>Impedance<br>Z <sub>Z</sub> @ I <sub>Z2</sub> | Dynamic<br>Impedance<br>Z <sub>ZK</sub><br>@<br>250 µA | Max.<br>Current<br>I <sub>ZM</sub> | Voltage<br>Reg.<br>V <sub>Z(reg)</sub><br>(ΔV <sub>Z</sub> )<br>Note 2 | Surge<br>Current<br>8.3 ms<br>square<br>Wave<br>I <sub>ZSM</sub> | Reverse<br>Voltage<br>V <sub>R</sub> | Max.<br>Reverse<br>Current<br>I <sub>R1</sub> @ V <sub>R</sub><br>25 °C | Max.<br>Reverse<br>Current<br>I <sub>R2</sub> @ V <sub>R</sub><br>150 °C | Max.<br>Noise<br>Density<br>N <sub>D</sub><br>@ 250 µA<br>1 to 3 kHz | Max.<br>Temp.<br>Coeff. of<br>Zener<br>Voltage<br>α <sub>VZ</sub> |
|----------------|-------------------------------------------------------|--------------------------------------------------------|------------------------------------|----------------------------------------------------------|--------------------------------------------------------|------------------------------------|------------------------------------------------------------------------|------------------------------------------------------------------|--------------------------------------|-------------------------------------------------------------------------|--------------------------------------------------------------------------|----------------------------------------------------------------------|-------------------------------------------------------------------|
|                | Volts                                                 | Volts                                                  | mA                                 | ohms                                                     | ohms                                                   | mA                                 | Volts                                                                  | Amps                                                             | Volts                                | µA                                                                      | µA                                                                       | µV /Hz                                                               | %/°C                                                              |
| 1N6309         | 2.4                                                   | 1.1                                                    | 20                                 | 30                                                       | 1,200                                                  | 177                                | 1.50                                                                   | 2.50                                                             | 1.0                                  | 100                                                                     | 200                                                                      | 1                                                                    | -.085                                                             |
| 1N6310         | 2.7                                                   | 1.2                                                    | 20                                 | 30                                                       | 1,300                                                  | 157                                | 1.50                                                                   | 2.20                                                             | 1.0                                  | 60                                                                      | 150                                                                      | 1                                                                    | -.080                                                             |
| 1N6311         | 3.0                                                   | 1.3                                                    | 20                                 | 29                                                       | 1,400                                                  | 141                                | 1.50                                                                   | 2.00                                                             | 1.0                                  | 30                                                                      | 100                                                                      | 1                                                                    | -.075                                                             |
| 1N6312         | 3.3                                                   | 1.5                                                    | 20                                 | 27                                                       | 1,400                                                  | 128                                | 1.60                                                                   | 1.80                                                             | 1.0                                  | 5                                                                       | 20                                                                       | 1                                                                    | -.070                                                             |
| 1N6313         | 3.6                                                   | 1.8                                                    | 20                                 | 25                                                       | 1,400                                                  | 117                                | 1.60                                                                   | 1.65                                                             | 1.0                                  | 3                                                                       | 12                                                                       | 1                                                                    | -.065                                                             |
| 1N6314         | 3.9                                                   | 2.0                                                    | 20                                 | 23                                                       | 1,700                                                  | 108                                | 1.60                                                                   | 1.50                                                             | 1.0                                  | 2                                                                       | 12                                                                       | 1                                                                    | -.060                                                             |
| 1N6315         | 4.3                                                   | 2.4                                                    | 20                                 | 20                                                       | 1,700                                                  | 99                                 | 0.90                                                                   | 1.40                                                             | 1.0                                  | 2                                                                       | 12                                                                       | 1                                                                    | -.045<br>+.020                                                    |
| 1N6316         | 4.7                                                   | 2.8                                                    | 20                                 | 17                                                       | 1,500                                                  | 90                                 | 0.50                                                                   | 1.27                                                             | 1.5                                  | 5                                                                       | 12                                                                       | 1                                                                    | -.028<br>+.032                                                    |
| 1N6317         | 5.1                                                   | 3.3                                                    | 20                                 | 14                                                       | 1,300                                                  | 83                                 | 0.40                                                                   | 1.17                                                             | 2.0                                  | 5                                                                       | 12                                                                       | 1                                                                    | -.020<br>+.035                                                    |
| 1N6318         | 5.6                                                   | 4.3                                                    | 20                                 | 8                                                        | 1,200                                                  | 76                                 | 0.40                                                                   | 1.10                                                             | 2.5                                  | 5                                                                       | 10                                                                       | 2                                                                    | +.050                                                             |
| 1N6319         | 6.2                                                   | 5.2                                                    | 20                                 | 3                                                        | 800                                                    | 68                                 | 0.30                                                                   | 0.97                                                             | 3.5                                  | 5                                                                       | 10                                                                       | 5                                                                    | +.060                                                             |
| 1N6320         | 6.8                                                   | 6.0                                                    | 20                                 | 3                                                        | 400                                                    | 63                                 | 0.35                                                                   | 1.23                                                             | 4.0                                  | 2                                                                       | 50                                                                       | 5                                                                    | +.062                                                             |
| 1N6321         | 7.5                                                   | 6.6                                                    | 20                                 | 4                                                        | 400                                                    | 57                                 | 0.40                                                                   | 1.16                                                             | 5.0                                  | 2                                                                       | 30                                                                       | 5                                                                    | +.068                                                             |
| 1N6322         | 8.2                                                   | 7.5                                                    | 20                                 | 5                                                        | 400                                                    | 52                                 | 0.40                                                                   | 1.07                                                             | 6.0                                  | 1                                                                       | 10                                                                       | 20                                                                   | +.075                                                             |
| 1N6323         | 9.1                                                   | 8.4                                                    | 20                                 | 6                                                        | 500                                                    | 47                                 | 0.50                                                                   | 0.97                                                             | 7.0                                  | 1                                                                       | 10                                                                       | 40                                                                   | +.076                                                             |
| 1N6324         | 10.0                                                  | 9.1                                                    | 20                                 | 6                                                        | 500                                                    | 43                                 | 0.50                                                                   | 0.89                                                             | 8.0                                  | 1                                                                       | 10                                                                       | 80                                                                   | +.079                                                             |
| 1N6325         | 11.0                                                  | 10.0                                                   | 20                                 | 7                                                        | 550                                                    | 39                                 | 0.50                                                                   | 0.83                                                             | 8.5                                  | 1                                                                       | 10                                                                       | 100                                                                  | +.082                                                             |
| 1N6326         | 12.0                                                  | 11.0                                                   | 20                                 | 7                                                        | 550                                                    | 35                                 | 0.55                                                                   | 0.77                                                             | 9.0                                  | 1                                                                       | 10                                                                       | 100                                                                  | +.083                                                             |
| 1N6327         | 13.0                                                  | 11.9                                                   | 9.5                                | 8                                                        | 550                                                    | 33                                 | 0.55                                                                   | 0.71                                                             | 9.9                                  | 0.05                                                                    | 10                                                                       | 100                                                                  | +.083                                                             |
| 1N6328         | 15.0                                                  | 13.8                                                   | 8.5                                | 10                                                       | 600                                                    | 28                                 | 0.70                                                                   | 0.62                                                             | 11.0                                 | 0.05                                                                    | 10                                                                       | 100                                                                  | +.084                                                             |
| 1N6329         | 16.0                                                  | 14.7                                                   | 7.8                                | 12                                                       | 600                                                    | 27                                 | 0.75                                                                   | 0.58                                                             | 12.0                                 | 0.05                                                                    | 10                                                                       | 100                                                                  | +.084                                                             |
| 1N6330         | 18.0                                                  | 16.6                                                   | 7.0                                | 14                                                       | 600                                                    | 24                                 | 0.85                                                                   | 0.52                                                             | 14.0                                 | 0.05                                                                    | 10                                                                       | 100                                                                  | +.085                                                             |
| 1N6331         | 20.0                                                  | 18.5                                                   | 6.2                                | 18                                                       | 500                                                    | 21                                 | 0.95                                                                   | 0.47                                                             | 15.0                                 | 0.05                                                                    | 10                                                                       | 100                                                                  | +.086                                                             |
| 1N6332         | 22.0                                                  | 20.4                                                   | 5.6                                | 20                                                       | 500                                                    | 19                                 | 1.05                                                                   | 0.43                                                             | 17.0                                 | 0.05                                                                    | 10                                                                       | 100                                                                  | +.087                                                             |
| 1N6333         | 24.0                                                  | 22.3                                                   | 5.2                                | 24                                                       | 500                                                    | 18                                 | 1.15                                                                   | 0.39                                                             | 18.0                                 | 0.05                                                                    | 10                                                                       | 100                                                                  | +.088                                                             |
| 1N6334         | 27.0                                                  | 25.2                                                   | 4.6                                | 27                                                       | 500                                                    | 16                                 | 1.30                                                                   | 0.35                                                             | 21.0                                 | 0.05                                                                    | 10                                                                       | 100                                                                  | +.090                                                             |
| 1N6335         | 30.0                                                  | 28.0                                                   | 4.2                                | 32                                                       | 500                                                    | 14                                 | 1.45                                                                   | 0.31                                                             | 23.0                                 | 0.05                                                                    | 10                                                                       | 100                                                                  | +.091                                                             |
| 1N6336         | 33.0                                                  | 30.9                                                   | 3.8                                | 40                                                       | 600                                                    | 13                                 | 1.60                                                                   | 0.28                                                             | 25.0                                 | 0.05                                                                    | 10                                                                       | 100                                                                  | +.092                                                             |
| 1N6337         | 36.0                                                  | 33.7                                                   | 3.4                                | 50                                                       | 600                                                    | 12                                 | 1.75                                                                   | 0.260                                                            | 27.0                                 | 0.05                                                                    | 10                                                                       | 100                                                                  | +.093                                                             |
| 1N6338         | 39.0                                                  | 36.6                                                   | 3.2                                | 55                                                       | 700                                                    | 11                                 | 1.90                                                                   | 0.240                                                            | 30                                   | 0.05                                                                    | 10                                                                       | 100                                                                  | +.094                                                             |
| 1N6339         | 43.0                                                  | 40.4                                                   | 3.0                                | 65                                                       | 800                                                    | 9.9                                | 2.10                                                                   | 0.220                                                            | 33                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.095                                                             |
| 1N6340         | 47.0                                                  | 44.2                                                   | 2.7                                | 75                                                       | 900                                                    | 9.0                                | 2.25                                                                   | 0.200                                                            | 36                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.095                                                             |
| 1N6341         | 51.0                                                  | 48.0                                                   | 2.5                                | 85                                                       | 1,000                                                  | 8.3                                | 2.50                                                                   | 0.180                                                            | 39                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.096                                                             |
| 1N6342         | 56.0                                                  | 52.7                                                   | 2.2                                | 100                                                      | 1,200                                                  | 7.6                                | 2.70                                                                   | 0.170                                                            | 43                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.097                                                             |
| 1N6343         | 62.0                                                  | 58.4                                                   | 2.0                                | 125                                                      | 1,300                                                  | 6.8                                | 2.90                                                                   | 0.150                                                            | 47                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.099                                                             |
| 1N6344         | 68.0                                                  | 64.1                                                   | 1.8                                | 155                                                      | 1,500                                                  | 6.3                                | 3.20                                                                   | 0.130                                                            | 52                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.101                                                             |
| 1N6345         | 75.0                                                  | 70.8                                                   | 1.7                                | 180                                                      | 1,600                                                  | 5.7                                | 3.40                                                                   | 0.125                                                            | 56                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.103                                                             |
| 1N6346         | 82.0                                                  | 77.4                                                   | 1.5                                | 220                                                      | 1,800                                                  | 5.2                                | 3.80                                                                   | 0.115                                                            | 62                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.105                                                             |
| 1N6347         | 91.0                                                  | 86.0                                                   | 1.4                                | 270                                                      | 2,100                                                  | 4.7                                | 4.20                                                                   | 0.100                                                            | 69                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.108                                                             |
| 1N6348         | 100.0                                                 | 94.5                                                   | 1.3                                | 340                                                      | 2,400                                                  | 4.3                                | 4.40                                                                   | 0.095                                                            | 76                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.110                                                             |
| 1N6349         | 110.0                                                 | 104.0                                                  | 1.1                                | 500                                                      | 2,800                                                  | 3.9                                | 4.80                                                                   | 0.085                                                            | 84                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.110                                                             |
| 1N6350         | 120.0                                                 | 113.0                                                  | 1.0                                | 600                                                      | 3,200                                                  | 3.5                                | 5.20                                                                   | 0.080                                                            | 91                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.110                                                             |
| 1N6351         | 130.0                                                 | 122                                                    | 0.95                               | 850                                                      | 4,100                                                  | 3.3                                | 5.60                                                                   | 0.070                                                            | 99                                   | 0.05                                                                    | 10                                                                       | 80                                                                   | +.110                                                             |
| 1N6352         | 150.0                                                 | 141                                                    | 0.85                               | 1,000                                                    | 4,500                                                  | 2.8                                | 7.00                                                                   | 0.065                                                            | 114                                  | 0.05                                                                    | 10                                                                       | 80                                                                   | +.110                                                             |
| 1N6353         | 160.0                                                 | 151                                                    | 0.80                               | 1,200                                                    | 5,000                                                  | 2.7                                | 7.50                                                                   | 0.060                                                            | 122                                  | 0.05                                                                    | 10                                                                       | 80                                                                   | +.110                                                             |
| 1N6354         | 180.0                                                 | 170                                                    | 0.68                               | 1,500                                                    | 5,600                                                  | 2.4                                | 9.00                                                                   | 0.050                                                            | 137                                  | 0.05                                                                    | 10                                                                       | 80                                                                   | +.110                                                             |
| 1N6355         | 200.0                                                 | 189                                                    | 0.65                               | 1,800                                                    | 6,500                                                  | 2.1                                | 12.00                                                                  | 0.045                                                            | 152                                  | 0.05                                                                    | 10                                                                       | 80                                                                   | +.110                                                             |

**NOTES:**


- Standard voltage tolerance is 5 percent. Tighter tolerances are available in plus/minus 1 and 2 percent voltage tolerances. (See [part nomenclature](#).)
- Voltage regulation V<sub>Z(reg)</sub> is the measured voltage change at thermal equilibrium between the current of 10% and 50% of maximum Zener current I<sub>ZM</sub> when the lead temperature is maintained at 25 °C = +8 °C, -2 °C.

**GRAPHS**



**FIGURE 1 - (1N6309 – 1N6320)**  
 $T_L$  Temperature-Power Derating Curve  
 $R_{\theta JL}$  3/8 inch = 150 °C/W (dc operation)



**FIGURE 2 - (1N6321 – 1N6355)**  
 $T_L$  Temperature-Power Derating Curve  
 $R_{\theta JL}$  3/8 inch = 95.5 °C/W (dc operation)

**GRAPHS (continued)**


**FIGURE 3**  
Temperature-Power Derating Curve  
 $R_{\theta JA} = 240\text{ }^{\circ}\text{C/W}$  (dc operation)

**PACKAGE DIMENSIONS**

**NOTE:**

1. Dimensions are in inches.
2. Millimeters are given for general information only.
3. Lead diameter not controlled in this zone to allow for flash.  
Lead finish build-up and minor irregularities other than slugs.
4. In accordance with ASME Y14.5M, diameters are equivalent to  $\Phi$ x symbology.
5. The BL dimension shall include the entire body including slugs.

| Ltr | DIMENSIONS |       |             |       | Notes |
|-----|------------|-------|-------------|-------|-------|
|     | INCH       |       | MILLIMETERS |       |       |
|     | Min        | Max   | Min         | Max   |       |
| BD  | .060       | .090  | 1.52        | 2.29  |       |
| BL  | .120       | .200  | 3.05        | 5.08  | 5     |
| LD  | .018       | .022  | 0.46        | 0.56  |       |
| LL  | 1.000      | 1.500 | 25.40       | 38.10 |       |
| LL1 |            | .050  |             | 1.27  | 3     |