

# Octal 3-State Noninverting Transparent Latch

## MC74HC573A, MC74HCT573A

The MC74HC573A / MC74HCT573A is identical in pinout to the LS573. The MC74HC573A device inputs are compatible with standard CMOS outputs; with pullup resistors, they are compatible with LSTTL outputs. The MC74HCT573A may be used as a level converter for interfacing TTL or NMOS outputs to High-Speed CMOS inputs.

These latches appear transparent to data (i.e., the outputs change asynchronously) when Latch Enable is high. When Latch Enable goes low, data meeting the setup and hold time becomes latched.

The HC573A/HCT573A is identical in function to the HC373A/HCT373A but has the data inputs on the opposite side of the package from the outputs to facilitate PC board layout.

### Features

- Output Drive Capability: 15 LSTTL Loads
- Outputs Directly Interface to CMOS, NMOS, and TTL
- Operating Voltage Range:  
2.0 to 6.0 V (HC), 4.5 to 5.5 V (HCT)
- Low Input Current: 1  $\mu$ A
- High Noise Immunity Characteristic of CMOS Devices
- In Compliance with the Requirements Defined by JEDEC Standard No. 7 A
- Chip Complexity: 234 FETs or 58.5 Equivalent Gates
- -Q Suffix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant





Figure 1. Logic Diagram




SOIC-20  
DW SUFFIX  
CASE 751D



TSSOP-20  
DT SUFFIX  
CASE 948E

### MARKING DIAGRAMS



SOIC-20

TSSOP-20

XXXXXXXX = Specific Device Code

A = Assembly Location

WL, L = Wafer Lot


YY, Y = Year

WW, W = Work Week

G or ■ = Pb-Free Package

(Note: Microdot may be in either location)

### PIN ASSIGNMENT



### FUNCTION TABLE

| Inputs        |              |   | Output    |
|---------------|--------------|---|-----------|
| Output Enable | Latch Enable | D | Q         |
| L             | H            | H | H         |
| L             | H            | L | L         |
| L             | L            | X | No Change |
| H             | X            | X | Z         |

X = Don't Care

Z = High Impedance

### ORDERING INFORMATION

See detailed ordering and shipping information on page 8 of this data sheet.

# MC74HC573A, MC74HCT573A

## MAXIMUM RATINGS

| Symbol        | Parameter                                                    | Value                                    | Unit                              |
|---------------|--------------------------------------------------------------|------------------------------------------|-----------------------------------|
| $V_{CC}$      | DC Supply Voltage                                            | -0.5 to +6.5                             | V                                 |
| $V_{IN}$      | DC Input Voltage                                             | -0.5 to $V_{CC} + 0.5$                   | V                                 |
| $V_{OUT}$     | DC Output Voltage                                            | -0.5 to $V_{CC} + 0.5$                   | V                                 |
| $I_{IN}$      | DC Input Current, per Pin                                    | $\pm 20$                                 | mA                                |
| $I_{OUT}$     | DC Output Current, per Pin                                   | $\pm 35$                                 | mA                                |
| $I_{CC}$      | DC Supply Current, $V_{CC}$ and GND Pins                     | $\pm 75$                                 | mA                                |
| $I_{IK}$      | Input Clamp Current ( $V_{IN} < 0$ or $V_{IN} > V_{CC}$ )    | $\pm 20$                                 | mA                                |
| $I_{OK}$      | Output Clamp Current ( $V_{OUT} < 0$ or $V_{OUT} > V_{CC}$ ) | $\pm 20$                                 | mA                                |
| $T_{STG}$     | Storage Temperature                                          | -65 to +150                              | °C                                |
| $T_L$         | Lead Temperature, 1 mm from Case for 10 Seconds              | 260                                      | °C                                |
| $T_J$         | Junction Temperature Under Bias                              | $\pm 150$                                | °C                                |
| $\theta_{JA}$ | Thermal Resistance (Note 1)                                  | SOIC-20W<br>WQFN20<br>QFN20<br>TSSOP-20  | 96<br>99<br>111<br>150<br>°C/W    |
| $P_D$         | Power Dissipation in Still Air at 25°C                       | SOIC-20W<br>WQFN20<br>QFN20<br>TSSOP-20  | 1302<br>1256<br>1127<br>833<br>mW |
| MSL           | Moisture Sensitivity                                         | SOIC-20W<br>All Other Packages           | Level 3<br>Level 1<br>-           |
| $F_R$         | Flammability Rating                                          | Oxygen Index: 28 to 34                   | UL 94 V-0 @<br>0.125 in<br>-      |
| $V_{ESD}$     | ESD Withstand Voltage (Note 2)                               | Human Body Model<br>Charged Device Model | >2000<br>N/A<br>V                 |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Measured with minimum pad spacing on an FR4 board, using 76 mm-by-114 mm, 2-ounce copper trace no air flow per JESD51-7.
2. HBM tested to EIA / JESD22-A114-A. CDM tested to JESD22-C101-A. JEDEC recommends that ESD qualification to EIA/JESD22-A115A (Machine Model) be discontinued.

## RECOMMENDED OPERATING CONDITIONS

| Symbol | Parameter | Min | Max | Unit |
|--------|-----------|-----|-----|------|
|--------|-----------|-----|-----|------|

### MC74HC

|                   |                                           |                                                                               |             |                          |
|-------------------|-------------------------------------------|-------------------------------------------------------------------------------|-------------|--------------------------|
| $V_{CC}$          | DC Supply Voltage                         | 2.0                                                                           | 6.0         | V                        |
| $V_{IN}, V_{OUT}$ | DC Input Voltage, Output Voltage (Note 3) | 0                                                                             | $V_{CC}$    | V                        |
| $T_A$             | Operating Free-Air Temperature            | -55                                                                           | +125        | °C                       |
| $t_r, t_f$        | Input Rise or Fall Time                   | $V_{CC} = 2.0\text{ V}$<br>$V_{CC} = 4.5\text{ V}$<br>$V_{CC} = 6.0\text{ V}$ | 0<br>0<br>0 | 1000<br>500<br>400<br>ns |

### MC74HCT

|                   |                                           |     |          |    |
|-------------------|-------------------------------------------|-----|----------|----|
| $V_{CC}$          | DC Supply Voltage                         | 4.5 | 5.5      | V  |
| $V_{IN}, V_{OUT}$ | DC Input Voltage, Output Voltage (Note 3) | 0   | $V_{CC}$ | V  |
| $T_A$             | Operating Free-Air Temperature            | -55 | +125     | °C |
| $t_r, t_f$        | Input Rise or Fall Time                   | 0   | 500      | ns |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

3. Unused inputs must always be tied to an appropriate logic voltage level (e.g., either GND or  $V_{CC}$ ). Unused outputs must be left open.

# MC74HC573A, MC74HCT573A

## DC ELECTRICAL CHARACTERISTICS (MC74HC573A)

| Symbol          | Parameter                                      | Test Conditions                                                                                                                  | V <sub>CC</sub><br>V     | Guaranteed Limit          |                           |                           | Unit |
|-----------------|------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|--------------------------|---------------------------|---------------------------|---------------------------|------|
|                 |                                                |                                                                                                                                  |                          | -55 to<br>25°C            | ≤ 85°C                    | ≤ 125°C                   |      |
| V <sub>IH</sub> | Minimum High-Level Input Voltage               | V <sub>OUT</sub> = 0.1 V or V <sub>CC</sub> - 0.1 V<br> I <sub>OUT</sub>   ≤ 20 μA                                               | 2.0<br>3.0<br>4.5<br>6.0 | 1.5<br>2.1<br>3.15<br>4.2 | 1.5<br>2.1<br>3.15<br>4.2 | 1.5<br>2.1<br>3.15<br>4.2 | V    |
| V <sub>IL</sub> | Maximum Low-Level Input Voltage                | V <sub>OUT</sub> = 0.1 V or V <sub>CC</sub> - 0.1 V<br> I <sub>OUT</sub>   ≤ 20 μA                                               | 2.0<br>3.0<br>4.5<br>6.0 | 0.5<br>0.9<br>1.35<br>1.8 | 0.5<br>0.9<br>1.35<br>1.8 | 0.5<br>0.9<br>1.35<br>1.8 | V    |
| V <sub>OH</sub> | Minimum High-Level Output Voltage              | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                                                             |                          |                           |                           |                           | V    |
|                 |                                                | I <sub>OUT</sub>   ≤ 20 μA                                                                                                       | 2.0<br>4.5<br>6.0        | 1.9<br>4.4<br>5.9         | 1.9<br>4.4<br>5.9         | 1.9<br>4.4<br>5.9         |      |
|                 |                                                | I <sub>OUT</sub>   ≤ 2.4 mA<br> I <sub>OUT</sub>   ≤ 6.0 mA<br> I <sub>OUT</sub>   ≤ 7.8 mA                                      | 3.0<br>4.5<br>6.0        | 2.48<br>3.98<br>5.48      | 2.34<br>3.84<br>5.34      | 2.2<br>3.7<br>5.2         |      |
|                 |                                                |                                                                                                                                  |                          |                           |                           |                           |      |
| V <sub>OL</sub> | Minimum Low-Level Output Voltage               | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                                                             |                          |                           |                           |                           | V    |
|                 |                                                | I <sub>OUT</sub>   ≤ 20 μA                                                                                                       | 2.0<br>4.5<br>6.0        | 0.1<br>0.1<br>0.1         | 0.1<br>0.1<br>0.1         | 0.1<br>0.1<br>0.1         |      |
|                 |                                                | I <sub>OUT</sub>   ≤ 2.4 mA<br> I <sub>OUT</sub>   ≤ 6.0 mA<br> I <sub>OUT</sub>   ≤ 7.8 mA                                      | 3.0<br>4.5<br>6.0        | 0.26<br>0.26<br>0.26      | 0.33<br>0.33<br>0.33      | 0.4<br>0.4<br>0.4         |      |
|                 |                                                |                                                                                                                                  |                          |                           |                           |                           |      |
| I <sub>IN</sub> | Maximum Input Leakage Current                  | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                         | 6.0                      | ±0.1                      | ±1.0                      | ±1.0                      | μA   |
| I <sub>OZ</sub> | Maximum Three-State Leakage Current            | Output in High Impedance;<br>V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ;<br>V <sub>OUT</sub> = V <sub>CC</sub> or GND | 6.0                      | ±0.5                      | ±5.0                      | ±10.0                     | μA   |
| I <sub>CC</sub> | Maximum Quiescent Supply Current (per Package) | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                         | 6.0                      | 4.0                       | 40                        | 160                       | μA   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

# MC74HC573A, MC74HCT573A

## AC ELECTRICAL CHARACTERISTICS (MC74HC573A) (See Figures 2 and 3)

| Symbol                                 | Parameter                                                                  | V <sub>CC</sub><br>V | Guaranteed Limit |        |         | Unit |
|----------------------------------------|----------------------------------------------------------------------------|----------------------|------------------|--------|---------|------|
|                                        |                                                                            |                      | –55 to<br>25°C   | ≤ 85°C | ≤ 125°C |      |
| t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | Maximum Propagation Delay, D to Q                                          | 2.0                  | 150              | 190    | 225     | ns   |
|                                        |                                                                            | 3.0                  | 100              | 140    | 180     |      |
|                                        |                                                                            | 4.5                  | 30               | 38     | 45      |      |
|                                        |                                                                            | 6.0                  | 26               | 33     | 38      |      |
| t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | Maximum Propagation Delay, Latch Enable to Q                               | 2.0                  | 160              | 200    | 240     | ns   |
|                                        |                                                                            | 3.0                  | 105              | 145    | 190     |      |
|                                        |                                                                            | 4.5                  | 32               | 40     | 48      |      |
|                                        |                                                                            | 6.0                  | 27               | 34     | 41      |      |
| t <sub>PLZ</sub> ,<br>t <sub>PHZ</sub> | Maximum Propagation Delay, Output Enable to Q                              | 2.0                  | 150              | 190    | 225     | ns   |
|                                        |                                                                            | 3.0                  | 100              | 140    | 180     |      |
|                                        |                                                                            | 4.5                  | 30               | 38     | 45      |      |
|                                        |                                                                            | 6.0                  | 26               | 33     | 38      |      |
| t <sub>PZL</sub> ,<br>t <sub>PZH</sub> | Maximum Propagation Delay, Output Enable to Q                              | 2.0                  | 150              | 190    | 225     | ns   |
|                                        |                                                                            | 3.0                  | 100              | 140    | 180     |      |
|                                        |                                                                            | 4.5                  | 30               | 38     | 45      |      |
|                                        |                                                                            | 6.0                  | 26               | 33     | 38      |      |
| t <sub>TLH</sub> ,<br>t <sub>THL</sub> | Maximum Output Transition Time, Any Output                                 | 2.0                  | 60               | 75     | 90      | ns   |
|                                        |                                                                            | 3.0                  | 23               | 27     | 32      |      |
|                                        |                                                                            | 4.5                  | 12               | 15     | 18      |      |
|                                        |                                                                            | 6.0                  | 10               | 13     | 15      |      |
| C <sub>IN</sub>                        | Maximum Input Capacitance                                                  | –                    | 10               | 10     | 10      | pF   |
| C <sub>OUT</sub>                       | Maximum Three-State Output Capacitance<br>(Output in High Impedance State) | –                    | 15               | 15     | 15      | pF   |

| C <sub>PD</sub> | Power Dissipation Capacitance (Per Enabled Output) (Note 4) | 5.0 | Typical @ 25°C | pF |
|-----------------|-------------------------------------------------------------|-----|----------------|----|
|                 |                                                             |     | 23             |    |

4. Used to determine the no-load dynamic power consumption:  $P_D = C_{PD} \times V_{CC}^2 \times f + I_{CC} \times V_{CC}$ .

## TIMING REQUIREMENTS (MC74HC573A) (See Figures 2 and 3)

| Symbol                          | Parameter                             | V <sub>CC</sub><br>(V) | Guaranteed Limit |        |         | Unit |
|---------------------------------|---------------------------------------|------------------------|------------------|--------|---------|------|
|                                 |                                       |                        | –55 to<br>25°C   | ≤ 85°C | ≤ 125°C |      |
| t <sub>SU</sub>                 | Minimum Setup Time, D to Latch Enable | 2.0                    | 50               | 65     | 75      | ns   |
|                                 |                                       | 3.0                    | 40               | 50     | 60      |      |
|                                 |                                       | 4.5                    | 10               | 13     | 15      |      |
|                                 |                                       | 6.0                    | 9.0              | 11     | 13      |      |
| t <sub>H</sub>                  | Minimum Hold Time, Latch Enable to D  | 2.0                    | 5.0              | 5.0    | 5.0     | ns   |
|                                 |                                       | 3.0                    | 5.0              | 5.0    | 5.0     |      |
|                                 |                                       | 4.5                    | 5.0              | 5.0    | 5.0     |      |
|                                 |                                       | 6.0                    | 5.0              | 5.0    | 5.0     |      |
| t <sub>W</sub>                  | Minimum Pulse Width, Latch Enable     | 2.0                    | 75               | 95     | 110     | ns   |
|                                 |                                       | 3.0                    | 60               | 80     | 90      |      |
|                                 |                                       | 4.5                    | 15               | 19     | 22      |      |
|                                 |                                       | 6.0                    | 13               | 16     | 19      |      |
| t <sub>r</sub> , t <sub>f</sub> | Maximum Input Rise and Fall Times     | 2.0                    | 1000             | 1000   | 1000    | ns   |
|                                 |                                       | 3.0                    | 800              | 800    | 800     |      |
|                                 |                                       | 4.5                    | 500              | 500    | 500     |      |
|                                 |                                       | 6.0                    | 400              | 400    | 400     |      |

# MC74HC573A, MC74HCT573A

## DC ELECTRICAL CHARACTERISTICS (MC74HCT573A)

| Symbol          | Parameter                                      | Test Conditions                                                                                                                  | V <sub>CC</sub><br>V | Guaranteed Limit |            |            | Unit |
|-----------------|------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|----------------------|------------------|------------|------------|------|
|                 |                                                |                                                                                                                                  |                      | -55 to<br>25°C   | ≤ 85°C     | ≤ 125°C    |      |
| V <sub>IH</sub> | Minimum High-Level Input Voltage               | V <sub>OUT</sub> = 0.1 V or V <sub>CC</sub> -0.1 V;<br> I <sub>OUT</sub>   ≤ 20 μA                                               | 4.5<br>5.5           | 2.0<br>2.0       | 2.0<br>2.0 | 2.0<br>2.0 | V    |
| V <sub>IL</sub> | Maximum Low-Level Input Voltage                | V <sub>OUT</sub> = 0.1 V or V <sub>CC</sub> -0.1 V;<br> I <sub>OUT</sub>   ≤ 20 μA                                               | 4.5<br>5.5           | 0.8<br>0.8       | 0.8<br>0.8 | 0.8<br>0.8 | V    |
| V <sub>OH</sub> | Minimum High-Level Output Voltage              | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ;                                                                           |                      |                  |            |            | V    |
|                 |                                                | I <sub>OUT</sub>   ≤ 20 μA                                                                                                       | 4.5<br>5.5           | 4.4<br>5.4       | 4.4<br>5.4 | 4.4<br>5.4 |      |
|                 |                                                | I <sub>OUT</sub>   ≤ 6.0 mA                                                                                                      | 4.5                  | 3.98             | 3.84       | 3.7        |      |
| V <sub>OL</sub> | Maximum Low-Level Output Voltage               | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ;                                                                           |                      |                  |            |            | V    |
|                 |                                                | I <sub>OUT</sub>   ≤ 20 μA                                                                                                       | 4.5<br>5.5           | 0.1<br>0.1       | 0.1<br>0.1 | 0.1<br>0.1 |      |
|                 |                                                | I <sub>OUT</sub>   ≤ 6.0 mA                                                                                                      | 4.5                  | 0.26             | 0.33       | 0.4        |      |
| I <sub>IN</sub> | Maximum Input Leakage Current                  | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                         | 5.5                  | ±0.1             | ±1.0       | ±1.0       | μA   |
| I <sub>OZ</sub> | Maximum Three-State Leakage Current            | Output in High Impedance;<br>V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub> ;<br>V <sub>OUT</sub> = V <sub>CC</sub> or GND | 5.5                  | ±0.5             | ±5.0       | ±10.0      | μA   |
| I <sub>CC</sub> | Maximum Quiescent Supply Current (per Package) | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                         | 5.5                  | 4.0              | 40         | 160        | μA   |

| ΔI <sub>CC</sub> | Additional Quiescent Supply Current (Note 5) | V <sub>IN</sub> = 2.4 V, Any One Input;<br>V <sub>IN</sub> = V <sub>CC</sub> or GND, Other Inputs;<br>I <sub>OUT</sub> = 0 μA | 5.5 | ≥ -55°C | 25°C to 125°C | mA |
|------------------|----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|-----|---------|---------------|----|
|                  |                                              |                                                                                                                               |     | 2.9     | 2.4           |    |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Total Supply Current = I<sub>CC</sub> + Σ ΔI<sub>CC</sub>.

# MC74HC573A, MC74HCT573A

## AC ELECTRICAL CHARACTERISTICS (MC74HCT573A) (See Figures 2 and 3)

| Symbol                                 | Parameter                                                                  | V <sub>CC</sub><br>V | Guaranteed Limit |        |         | Unit |
|----------------------------------------|----------------------------------------------------------------------------|----------------------|------------------|--------|---------|------|
|                                        |                                                                            |                      | -55 to<br>25°C   | ≤ 85°C | ≤ 125°C |      |
| t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | Maximum Propagation Delay, D to Q                                          | 4.5 –<br>5.5         | 30               | 38     | 45      | ns   |
| t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | Maximum Propagation Delay, Latch Enable to Q                               | 4.5 –<br>5.5         | 30               | 38     | 45      | ns   |
| t <sub>PLZ</sub> ,<br>t <sub>PHZ</sub> | Maximum Propagation Delay, Output Enable to Q<br>ENABLE B to YB            | 4.5 –<br>5.5         | 28               | 35     | 42      | ns   |
| t <sub>PZL</sub> ,<br>t <sub>PZH</sub> | Maximum Propagation Delay, Output Enable to Q<br>ENABLE B to YB            | 4.5 –<br>5.5         | 28               | 35     | 42      | ns   |
| t <sub>TLH</sub> ,<br>t <sub>THL</sub> | Maximum Output Transition Time, Any Output                                 | 4.5 –<br>5.5         | 12               | 15     | 18      | ns   |
| C <sub>IN</sub>                        | Maximum Input Capacitance                                                  | –                    | 10               | 10     | 10      | pF   |
| C <sub>OUT</sub>                       | Maximum Three-State Output Capacitance<br>(Output in High Impedance State) | –                    | 15               | 15     | 15      | pF   |


| C <sub>PD</sub> | Power Dissipation Capacitance (Per Enabled Output) (Note 6) | 5.0 | Typical @ 25°C | pF |
|-----------------|-------------------------------------------------------------|-----|----------------|----|
|                 |                                                             |     | 48             |    |

6. Used to determine the no-load dynamic power consumption:  $P_D = C_{PD} \times V_{CC}^2 \times f + I_{CC} \times V_{CC}$ .

## TIMING REQUIREMENTS (MC74HCT573A) (See Figures 2 and 3)

| Symbol                          | Parameter                             | V <sub>CC</sub><br>(V) | Guaranteed Limit |        |         | Unit |
|---------------------------------|---------------------------------------|------------------------|------------------|--------|---------|------|
|                                 |                                       |                        | -55 to<br>25°C   | ≤ 85°C | ≤ 125°C |      |
| t <sub>SU</sub>                 | Minimum Setup Time, D to Latch Enable | 4.5 –<br>5.5           | 10               | 13     | 15      | ns   |
| t <sub>H</sub>                  | Minimum Hold Time, Latch Enable to D  | 4.5 –<br>5.5           | 5.0              | 5.0    | 5.0     | ns   |
| t <sub>W</sub>                  | Minimum Pulse Width, Latch Enable     | 4.5 –<br>5.5           | 15               | 19     | 22      | ns   |
| t <sub>r</sub> , t <sub>f</sub> | Maximum Input Rise and Fall Times     | 4.5 –<br>5.5           | 500              | 500    | 500     | ns   |


# MC74HC573A, MC74HCT573A



\*C<sub>L</sub> Includes probe and jig capacitance

| Test                                | Switch Position | C <sub>L</sub> | R <sub>L</sub> |
|-------------------------------------|-----------------|----------------|----------------|
| t <sub>PLH</sub> / t <sub>PHL</sub> | Open            | 50 pF          | 1 kΩ           |
| t <sub>PLZ</sub> / t <sub>PZL</sub> | V <sub>CC</sub> |                |                |
| t <sub>PHZ</sub> / t <sub>PZH</sub> | GND             |                |                |

Figure 2. Test Circuit



| Device      | V <sub>IN</sub> , V | V <sub>m</sub> , V    |
|-------------|---------------------|-----------------------|
| MC74HC573A  | V <sub>CC</sub>     | 50% x V <sub>CC</sub> |
| MC74HCT573A | 3 V                 | 1.3 V                 |

Figure 3. Switching Waveforms

## MC74HC573A, MC74HCT573A




Figure 4. Expanded Logic Diagram

### ORDERING INFORMATION

| Device              | Package      | Marking     | Shipping <sup>†</sup>    |
|---------------------|--------------|-------------|--------------------------|
| MC74HC573ADWG       | SOIC-20 Wide | HC573A      | 38 Units / Rail          |
| MC74HC573ADWR2G     | SOIC-20 Wide | HC573A      | 1000 / Tape & Reel       |
| MC74HC573ADTG       | TSSOP-20     | HC<br>573A  | 75 Units / Rail          |
| MC74HC573ADTR2G     | TSSOP-20     | HC<br>573A  | 2500 / Tape & Reel       |
| MC74HC573ADTR2G-Q*  | TSSOP-20     | HC<br>573A  | 2500 Units / Tape & Reel |
| MC74HCT573ADWG      | SOIC-20 Wide | HCT573A     | 38 Units / Rail          |
| MC74HCT573ADWR2G    | SOIC-20 Wide | HCT573A     | 1000 / Tape & Reel       |
| MC74HCT573ADTR2G    | TSSOP-20     | HCT<br>573A | 2500 / Tape & Reel       |
| MC74HCT573ADTR2G-Q* | TSSOP-20     | HCT<br>573A | 2500 / Tape & Reel       |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

\*-Q Suffix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable.



SCALE 1:1

SOIC-20 WB  
CASE 751D-05  
ISSUE H

DATE 22 APR 2015



NOTES:

1. DIMENSIONS ARE IN MILLIMETERS.
2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 1994.
3. DIMENSIONS D AND E DO NOT INCLUDE MOLD PROTRUSION.
4. MAXIMUM MOLD PROTRUSION 0.15 PER SIDE.
5. DIMENSION B DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE PROTRUSION SHALL BE 0.13 TOTAL IN EXCESS OF B DIMENSION AT MAXIMUM MATERIAL CONDITION.

| DIM | MILLIMETERS |       |
|-----|-------------|-------|
|     | MIN         | MAX   |
| A   | 2.35        | 2.65  |
| A1  | 0.10        | 0.25  |
| b   | 0.35        | 0.49  |
| c   | 0.23        | 0.32  |
| D   | 12.65       | 12.95 |
| E   | 7.40        | 7.60  |
| e   | 1.27 BSC    |       |
| H   | 10.05       | 10.55 |
| h   | 0.25        | 0.75  |
| L   | 0.50        | 0.90  |
| θ   | 0°          | 7°    |

GENERIC  
MARKING DIAGRAM\*



XXXXXX = Specific Device Code  
A = Assembly Location  
WL = Wafer Lot  
YY = Year  
WW = Work Week  
G = Pb-Free Package

RECOMMENDED  
SOLDERING FOOTPRINT\*



DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

|                  |             |                                                                                                                                                                                     |
|------------------|-------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98ASB42343B | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | SOIC-20 WB  | PAGE 1 OF 1                                                                                                                                                                         |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)