

REVISION V

UNLESS OTHERWISE NOTED			TITLE: LOW PROFILE TERMINAL ASSEMBLY	DWG NO: TLW-1XX-XX-XXX-X-XXX-XX SHEET 1 OF 3
DIMENSIONS ARE IN INCHES	TOLERANCES ARE:			
ONE PLACE DECIMALS ±.1 TWO PLACE DECIMALS ±.01	THREE PLACE DECIMALS ± .005 FOUR PLACE DECIMALS ± .0020	ANGLES ± 2°		





FIG. 1
(THROUGH HOLE)

NOTES:

- 1.) MAX ALLOWABLE BOW AFTER ASSEMBLY: .005 IN/IN.
- 2.) TERMINAL PUSHOUT FORCE: 2 lbs. MIN.
- 3.) MAX PIN ROTATION IN BODY: 2°.
- 4.) C REPRESENTS A CRITICAL DIMENSION.
- 5.) MAX CUT FLASH: .010.
- 6.) GOLD CONTACT AREA LOCATION FOR G, H, S, L, F, SM, LM, FM, & STL PLATINGS.
- 7.) C ORIENTATE PINS TO PREVENT BANDOLIER MARKS FROM SHOWING IN THE POST AREA. (SEE TABLE 2)

TLW-1XX-XX-XXX-X-XXX-XX

No. OF POSITIONS

- 01 THRU -40 (SINGLE)
- 01 THRU -36 (DOUBLE)

LEAD STYLE

- 01: (RA) SEE FIG. 2
- 05: (TH) SEE TABLE 1
- 06: (TH) SEE TABLE 1

PLATING SPECIFICATION

- G: GOLD (SPECIFY -G IN TERMINAL SUFFIX -XXX)
- T: TIN (SPECIFY -T IN TERMINAL SUFFIX -XXX)
- H: HEAVY GOLD (SPECIFY -H IN TERMINAL SUFFIX -XXX)
- S: SELECTIVE (SPECIFY -S IN TERMINAL SUFFIX -XXX)
- F: FLASH SELECTIVE (SPECIFY -F IN TERMINAL SUFFIX -XXX)
- L: LIGHT SELECTIVE (SPECIFY -L IN TERMINAL SUFFIX -XXX)
- TM: MATTE TIN (SPECIFY -T IN TERMINAL SUFFIX -XXX)
- SM: SELECTIVE HEAVY GOLD, MATTE TIN TAIL (SPECIFY -S IN TERMINAL SUFFIX -XXX)
- FM: FLASH SELECTIVE GOLD, MATTE TIN TAIL (SPECIFY -F IN TERMINAL SUFFIX -XXX)
- LM: LIGHT SELECTIVE GOLD, MATTE TIN TAIL (SPECIFY -L IN TERMINAL SUFFIX -XXX)
- STL: SELECTIVE GOLD, TIN/LEAD TAIL (SPECIFY -STL IN TERMINAL SUFFIX -XXX) (AVAILABLE IN STRAIGHT THROUGH HOLE VERSION **ONLY**)

OPTIONS

- BLANK: THROUGH HOLE (SEE FIG 1)
- RA: RIGHT ANGLE (LEAD STYLE -01 ONLY) (SEE FIG 2)
- LL: TH WITH LOCKING LEADS (SEE FIG 4)
- LA: RA WITH LOCKING LEADS (SEE FIG 3)

POLARIZING SPECIFICATION


XXX INDICATES POS. TO BE OMITTED
(IDENTIFY POSITION WITH FEET DOWN)

ROW SPECIFICATION


- S: SINGLE ROW (USE TLW-XX-S)
- D: DOUBLE ROW (USE TLW-XX-D)

TABLE 1

LEAD	TERMINAL 1	TERMINAL 2	"L"	"A"	"B"	"C"
-05	T-1S6-21-XXX-2	N/A	.335	.105	.170	.050
-06	T-1S6-18-XXX-2	N/A	.300	.105	.135	.050
-01-S	T-1S6-22-XXX-2	N/A	.495	.230	N/A	.165
-01-D	T-1S6-22-XXX-2	-----	.495	.230	N/A	.165
-01-D	-----	T-1S6-23-XXX-2	.695	.230	N/A	.165



-S: SINGLE



-D: DOUBLE

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC INC.

MATERIAL:
INSULATOR:
LIQUID CRYSTAL POLYMER
COLOR: BLACK

TERMINALS:
PHOSPHOR BRONZE

EXISPROD/ASSEMBLY/100
TLWASM

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:

M PUFFER 8-18-97

TLW-1XX-XX-XXX-X-XXX-XX

SHEET 1 OF 3