




- 1 MATERIAL: CONNECTOR- NYLON UL94V-2 (RED).
CONTACTS- 0.30 [.012] THK COPPER ALLOY
(BRIGHT TIN-LEAD 0.00203 [.000080] MIN THK).
(MATTE TIN 0.00203 [.000080] MIN THK).
- 2 CONTACTS ACCEPT #22 AWG SOLID, FUSED STRANDED OR
STRANDED (7 STRANDS) WIRE WITH 2.41 [.095] MAX INSULATION DIA.
- 3 BOW, IN ANY DIRECTION, NOT TO EXCEED 0.15 [.006] PER IN.
- 4 HOUSING FEATURES: FEED-THRU.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	TIN	91.14 [3.588]	95.20 [3.748]	99.06 [3.900]	24	5-641524-4
		55.47 [2.184]	59.54 [2.344]	63.40 [2.496]	15	4-641524-5
		43.59 [1.716]	47.65 [1.876]	51.51 [2.028]	12	4-641524-2
		31.70 [1.248]	35.76 [1.408]	39.62 [1.560]	9	3-641524-9
		19.81 [.780]	23.88 [.940]	27.74 [1.092]	6	3-641524-6
		11.89 [.468]	15.95 [.628]	19.81 [.780]	4	3-641524-4
		7.92 [.312]	11.99 [.472]	15.85 [.624]	3	3-641524-3
		3.96 [.156]	8.03 [.316]	11.89 [.468]	2	3-641524-2
	SUPERSEDED	91.14 [3.588]	95.20 [3.748]	99.06 [3.900]	24	— 641524-4 —
	SUPERSEDED	55.47 [2.184]	59.54 [2.344]	63.40 [2.496]	15	— 641524-5 —
	SUPERSEDED	43.59 [1.716]	47.65 [1.876]	51.51 [2.028]	12	— 641524-2 —
	SUPERSEDED	31.70 [1.248]	35.76 [1.408]	39.62 [1.560]	9	— 641524-9 —
	SUPERSEDED	19.81 [.780]	23.88 [.940]	27.74 [1.092]	6	— 641524-6 —
		11.89 [.468]	15.95 [.628]	19.81 [.780]	4	641524-4
		7.92 [.312]	11.99 [.472]	15.85 [.624]	3	641524-3
	SUPERSEDED	3.96 [.156]	8.03 [.316]	11.89 [.468]	2	— 641524-2 —

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: J. HUFFMAN 6-26-95 CHK: R. SWING 6-29-95 APVD: _____		 TE Connectivity	
DIMENSIONS: mm [INCHES] 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± . 1 PLC ± 0.13 [.005] 4 PLC ± . ANGLES ± . FINISH		PRODUCT SPEC _____ APPLICATION SPEC _____ WEIGHT _____	
MATERIAL SEE NOTE 1		CUSTOMER DRAWING		MTA-156 POSTED CONNECTOR ASSEMBLY, 22 AWG SIZE CAGE CODE DRAWING NO A1 00779 C=641524 SCALE: 5:1 SHEET 1 OF 1 REV: G	
				RESTRICTED TO _____	