




AB4510 SERIES

External Dimensions



Frame: Aluminum alloy
Impeller: Plastic (UL: 94V-0)
Lead wire: UL 1571 AWG28

Specifications (Nominal)


*Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
45x45x10	AB4505LB-GD1(B)	◎ ※ ●	5	0.07	0.35	4000	0.050 1.790	0.160 4.064	26.7	26.0
	AB4505MB-GD1(B)	◎ ※ ●	5	0.09	0.45	5000	0.065 2.300	0.250 6.350	31.1	
	AB4512LB-GD0(B)	◎ ※ ●	12	0.06	0.72	4000	0.050 1.790	0.160 4.064	26.7	
	AB4512MB-GD0(B)	◎ ※ ●	12	0.07	0.84	5000	0.065 2.300	0.250 6.350	31.1	
	AB4512HB-GD0(B)	◎ ※ ●	12	0.09	1.08	5800	0.076 2.700	0.340 8.636	37.0	

Specifications subject to change without notice.

The specification for bearing type is for reference only, for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以2Ball為主, 若需其他產品資訊請聯絡您在ADDA的業務代表, 謝謝!!)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓	✓		✓		✓					

*Safety approvals

UL	UL	SP	CE	CE
✓	✓		✓	✓