


SPECIFICATIONS

Model Number: **MX2B4**
 Part Number: **030389**

September 27, 2006



Mechanical Drawing:



Motor:

Nominal Voltage	= 115 VAC
Frequency	= 50/60 Hertz
Nominal Running Current	= 0.20/0.18 Amps
Locked Rotor Current	= 0.26/0.24 Amps
Running Power	= 17/15 Watts
Average Speed	= 2700/3100 RPM
Bearings	= Ball
Air Flow	= 115 CFM

Construction:

Venturi: Zinc Alloy, painted black.
 Propeller: flame retardant polypropylene with patented Feathered Edge.

Life Expectancy:

This fan is designed for continuous duty life of 55,000 hours at 40°C

Additional Features:

Two-Pole Shaded Pole Induction Motor	
Impedance Protected	
Operating Temperature:	-28°C to 70°C
Storage Temperature:	-40°C to 85°C

Termination:

12" Lead wires, 22 AWG, UL 1015

Agency Approvals:

UL, CSA, & VDE