

HDC enclosures
HDC 16B SLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings
- your first choice for industrial housings with IP 65 protection.

General ordering data

Order No.	1900170000
Type	HDC 16B SLU 1M25G
Version	HDC enclosures, Size: 6, Protection degree: IP 65, Base enclosure, End-locking clamp, lower side, Standard, Size of cable entries: M 25
GTIN (EAN)	4032248520800
Qty.	1 pc(s).

HDC enclosures

HDC 16B SLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	117 mm	Width	79.5 mm
Height	64 mm	Mounting dimension - width	105 mm
Mounting dimension - height	45 mm	Net weight	361 g

Dimensions

Total length housing	93.3 mm	Width housing C	43 mm
Width base C1	56.5 mm	Height of housing B	64 mm
Height of base B1	5 mm	Hole pitch length A2	105 mm
Cable entry	w. threading		

General data

Housing main material	diecast aluminium
-----------------------	-------------------

Version

Design of housing	Base enclosure	Size	6
Design	Standard	Top part/bottom part/lid	lower part
Design of locking system	End-locking clamp, lower side	Cable entry	w. threading
Size of cable entries	M 25	Number of cable entry on top	0
Number of cable entry sideways	1		

Classifications

ETIM 2.0	EC000437	ETIM 3.0	EC000437
UNSPSC	30-21-18-01	eClass 4.1	27-14-08-05
eClass 5.1	27-14-34-19	eClass 6.2	27-26-12-03
eClass 7.1	27-44-02-02		

Approvals

Approvals



ROHS	Conform
------	---------