

ISG Series



- Regulated Single Output
- SMD Package
- Industry Standard Pinout
- 1000 VDC Isolation
- Short Circuit Protection
- MTBF >3.5 Mhrs
- 3 Year Warranty

Specification

Input

- Input Voltage Range • Nominal $\pm 5\%$
 Input Reverse Voltage Protection • None

Output

- Output Voltage • See table
 Minimum Load • 10%⁽²⁾
 Line Regulation • $\pm 0.25\%$
 Load Regulation • $\pm 1\%$, 10-100% load change
 Setpoint Accuracy • $\pm 3\%$ at 100% load
 Ripple & Noise • 100 mV pk-pk 20 MHz bandwidth
 Temperature Coefficient • $0.03\%/^{\circ}\text{C}$
 Short Circuit Protection • Continuous

General


- Efficiency • See table
 Isolation Voltage • 1000 VDC
 Isolation Resistance • $10^9 \Omega$
 Switching Frequency • 100 kHz typical at nominal input, full load
 MTBF • >3.5 Mhrs to MIL-HDBK-217F at 25 °C, GB

Environmental


- Operating Temperature • -40 °C to +85 °C, derate from 100% load at 70 °C to 60% load at 85 °C
 Storage Temperature • -55 °C to +125 °C
 Case Temperature • 100 °C max
 Cooling • Convection-cooled
 Lead Temperature • 260 °C, 0.06 in (1.5 mm) from case, 10 s

Input Voltage	Output Voltage	Output Current	Efficiency (typical)	Model Number ⁽¹⁾
5 VDC	5 V	150 mA	68%	ISG0505A
	15 V	67 mA	69%	ISG0515A
12 VDC	15 V	67 mA	70%	ISG1215A

Mechanical Details



Recommended footprint
 Top view grid: 0.1 x 0.1 in (2.54 x 2.54 mm)



Pin	Standard	'-X' Version
1	GND	GND
2	V _{in}	V _{in}
4	0 V	0 V
7	+V _o	+V _o
3, 6, 8, 9	N.C.	No Pin
5, 10	N.C.	N.C.

N.C. Not connected

Notes

- For optional '-X' pin configuration, add suffix '-X' to part number.
- Operation at no load will not damage device but may not meet all specifications.
- All dimensions in inches (mm)
- Tolerance: ± 0.010 (± 0.25)
- Weight: 0.003 lbs (1.7 g)
- Pin tolerance: ± 0.004 (± 0.10 mm)