



LOC	DIST	REVISIONS							
		P	LTR	DESCRIPTION			DATE	DWN	APVD
—	—		C	REV PER ECO 13-016715			10-27-13	CT	JW



- 1 WIRE INSULATION: 12.70[.500] – 13.97[.550] DIA
- △2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.



INSERT & FUNNEL: BRASS MIL-C-50 NICKEL PL PER QQ-N-290 0.00762[.000300] AVG THK BODY: COPPER ASTM-B187 ANNEALED TIN PL PER MIL-T-10727 0.00381[.000150] MIN THK	55944-1
MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 4/29/93	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK WJ VOCKROTH 5/5/93		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	NAME TERMINAL, RING TONGUE, COPALUM TM	
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC 108-11011 APPLICATION SPEC 114-2134		
MATERIAL SEE TABLE 15.0		FINISH SEE TABLE	WEIGHT 75.0 Grams	RESTRICTED TO —
			CUSTOMER DRAWING	SCALE 2:1 SHEET 1 of 1 REV C