



SCHURTER ELECTRONIC COMPONENTS



Transibloc

To mount heatsinks to chassis via unique insulating block which enables power transistors to be mounted on heatsink direct without Mica insulation. This provides for better thermal path to heatsink and as entire heatsink is floated with respect to chassis only one voltage connection need be made to the base terminal.


Ideal for use with heatsinks featuring a 1/16 inch thick flange.



Transipillar

A versatile and rugged insulated mounting system consisting of studs and inserts moulded into a nylon pillar. Various combinations of stud, insert, metric threads and lengths are available.


Please consult Sales Office.



Technical Specifications

Moulded pillar	Nylon 66
Inserts	Plain brass threads BS Class 6H
Studs	Zinc plated steel threads BS Class 6G
Insulation	Minimum thickness 1mm
	Minimum insulation resistance 10^4 Mohm @ 500Vdc
	Minimum withstand voltage 11KVdc
Continuous working temperature range	-20°C to +80°C

ISS.	MOD. & DATE
1	18.1.89
2	15.8.89 C9348
3	19.8.92 C9430
4	15.2.94 C9466
5	12.9.01 C9526
DRN. A.J.Flint CHKD. R.D. DESIGN APPROVAL PRODN. APPROVAL	



984-00

TOLERANCE	BODY LENGTH L	
		mm
± 0.40 0.00	16	16.00
± 0.20	19	19.00
± 0.20	22	22.00
± 0.20	25	25.00
± 0.30	32	32.00
± 0.30	38	38.00
± 0.30	45	45.00
± 0.30	51	51.00
± 0.30	57	57.00
± 0.30	64	64.00

	STYLE	
1	STUD / STUD	S/S
2	INSERT / STUD	I/S
3	INSERT / INSERT	I/I

TPI/9.5/1/M4/1

TOLERANCES X.X +/- 0.4 X.XX +/- 0.1 UNLESS STATED OTHERWISE	MATL.	REFER TO PARTS LIST	SCALE — x FULL SIZE	TITLE TRANSIPILLAR-M4
	FINISH		DO NOT SCALE DRAWING	
DIMS IN MM	SCHURTER LTD. BOGNOR REGIS, UNITED KINGDOM		USED ON:	DRG No.
			SHT. 1 OF 1 SHTS.	9840.0100 to 9849.9300