

Front adapters - FLKM S135/S400/SO123 - 2301752

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The FLKM S135/S400/SO adapter links a SIMATIC® S5 plug directly with the basic SIMATIC® S7 400 card.
Conversion: S5 card 6ES5 436-4UA12 to S7 card 6ES7-421-1FH20-0AA0

RoHS

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	407.000 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	230 V AC/DC
Max. permissible current	4 A (per path)
	4 A (per connection, supply via separate power supply)
Mounting position	any

Connection data 1

Connection name	Field level
Connection method	SIEMENS S5-135 U pin strip

Supported controller

Controller	SIEMENS S5-135 U
- suitable I/O card	6ES5 436-4UA12

Front adapters - FLKM S135/S400/SO123 - 2301752

Technical data

Supported controller

Controller	SIEMENS S7-400
- suitable I/O card	6ES7 421-1FH20-0AA0

Standards and Regulations


Standards/regulations	IEC 60664
	DIN EN 50178
Rated insulation voltage	230 V
Rated surge voltage	2.1 kV (Functional insulation)
Pollution degree	2
Overvoltage category	II

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Circuit diagram



Connection scheme: FLKM S135/S400/SO123

Front adapters - FLKM S135/S400/SO123 - 2301752

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27249205
eCl@ss 7.0	27249205
eCl@ss 8.0	27249290
eCl@ss 9.0	27242292

ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC002584

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421