

IM series

Sealed snap-action pushbutton switches - bushing Ø 12 mm - momentary

Distinctive features and specifications

UG1410-A-R2



- ☐ Snap-action : tactile feedback with audible click
- ☐ High current/voltage rating
- ☐ Sealed to IP67
- ☐ Flat round actuator for optional marking

ENVIRONMENTAL SPECIFICATIONS

- Front panel sealing : IP67 according to IEC 60529
- Shock resistance : 50 g - 11 ms according to IEC 68-2-27
- Salt spray : IEC 512-6, test 11f
- Operating temperature : -40°C to +85°C
- Storage temperature : -40°C to +85°C

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load : 3A 28VDC
- Initial contact resistance : 100 mΩ max.
- Insulation resistance : 1 GΩ min. at 500VDC
- Dielectric strength : 500 Vrms between terminals
- Electrical life at full load : 25.000 cycles

GENERAL SPECIFICATIONS

- Panel thickness : 1,5 mm (.059) to 10 mm (.394)
- Total travel : 1,7 mm (.067) +/- 0,3 mm
- Low level or mechanical life : 1.000.000 cycles
- Torque (applied to nut) : 1 Nm max. with metal nut U166
1,5 Nm max. with plastic nut U4248

MATERIALS

- Case : polyamide 4/6
- Actuator : polyamide 6/6
- Bushing/bezel : polyamide 6/6
- Contacts : silver, gold plated
- Terminal seal : epoxy

AGENCY APPROVAL




1A 125VAC/250VAC
File E83438

Availability : consult factory for details of approved models.

Marking : to order switches marked UL, complete appropriate box of ordering format.


MOUNTING - STANDARD BEZEL

Panel cut-out




① Flat seal

Matrix mounting




Back of panel space requirement




MOUNTING - REDUCED BEZEL

Panel cut-out




② O-ring

Matrix mounting




Back of panel space requirement



IM series

Sealed snap-action pushbutton switches - bushing Ø 12 mm - momentary

Overview



ABOUT THIS SERIES

On the following pages, you will find successively :
model structure of switches and options in the same order as in above chart

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



NOTICE : please note that not all combinations of above numbers are available.
Refer to the following pages for further information.



A sealing boot is available to protect the switches against frost and sand (P/N U5125).
It is presented after the IA series and in section H.



Mounting accessories : Standard hardware supplied : 1 flat seal (standard bezel) or 1 O-ring (reduced bezel) and 1 metal hex nut 14 mm (.551) across flats. Hex nut part number U166.
Plastic nut 17 mm (.669) across flats, thickness 4 mm (.157) available on request. Part number U4248.



Packaging unit : 50 pieces


The company reserves the right to change specifications without notice.

IM series


Sealed snap-action pushbutton switches - bushing Ø 12 mm - momentary

Options


BEZEL OPTIONS




- Blank** Standard bezel
- 075** Dia. 15 (.590) reduced bezel, mounting of the switch from the front into a threaded panel cut-out
- 234** Dia. 15 (.590) reduced bezel, standard mounting




ACTUATOR OPTION



- Blank** Standard actuator
- 104** High actuator



AGENCY APPROVAL



UL

Availability : consult factory for details of approved models.
Marking : to order switches marked UL, complete above box with "UL".

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Apem:

[IMP7P462](#) [IMR7Z452075](#) [IMR7P422075](#) [IMP7P422104](#) [IMR7P412104](#) [IMP7Z452104](#) [IMR7P492075](#)
[IMP7Z462075](#) [IMR7Z412234](#) [IMP7Z492](#) [IMP7Z422](#) [IMP7P462234](#) [IMR7P462104](#) [IMR7P452234](#) [IMR7Z462](#)
[IMP7P432075](#) [IMR7Z492104](#) [IMP7P4B2075](#) [IMR7P432](#) [IMR7P4B2](#) [IMR7Z4B2075](#) [IMP7Z412](#) [IMR7P4B2075](#)
[IMR7Z422104](#) [IMR7P492104](#) [IMR7Z462234](#) [IMR7P422104](#) [IMP7Z472](#) [IMP7Z462104](#) [IMP7P472](#) [IMR7Z462075](#)
[IMP7Z4B2](#) [IMR7P462](#) [IMP7P422234](#) [IMP7P412234](#) [IMR7Z432104](#) [IMP7Z432](#) [IMP7P412](#) [IMR7P472104](#)
[IMR7P432075](#) [IMP7P472234](#) [IMP7Z4B2075](#) [IMR7Z412](#) [IMR7P412](#) [IMR7P452](#) [IMP7Z412075](#) [IMP7Z472075](#)
[IMP7Z4B2234](#) [IMR7Z4B2104](#) [IMR7P462234](#) [IMP7Z462234](#) [IMP7P4B2234](#) [IMR7Z4B2234](#) [IMP7Z432075](#)
[IMP7Z472104](#) [IMR7Z4B2](#) [IMR7Z462104](#) [IMP7P432234](#) [IMR7P452075](#) [IMP7P472075](#) [IMP7Z452234](#) [IMP7P492](#)
[IMR7P4B2104](#) [IMR7Z412075](#) [IMP7Z492075](#) [IMR7Z472075](#) [IMP7P492104](#) [IMP7Z412104](#) [IMR7Z452104](#)
[IMP7Z422075](#) [IMP7Z452](#) [IMR7Z432075](#) [IMR7Z472234](#) [IMR7Z452](#) [IMP7P422](#) [IMP7P452234](#) [IMP7Z452075](#)
[IMP7Z422234](#) [IMP7Z432104](#) [IMP7P412104](#) [IMR7Z422](#) [IMP7P432104](#) [IMR7P412075](#) [IMR7P4B2234](#) [IMR7P472075](#)
[IMP7P422075](#) [IMR7Z422234](#) [IMR7Z412104](#) [IMR7Z472](#) [IMR7P452104](#) [IMR7P462075](#) [IMR7Z422075](#)
[IMP7P452075](#) [IMP7P462104](#) [IMR7Z452234](#) [IMP7Z462](#) [IMR7P422](#) [IMR7Z472104](#) [IMR7P432104](#) [IMP7P432](#)