


# SN54LV123A, SN74LV123A DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS WITH SCHMITT-TRIGGER INPUTS


SCLS3930 – APRIL 1998 – REVISED OCTOBER 2005

- 2-V to 5.5-V  $V_{CC}$  Operation
- Max  $t_{pd}$  of 11 ns at 5 V
- Typical  $V_{OLP}$  (Output Ground Bounce)  $<0.8$  V at  $V_{CC} = 3.3$  V,  $T_A = 25^\circ\text{C}$
- Typical  $V_{OHV}$  (Output  $V_{OH}$  Undershoot)  $>2.3$  V at  $V_{CC} = 3.3$  V,  $T_A = 25^\circ\text{C}$
- Support Mixed-Mode Voltage Operation on All Ports
- Schmitt-Trigger Circuitry on  $\overline{A}$ , B, and  $\overline{CLR}$  Inputs for Slow Input Transition Rates
- Edge Triggered From Active-High or Active-Low Gated Logic Inputs
- $I_{off}$  Supports Partial-Power-Down Mode Operation
- Retriggerable for Very Long Output Pulses, up to 100% Duty Cycle
- Overriding Clear Terminates Output Pulse
- Glitch-Free Power-Up Reset on Outputs
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)
  - 1000-V Charged-Device Model (C101)


SN54LV123A ... J OR W PACKAGE  
SN74LV123A ... D, DB, DGV, NS,  
OR PW PACKAGE  
(TOP VIEW)



SN74LV123A ... RGY PACKAGE  
(TOP VIEW)



SN54LV123A ... FK PACKAGE  
(TOP VIEW)



NC – No internal connection

## description/ordering information

The 'LV123A devices are dual retriggerable monostable multivibrators designed for 2-V to 5.5-V  $V_{CC}$  operation.

These edge-triggered multivibrators feature output pulse-duration control by three methods. In the first method, the  $\overline{A}$  input is low and the B input goes high. In the second method, the B input is high and the  $\overline{A}$  input goes low. In the third method, the  $\overline{A}$  input is low, the B input is high, and the clear ( $\overline{CLR}$ ) input goes high.

The output pulse duration is programmable by selecting external resistance and capacitance values. The external timing capacitor must be connected between  $C_{ext}$  and  $R_{ext}/C_{ext}$  (positive) and an external resistor connected between  $R_{ext}/C_{ext}$  and  $V_{CC}$ . To obtain variable pulse durations, connect an external variable resistance between  $R_{ext}/C_{ext}$  and  $V_{CC}$ . The output pulse duration also can be reduced by taking  $\overline{CLR}$  low.

Pulse triggering occurs at a particular voltage level and is not directly related to the transition time of the input pulse. The  $\overline{A}$ , B, and  $\overline{CLR}$  inputs have Schmitt triggers with sufficient hysteresis to handle slow input transition rates with jitter-free triggering at the outputs.

Once triggered, the basic pulse duration can be extended by retriggering the gated low-level-active ( $\overline{A}$ ) or high-level-active (B) input. Pulse duration can be reduced by taking  $\overline{CLR}$  low. The input/output timing diagram illustrates pulse control by retriggering the inputs and early clearing.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

UNLESS OTHERWISE NOTED this document contains PRODUCTION DATA information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2005, Texas Instruments Incorporated

# SN54LV123A, SN74LV123A DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS WITH SCHMITT-TRIGGER INPUTS

SCLS393O – APRIL 1998 – REVISED OCTOBER 2005

## description/ordering information (continued)

During power up, Q outputs are in the low state, and  $\overline{Q}$  outputs are in the high state. The outputs are glitch free, without applying a reset pulse.

These devices are fully specified for partial-power-down applications using  $I_{off}$ . The  $I_{off}$  circuitry disables the outputs, preventing damaging current backflow through the devices when they are powered down.







Pin assignments for these devices are identical to those of the 'AHC123A and 'AHCT123A devices for interchangeability, when allowed.

## ORDERING INFORMATION

| T <sub>A</sub> | PACKAGE†    |              | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|----------------|-------------|--------------|-----------------------|------------------|
| –40°C to 85°C  | QFN – RGY   | Reel of 1000 | SN74LV123ARGYR        | LV123A           |
|                | SOIC – D    | Tube of 40   | SN74LV123AD           | LV123A           |
|                |             | Reel of 2500 | SN74LV123ADR          |                  |
|                | SOP – NS    | Reel of 2000 | SN74LV123ANSR         | 74LV123A         |
|                | SSOP – DB   | Reel of 2000 | SN74LV123ADBR         | LV123A           |
|                | TSSOP – PW  | Tube of 90   | SN74LV123APW          | LV123A           |
|                |             | Reel of 2000 | SN74LV123APWR         |                  |
|                |             | Reel of 250  | SN74LV123APWT         |                  |
|                | TVSOP – DGV | Reel of 2000 | SN74LV123ADGVR        | LV123A           |
| –55°C to 125°C | CDIP – J    | Tube of 25   | SNJ54LV123AJ          | SNJ54LV123AJ     |
|                | CFP – W     | Tube of 150  | SNJ54LV123AW          | SNJ54LV123AW     |
|                | LCCC – FK   | Tube of 55   | SNJ54LV123AFK         | SNJ54LV123AFK    |


† Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).

## FUNCTION TABLE (each multivibrator)


| INPUTS |                |   | OUTPUTS   |   |
|--------|----------------|---|---|---|
| CLR    | $\overline{A}$ | B | Q   | $\overline{Q}$  |
| L      | X              | X | L   | H   |
| X      | H              | X | L <sup>‡</sup>  | H <sup>‡</sup>  |
| X      | X              | L | L <sup>‡</sup>  | H <sup>‡</sup>  |
| H      | L              | ↑ |  |  |
| H      | ↓              | H |  |  |
| ↑      | L              | H |  |  |

<sup>‡</sup> These outputs are based on the assumption that the indicated steady-state conditions at the  $\overline{A}$  and B inputs have been set up long enough to complete any pulse started before the setup.

logic diagram, each multivibrator (positive logic)



input/output timing diagram



# SN54LV123A, SN74LV123A

## DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS

### WITH SCHMITT-TRIGGER INPUTS

SCLS393O – APRIL 1998 – REVISED OCTOBER 2005

#### absolute maximum ratings over operating free-air temperature (unless otherwise noted)<sup>†</sup>

|   |                            |
|---|----------------------------|
| Supply voltage range, $V_{CC}$  | –0.5 V to 7 V              |
| Input voltage range, $V_I$ (see Note 1)   | –0.5 V to 7 V              |
| Voltage range applied to any output in the high-impedance<br>or power-off state, $V_O$ (see Note 1) | –0.5 V to 7 V              |
| Output voltage range in high or low state, $V_O$ (see Notes 1 and 2)                                | –0.5 V to $V_{CC} + 0.5$ V |
| Output voltage range in power-off state, $V_O$ (see Note 1)   | –0.5 V to 7 V              |
| Input clamp current, $I_{IK}$ ( $V_I < 0$ )   | –20 mA                     |
| Output clamp current, $I_{OK}$ ( $V_O < 0$ )  | –50 mA                     |
| Continuous output current, $I_O$ ( $V_O = 0$ to $V_{CC}$ )  | ±25 mA                     |
| Continuous current through $V_{CC}$ or GND  | ±50 mA                     |
| Package thermal impedance, $\theta_{JA}$ (see Note 3): D package                                    | 73°C/W                     |
| (see Note 3): DB package  | 82°C/W                     |
| (see Note 3): DGV package   | 120°C/W                    |
| (see Note 3): NS package  | 64°C/W                     |
| (see Note 3): PW package  | 108°C/W                    |
| (see Note 4): RGY package   | 39°C/W                     |
| Storage temperature range, $T_{stg}$  | –65°C to 150°C             |

<sup>†</sup> Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES:
1. The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.
  2. This value is limited to 5.5 V maximum.
  3. The package thermal impedance is calculated in accordance with JESD 51-7.
  4. The package thermal impedance is calculated in accordance with JESD 51-5.

# SN54LV123A, SN74LV123A DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS WITH SCHMITT-TRIGGER INPUTS

SCLS3930 – APRIL 1998 – REVISED OCTOBER 2005

## recommended operating conditions (see Note 5)

|                     |                                |                                  | SN54LV123A            |                       | SN74LV123A            |                       | UNIT |
|---------------------|--------------------------------|----------------------------------|-----------------------|-----------------------|-----------------------|-----------------------|------|
|                     |                                |                                  | MIN                   | MAX                   | MIN                   | MAX                   |      |
| V <sub>CC</sub>     | Supply voltage                 |                                  | 2                     | 5.5                   | 2                     | 5.5                   | V    |
| V <sub>IH</sub>     | High-level input voltage       | V <sub>CC</sub> = 2 V            | 1.5                   |                       | 1.5                   |                       | V    |
|                     |                                | V <sub>CC</sub> = 2.3 V to 2.7 V | V <sub>CC</sub> × 0.7 |                       | V <sub>CC</sub> × 0.7 |                       |      |
|                     |                                | V <sub>CC</sub> = 3 V to 3.6 V   | V <sub>CC</sub> × 0.7 |                       | V <sub>CC</sub> × 0.7 |                       |      |
|                     |                                | V <sub>CC</sub> = 4.5 V to 5.5 V | V <sub>CC</sub> × 0.7 |                       | V <sub>CC</sub> × 0.7 |                       |      |
| V <sub>IL</sub>     | Low-level input voltage        | V <sub>CC</sub> = 2 V            |                       | 0.5                   |                       | 0.5                   | V    |
|                     |                                | V <sub>CC</sub> = 2.3 V to 2.7 V |                       | V <sub>CC</sub> × 0.3 |                       | V <sub>CC</sub> × 0.3 |      |
|                     |                                | V <sub>CC</sub> = 3 V to 3.6 V   |                       | V <sub>CC</sub> × 0.3 |                       | V <sub>CC</sub> × 0.3 |      |
|                     |                                | V <sub>CC</sub> = 4.5 V to 5.5 V |                       | V <sub>CC</sub> × 0.3 |                       | V <sub>CC</sub> × 0.3 |      |
| V <sub>I</sub>      | Input voltage                  |                                  | 0                     | 5.5                   | 0                     | 5.5                   | V    |
| V <sub>O</sub>      | Output voltage                 |                                  | 0                     | V <sub>CC</sub>       | 0                     | V <sub>CC</sub>       | V    |
| I <sub>OH</sub>     | High-level output current      | V <sub>CC</sub> = 2 V            |                       | –50                   |                       | –50                   | μA   |
|                     |                                | V <sub>CC</sub> = 2.3 V to 2.7 V |                       | –2                    |                       | –2                    | mA   |
|                     |                                | V <sub>CC</sub> = 3 V to 3.6 V   |                       | –6                    |                       | –6                    |      |
|                     |                                | V <sub>CC</sub> = 4.5 V to 5.5 V |                       | –12                   |                       | –12                   |      |
| I <sub>OL</sub>     | Low-level output current       | V <sub>CC</sub> = 2 V            |                       | 50                    |                       | 50                    | μA   |
|                     |                                | V <sub>CC</sub> = 2.3 V to 2.7 V |                       | 2                     |                       | 2                     | mA   |
|                     |                                | V <sub>CC</sub> = 3 V to 3.6 V   |                       | 6                     |                       | 6                     |      |
|                     |                                | V <sub>CC</sub> = 4.5 V to 5.5 V |                       | 12                    |                       | 12                    |      |
| R <sub>ext</sub>    | External timing resistance     | V <sub>CC</sub> = 2 V            | 5k                    |                       | 5k                    |                       | Ω    |
|                     |                                | V <sub>CC</sub> ≥ 3 V            | 1k                    |                       | 1k                    |                       |      |
| C <sub>ext</sub>    | External timing capacitance    |                                  | No restriction        |                       | No restriction        |                       | pF   |
| Δt/ΔV <sub>CC</sub> | Power-up ramp rate             |                                  | 1                     |                       | 1                     |                       | ms/V |
| T <sub>A</sub>      | Operating free-air temperature |                                  | –55                   | 125                   | –40                   | 85                    | °C   |

NOTE 5: Unused R<sub>ext</sub>/C<sub>ext</sub> terminals should be left unconnected. All remaining unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

# SN54LV123A, SN74LV123A

## DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS

### WITH SCHMITT-TRIGGER INPUTS

SCLS393O – APRIL 1998 – REVISED OCTOBER 2005

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER        |   | TEST CONDITIONS   | V <sub>CC</sub> | SN54LV123A           |     |     | SN74LV123A           |     |     | UNIT |
|------------------|---|---|-----------------|----------------------|-----|-----|----------------------|-----|-----|------|
|                  |   |   |                 | MIN                  | TYP | MAX | MIN                  | TYP | MAX |      |
| V <sub>OH</sub>  |   | I <sub>OH</sub> = -50 μA  | 2 V to 5.5 V    | V <sub>CC</sub> -0.1 |     |     | V <sub>CC</sub> -0.1 |     |     | V    |
|                  |   | I <sub>OH</sub> = -2 mA   | 2.3 V           | 2                    |     |     | 2                    |     |     |      |
|                  |   | I <sub>OH</sub> = -6 mA   | 3 V             | 2.48                 |     |     | 2.48                 |     |     |      |
|                  |   | I <sub>OH</sub> = -12 mA  | 4.5 V           | 3.8                  |     |     | 3.8                  |     |     |      |
| V <sub>OL</sub>  |   | I <sub>OL</sub> = 50 μA   | 2 V to 5.5 V    | 0.1                  |     |     | 0.1                  |     |     | V    |
|                  |   | I <sub>OL</sub> = 2 mA  | 2.3 V           | 0.4                  |     |     | 0.4                  |     |     |      |
|                  |   | I <sub>OL</sub> = 6 mA  | 3 V             | 0.44                 |     |     | 0.44                 |     |     |      |
|                  |   | I <sub>OL</sub> = 12 mA   | 4.5 V           | 0.55                 |     |     | 0.55                 |     |     |      |
| I <sub>I</sub>   | R <sub>ext</sub> /C <sub>ext</sub> <sup>†</sup> | V <sub>I</sub> = 5.5 V or GND   | 2 V to 5.5 V    | ±2.5                 |     |     | ±2.5                 |     |     | μA   |
|                  | $\overline{A}$ , B, and $\overline{CLR}$        | V <sub>I</sub> = 5.5 V or GND   | 0               | ±1                   |     |     | ±1                   |     |     |      |
|                  |   |   |                 | 0 to 5.5 V           | ±1  |     |                      | ±1  |     |      |
| I <sub>CC</sub>  | Quiescent                                       | V <sub>I</sub> = V <sub>CC</sub> or GND, I <sub>O</sub> = 0                                       | 5.5 V           | 20                   |     |     | 20                   |     |     | μA   |
| I <sub>CC</sub>  | Active state (per circuit)                      | V <sub>I</sub> = V <sub>CC</sub> or GND, R <sub>ext</sub> /C <sub>ext</sub> = 0.5 V <sub>CC</sub> | 2.3 V           | 220                  |     |     | 220                  |     |     | μA   |
|                  |   |   | 3 V             | 280                  |     |     | 280                  |     |     |      |
|                  |   |   | 4.5 V           | 650                  |     |     | 650                  |     |     |      |
|                  |   |   | 5.5 V           | 975                  |     |     | 975                  |     |     |      |
| I <sub>off</sub> |   | V <sub>I</sub> or V <sub>O</sub> = 0 to 5.5 V   | 0               |                      |     |     | 5                    |     |     | μA   |
| C <sub>i</sub>   |   | V <sub>I</sub> = V <sub>CC</sub> or GND   | 3.3 V           | 1.9                  |     |     | 1.9                  |     |     | pF   |
|                  |   |   | 5 V             | 1.9                  |     |     | 1.9                  |     |     |      |

<sup>†</sup> This test is performed with the terminal in the off-state condition.

timing requirements over recommended operating free-air temperature range, V<sub>CC</sub> = 2.5 V ± 0.2 V (unless otherwise noted) (see Figure 1)

|                 |                      |                         | TEST CONDITIONS            |      | T <sub>A</sub> = 25°C |     |     | SN54LV123A |     | SN74LV123A |     | UNIT |
|-----------------|----------------------|-------------------------|----------------------------|------|-----------------------|-----|-----|------------|-----|------------|-----|------|
|                 |                      |                         |                            |      | MIN                   | TYP | MAX | MIN        | MAX | MIN        | MAX |      |
| t <sub>w</sub>  | Pulse duration       | CL <sub>R</sub>         |                            |      | 6                     |     |     | 6.5        |     | 6.5        |     | ns   |
|                 |                      | A or B trigger          |                            |      | 6                     |     |     | 6.5        |     | 6.5        |     |      |
| t <sub>rr</sub> | Pulse retrigger time | R <sub>ext</sub> = 1 kΩ | C <sub>ext</sub> = 100 pF  | ‡ 94 |                       |     | ‡   |            |     | ‡          |     | ns   |
|                 |                      |                         | C <sub>ext</sub> = 0.01 μF | ‡ 2  |                       |     | ‡   |            |     | ‡          |     | μs   |

<sup>‡</sup> See retriggering data in the application information section.

timing requirements over recommended operating free-air temperature range, V<sub>CC</sub> = 3.3 V ± 0.3 V (unless otherwise noted) (see Figure 1)

|                 |                      |                                    | TEST CONDITIONS            |   | T <sub>A</sub> = 25°C |     |     | SN54LV123A |     | SN74LV123A |     | UNIT |
|-----------------|----------------------|------------------------------------|----------------------------|---|-----------------------|-----|-----|------------|-----|------------|-----|------|
|                 |                      |                                    |                            |   | MIN                   | TYP | MAX | MIN        | MAX | MIN        | MAX |      |
| t <sub>w</sub>  | Pulse duration       | $\overline{\text{CLR}}$            |                            |   | 5                     |     |     | 5          |     | 5          |     | ns   |
|                 |                      | $\overline{\text{A}}$ or B trigger |                            |   | 5                     |     |     | 5          |     | 5          |     |      |
| t <sub>rr</sub> | Pulse retrigger time | R <sub>ext</sub> = 1 kΩ            | C <sub>ext</sub> = 100 pF  | ‡ | 76                    | ‡   |     |            | ‡   |            | ns  |      |
|                 |                      |                                    | C <sub>ext</sub> = 0.01 μF | ‡ | 1.8                   | ‡   |     |            | ‡   |            | μs  |      |

<sup>‡</sup> See retriggering data in the application information section.

PRODUCT PREVIEW information concerns products in the formative or design phase of development. Characteristic data and other specifications are design goals. Texas Instruments reserves the right to change or discontinue these products without notice.



# SN54LV123A, SN74LV123A DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS WITH SCHMITT-TRIGGER INPUTS

SCLS3930 – APRIL 1998 – REVISED OCTOBER 2005

timing requirements over recommended operating free-air temperature range,  $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$  (unless otherwise noted) (see Figure 1)

|          |                      | TEST CONDITIONS                    | $T_A = 25^\circ\text{C}$            |     |       | SN54LV123A |     | SN74LV123A |     | UNIT          |
|----------|----------------------|------------------------------------|-------------------------------------|-----|-------|------------|-----|------------|-----|---------------|
|          |                      |                                    | MIN                                 | TYP | MAX   | MIN        | MAX | MIN        | MAX |               |
| $t_w$    | Pulse duration       | $\overline{\text{CLR}}$            | 5                                   |     |       | 5          |     | 5          |     | ns            |
|          |                      | $\overline{\text{A}}$ or B trigger | 5                                   |     |       | 5          |     | 5          |     |               |
| $t_{rr}$ | Pulse retrigger time | $R_{ext} = 1\text{ k}\Omega$       | $C_{ext} = 100\text{ pF}$           |     | † 59  | †          |     | †          |     | ns            |
|          |                      |                                    | $C_{ext} = 0.01\text{ }\mu\text{F}$ |     | † 1.5 | †          |     | †          |     | $\mu\text{s}$ |

† See retriggering data in the *application information* section.

switching characteristics over recommended operating free-air temperature range,  $V_{CC} = 2.5\text{ V} \pm 0.2\text{ V}$  (unless otherwise noted) (see Figure 1)

| PARAMETER       | FROM (INPUT)                    | TO (OUTPUT)                | TEST CONDITIONS  | $T_A = 25^\circ\text{C}$ |       |     | SN54LV123A |       | SN74LV123A |      | UNIT          |
|-----------------|---------------------------------|----------------------------|--|--------------------------|-------|-----|------------|-------|------------|------|---------------|
|                 |                                 |                            |  | MIN                      | TYP   | MAX | MIN        | MAX   | MIN        | MAX  |               |
| $t_{pd}$        | $\overline{\text{A}}$ or B      | Q or $\overline{\text{Q}}$ | $C_L = 15\text{ pF}$   | 14.5*                    | 31.4* |     | 1*         | 37*   | 1          | 37   | ns            |
|                 | $\overline{\text{CLR}}$         | Q or $\overline{\text{Q}}$ |  | 13*                      | 25*   |     | 1*         | 29.5* | 1          | 29.5 |               |
|                 | $\overline{\text{CLR}}$ trigger | Q or $\overline{\text{Q}}$ |  | 15.1*                    | 33.4* |     | 1*         | 39*   | 1          | 39   |               |
| $t_{pd}$        | $\overline{\text{A}}$ or B      | Q or $\overline{\text{Q}}$ | $C_L = 50\text{ pF}$   | 16.6                     | 36    |     | 1          | 42    | 1          | 42   | ns            |
|                 | $\overline{\text{CLR}}$         | Q or $\overline{\text{Q}}$ |  | 14.7                     | 32.8  |     | 1          | 34.5  | 1          | 34.5 |               |
|                 | $\overline{\text{CLR}}$ trigger | Q or $\overline{\text{Q}}$ |  | 17.4                     | 38    |     | 1          | 44    | 1          | 44   |               |
| $t_w^\ddagger$  |                                 | Q or $\overline{\text{Q}}$ | $C_L = 50\text{ pF}$ ,<br>$C_{ext} = 28\text{ pF}$ ,<br>$R_{ext} = 2\text{ k}\Omega$             | 197                      | 260   |     |            | 320   |            | 320  | ns            |
|                 |                                 |                            | $C_L = 50\text{ pF}$ ,<br>$C_{ext} = 0.01\text{ }\mu\text{F}$ ,<br>$R_{ext} = 10\text{ k}\Omega$ | 90                       | 100   | 110 | 90         | 110   | 90         | 110  | $\mu\text{s}$ |
|                 |                                 |                            | $C_L = 50\text{ pF}$ ,<br>$C_{ext} = 0.1\text{ }\mu\text{F}$ ,<br>$R_{ext} = 10\text{ k}\Omega$  | 0.9                      | 1     | 1.1 | 0.9        | 1.1   | 0.9        | 1.1  | ms            |
| $\Delta t_w^\S$ |                                 |                            | $C_L = 50\text{ pF}$   | $\pm 1$                  |       |     |            |       |            |      | %             |

\* On products compliant to MIL-PRF-38535, this parameter is not production tested.

†  $t_w$  = Duration of pulse at Q and  $\overline{\text{Q}}$  outputs

§  $\Delta t_w$  = Output pulse-duration variation (Q and  $\overline{\text{Q}}$ ) between circuits in same package

PRODUCT PREVIEW information concerns products in the formative or design phase of development. Characteristic data and other specifications are design goals. Texas Instruments reserves the right to change or discontinue these products without notice.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

# SN54LV123A, SN74LV123A

## DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS

### WITH SCHMITT-TRIGGER INPUTS

SCLS393O – APRIL 1998 – REVISED OCTOBER 2005

switching characteristics over recommended operating free-air temperature range,  $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$  (unless otherwise noted) (see Figure 1)

| PARAMETER             | FROM<br>(INPUT)          | TO<br>(OUTPUT)      | TEST<br>CONDITIONS   | $T_A = 25^\circ\text{C}$ |       |     | SN54LV123A |       | SN74LV123A |      | UNIT          |
|-----------------------|--------------------------|---------------------|--|--------------------------|-------|-----|------------|-------|------------|------|---------------|
|                       |                          |                     |  | MIN                      | TYP   | MAX | MIN        | MAX   | MIN        | MAX  |               |
| $t_{pd}$              | $\overline{A}$ or B      | Q or $\overline{Q}$ | $C_L = 15\text{ pF}$   | 10.2*                    | 20.6* |     | 1*         | 24*   | 1          | 24   | ns            |
|                       | $\overline{CLR}$         | Q or $\overline{Q}$ |  | 9.3*                     | 15.8* |     | 1*         | 18.5* | 1          | 18.5 |               |
|                       | $\overline{CLR}$ trigger | Q or $\overline{Q}$ |  | 10.6*                    | 22.4* |     | 1*         | 26*   | 1          | 26   |               |
| $t_{pd}$              | $\overline{A}$ or B      | Q or $\overline{Q}$ | $C_L = 50\text{ pF}$   | 11.8                     | 24.1  |     | 1          | 27.5  | 1          | 27.5 | ns            |
|                       | $\overline{CLR}$         | Q or $\overline{Q}$ |  | 10.5                     | 19.3  |     | 1          | 22    | 1          | 22   |               |
|                       | $\overline{CLR}$ trigger | Q or $\overline{Q}$ |  | 12.3                     | 25.9  |     | 1          | 29.5  | 1          | 29.5 |               |
| $t_w^\dagger$         |                          |                     | $C_L = 50\text{ pF}$ ,<br>$C_{ext} = 28\text{ pF}$ ,<br>$R_{ext} = 2\text{ k}\Omega$             | 182                      | 240   |     |            | 300   |            | 300  | ns            |
|                       |                          |                     | $C_L = 50\text{ pF}$ ,<br>$C_{ext} = 0.01\text{ }\mu\text{F}$ ,<br>$R_{ext} = 10\text{ k}\Omega$ | 90                       | 100   | 110 | 90         | 110   | 90         | 110  | $\mu\text{s}$ |
|                       |                          |                     | $C_L = 50\text{ pF}$ ,<br>$C_{ext} = 0.1\text{ }\mu\text{F}$ ,<br>$R_{ext} = 10\text{ k}\Omega$  | 0.9                      | 1     | 1.1 | 0.9        | 1.1   | 0.9        | 1.1  | ms            |
| $\Delta t_w^\ddagger$ |                          |                     | $C_L = 50\text{ pF}$   | $\pm 1$                  |       |     |            |       |            |      | %             |

\* On products compliant to MIL-PRF-38535, this parameter is not production tested.

$^\dagger t_w$  = Duration of pulse at Q and  $\overline{Q}$  outputs

$^\ddagger \Delta t_w$  = Output pulse-duration variation (Q and  $\overline{Q}$ ) between circuits in same package

switching characteristics over recommended operating free-air temperature range,  $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$  (unless otherwise noted) (see Figure 1)

| PARAMETER             | FROM<br>(INPUT)          | TO<br>(OUTPUT)      | TEST<br>CONDITIONS   | $T_A = 25^\circ\text{C}$ |       |     | SN54LV123A |     | SN74LV123A |     | UNIT          |
|-----------------------|--------------------------|---------------------|--|--------------------------|-------|-----|------------|-----|------------|-----|---------------|
|                       |                          |                     |  | MIN                      | TYP   | MAX | MIN        | MAX | MIN        | MAX |               |
| $t_{pd}$              | $\overline{A}$ or B      | Q or $\overline{Q}$ | $C_L = 15\text{ pF}$   | 7.1*                     | 12*   |     | 1*         | 14* | 1          | 14  | ns            |
|                       | $\overline{CLR}$         | Q or $\overline{Q}$ |  | 6.5*                     | 9.4*  |     | 1*         | 11* | 1          | 11  |               |
|                       | $\overline{CLR}$ trigger | Q or $\overline{Q}$ |  | 7.4*                     | 12.9* |     | 1*         | 15* | 1          | 15  |               |
| $t_{pd}$              | $\overline{A}$ or B      | Q or $\overline{Q}$ | $C_L = 50\text{ pF}$   | 8.3                      | 14    |     | 1          | 16  | 1          | 16  | ns            |
|                       | $\overline{CLR}$         | Q or $\overline{Q}$ |  | 7.4                      | 11.4  |     | 1          | 13  | 1          | 13  |               |
|                       | $\overline{CLR}$ trigger | Q or $\overline{Q}$ |  | 8.7                      | 14.9  |     | 1          | 17  | 1          | 17  |               |
| $t_w^\dagger$         |                          |                     | $C_L = 50\text{ pF}$ ,<br>$C_{ext} = 28\text{ pF}$ ,<br>$R_{ext} = 2\text{ k}\Omega$             | 167                      | 200   |     |            | 240 |            | 240 | ns            |
|                       |                          |                     | $C_L = 50\text{ pF}$ ,<br>$C_{ext} = 0.01\text{ }\mu\text{F}$ ,<br>$R_{ext} = 10\text{ k}\Omega$ | 90                       | 100   | 110 | 90         | 110 | 90         | 110 | $\mu\text{s}$ |
|                       |                          |                     | $C_L = 50\text{ pF}$ ,<br>$C_{ext} = 0.1\text{ }\mu\text{F}$ ,<br>$R_{ext} = 10\text{ k}\Omega$  | 0.9                      | 1     | 1.1 | 0.9        | 1.1 | 0.9        | 1.1 | ms            |
| $\Delta t_w^\ddagger$ |                          |                     |  | $\pm 1$                  |       |     |            |     |            |     | %             |

\* On products compliant to MIL-PRF-38535, this parameter is not production tested.

$^\dagger t_w$  = Duration of pulse at Q and  $\overline{Q}$  outputs

$^\ddagger \Delta t_w$  = Output pulse-duration variation (Q and  $\overline{Q}$ ) between circuits in same package

PRODUCT PREVIEW information concerns products in the formative or design phase of development. Characteristic data and other specifications are design goals. Texas Instruments reserves the right to change or discontinue these products without notice.






# SN54LV123A, SN74LV123A DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS WITH SCHMITT-TRIGGER INPUTS

SCLS3930 – APRIL 1998 – REVISED OCTOBER 2005

operating characteristics,  $T_A = 25^\circ\text{C}$

| PARAMETER                              | TEST CONDITIONS                               | $V_{CC}$ | TYP | UNIT |
|--|---|----------|-----|------|
| $C_{pd}$ Power dissipation capacitance | $C_L = 50\text{ pF}, \quad f = 10\text{ MHz}$ | 3.3 V    | 44  | pF   |
|  |   | 5 V      | 49  |      |

## PARAMETER MEASUREMENT INFORMATION



- NOTES:
- A.  $C_L$  includes probe and jig capacitance.
  - B. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1\text{ MHz}$ ,  $Z_O = 50\ \Omega$ ,  $t_r = 3\text{ ns}$ ,  $t_f = 3\text{ ns}$ .
  - C. The outputs are measured one at a time, with one input transition per measurement.

**Figure 1. Load Circuit and Voltage Waveforms**

# SN54LV123A, SN74LV123A DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS WITH SCHMITT-TRIGGER INPUTS

SCLS393O – APRIL 1998 – REVISED OCTOBER 2005

## APPLICATION INFORMATION†




Figure 2




Figure 3

† Operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied.

## APPLICATION INFORMATION†




Figure 4. Output Pulse Duration vs External Timing Capacitance




Figure 5. Variations in Output Pulse Duration vs Temperature

† Operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied.

# SN54LV123A, SN74LV123A DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS WITH SCHMITT-TRIGGER INPUTS

SCLS393O – APRIL 1998 – REVISED OCTOBER 2005

## APPLICATION INFORMATION†




Figure 6




Figure 7




Figure 8




Figure 9

† Operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied.

## APPLICATION INFORMATION

### caution in use


To prevent malfunctions due to noise, connect a high-frequency capacitor between  $V_{CC}$  and GND, and keep the wiring between the external components and  $C_{ext}$  and  $R_{ext}/C_{ext}$  terminals as short as possible.

### power-down considerations

Large values of  $C_{ext}$  can cause problems when powering down the 'LV123A devices because of the amount of energy stored in the capacitor. When a system containing this device is powered down, the capacitor can discharge from  $V_{CC}$  through the protection diodes at pin 2 or pin 14. Current through the input protection diodes must be limited to 30 mA; therefore, the turn-off time of the  $V_{CC}$  power supply must not be faster than  $t = V_{CC} \times C_{ext}/30 \text{ mA}$ . For example, if  $V_{CC} = 5 \text{ V}$  and  $C_{ext} = 15 \text{ pF}$ , the  $V_{CC}$  supply must turn off no faster than  $t = (5 \text{ V}) \times (15 \text{ pF})/30 \text{ mA} = 2.5 \text{ ns}$ . Usually, this is not a problem because power supplies are heavily filtered and cannot discharge at this rate. When a more rapid decrease of  $V_{CC}$  to zero occurs, the 'LV123A devices can sustain damage. To avoid this possibility, use external clamping diodes.

### output pulse duration

The output pulse duration,  $t_w$ , is determined primarily by the values of the external capacitance ( $C_T$ ) and timing resistance ( $R_T$ ). The timing components are connected as shown in Figure 10.



**Figure 10. Timing-Component Connections**

The pulse duration is given by:

$$t_w = K \times R_T \times C_T \quad (1)$$

if  $C_T$  is  $\geq 1000 \text{ pF}$ ,  $K = 1.0$  or  
 if  $C_T$  is  $< 1000 \text{ pF}$ ,  $K$  can be determined from Figure 8

where:

$t_w$  = pulse duration in ns  
 $R_T$  = external timing resistance in  $k\Omega$   
 $C_T$  = external capacitance in pF  
 $K$  = multiplier factor

Equation 1 and Figure 3 can be used to determine values for pulse duration, external resistance, and external capacitance.

# SN54LV123A, SN74LV123A DUAL RETRIGGERABLE MONOSTABLE MULTIVIBRATORS WITH SCHMITT-TRIGGER INPUTS

SCLS393O – APRIL 1998 – REVISED OCTOBER 2005

## APPLICATION INFORMATION

### retriggering data

The minimum input retriggering time ( $t_{MIR}$ ) is the minimum time required after the initial signal before retriggering the input. After  $t_{MIR}$ , the device retriggers the output. Experimentally, it also can be shown that to retrigger the output pulse, the two adjacent input signals should be  $t_{MIR}$  apart, where  $t_{MIR} = 0.30 \times t_w$ . The retrigger pulse duration is calculated as shown in Figure 11.




Figure 11. Retrigger Pulse Duration

The minimum value from the end of the input pulse to the beginning of the retriggered output should be approximately 15 ns to ensure a retriggered output (see Figure 12).




Figure 12. Input/Output Requirements

## PACKAGING INFORMATION

| Orderable Device | Status <sup>(1)</sup> | Package Type | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup> | Lead/Ball Finish | MSL Peak Temp <sup>(3)</sup> |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|------------------------------|
| SN74LV123AD      | ACTIVE                | SOIC         | D               | 16   | 40          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADBR    | ACTIVE                | SSOP         | DB              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADBRE4  | ACTIVE                | SSOP         | DB              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADBRG4  | ACTIVE                | SSOP         | DB              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADE4    | ACTIVE                | SOIC         | D               | 16   | 40          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADG4    | ACTIVE                | SOIC         | D               | 16   | 40          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADGVR   | ACTIVE                | TVSOP        | DGV             | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADGVRE4 | ACTIVE                | TVSOP        | DGV             | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADGVRG4 | ACTIVE                | TVSOP        | DGV             | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADR     | ACTIVE                | SOIC         | D               | 16   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADRE4   | ACTIVE                | SOIC         | D               | 16   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ADRG4   | ACTIVE                | SOIC         | D               | 16   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ANSR    | ACTIVE                | SO           | NS              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ANSRE4  | ACTIVE                | SO           | NS              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ANSRG4  | ACTIVE                | SO           | NS              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123APW     | ACTIVE                | TSSOP        | PW              | 16   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123APWE4   | ACTIVE                | TSSOP        | PW              | 16   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123APWG4   | ACTIVE                | TSSOP        | PW              | 16   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123APWR    | ACTIVE                | TSSOP        | PW              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123APWRE4  | ACTIVE                | TSSOP        | PW              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123APWRG4  | ACTIVE                | TSSOP        | PW              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123APWT    | ACTIVE                | TSSOP        | PW              | 16   | 250         | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123APWTE4  | ACTIVE                | TSSOP        | PW              | 16   | 250         | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123APWTG4  | ACTIVE                | TSSOP        | PW              | 16   | 250         | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| SN74LV123ARGYR   | ACTIVE                | VQFN         | RGY             | 16   | 3000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-2-260C-1 YEAR          |

| Orderable Device | Status <sup>(1)</sup> | Package Type | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup> | Lead/Ball Finish | MSL Peak Temp <sup>(3)</sup> |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|------------------------------|
| SN74LV123ARGYRG4 | ACTIVE                | VQFN         | RGY             | 16   | 3000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-2-260C-1 YEAR          |

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSELETE:** TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## OTHER QUALIFIED VERSIONS OF SN74LV123A :

- Automotive: [SN74LV123A-Q1](#)
- Enhanced Product: [SN74LV123A-EP](#)

NOTE: Qualified Version Definitions:

- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects
- Enhanced Product - Supports Defense, Aerospace and Medical Applications



**TAPE AND REEL INFORMATION**


\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74LV123ADBR  | SSOP         | DB              | 16   | 2000 | 330.0              | 16.4               | 8.2     | 6.6     | 2.5     | 12.0    | 16.0   | Q1            |
| SN74LV123ADGVR | TVSOP        | DGV             | 16   | 2000 | 330.0              | 12.4               | 6.8     | 4.0     | 1.6     | 8.0     | 12.0   | Q1            |
| SN74LV123ADR   | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| SN74LV123ANSR  | SO           | NS              | 16   | 2000 | 330.0              | 16.4               | 8.2     | 10.5    | 2.5     | 12.0    | 16.0   | Q1            |
| SN74LV123APWR  | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 7.0     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |
| SN74LV123ARGYR | VQFN         | RGY             | 16   | 3000 | 180.0              | 12.4               | 3.8     | 4.3     | 1.5     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74LV123ADBR  | SSOP         | DB              | 16   | 2000 | 346.0       | 346.0      | 33.0        |
| SN74LV123ADGVR | TVSOP        | DGV             | 16   | 2000 | 346.0       | 346.0      | 29.0        |
| SN74LV123ADR   | SOIC         | D               | 16   | 2500 | 333.2       | 345.9      | 28.6        |
| SN74LV123ANSR  | SO           | NS              | 16   | 2000 | 346.0       | 346.0      | 33.0        |
| SN74LV123APWR  | TSSOP        | PW              | 16   | 2000 | 346.0       | 346.0      | 29.0        |
| SN74LV123ARGYR | VQFN         | RGY             | 16   | 3000 | 190.5       | 212.7      | 31.8        |

## DB (R-PDSO-G\*\*)

## PLASTIC SMALL-OUTLINE

28 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.  
 D. Falls within JEDEC MO-150

## PW (R-PDSO-G\*\*)

## PLASTIC SMALL-OUTLINE PACKAGE

14 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.  
 D. Falls within JEDEC MO-153

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE


14-PINS SHOWN



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

D (R-PDSO-G16)

PLASTIC SMALL-OUTLINE PACKAGE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- $\triangle C$  Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 (0,15) per end.
- $\triangle D$  Body width does not include interlead flash. Interlead flash shall not exceed .017 (0,43) per side.
- E. Reference JEDEC MS-012 variation AC.


## D(R-PDSO-G16)





- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Refer to IPC7351 for alternate board design.
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.

RGY (R-PVQFN-N16)

PLASTIC QUAD FLATPACK NO-LEAD



- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
  - B. This drawing is subject to change without notice.
  - C. QFN (Quad Flatpack No-Lead) package configuration.
  -  D. The package thermal pad must be soldered to the board for thermal and mechanical performance. See the Product Data Sheet for details regarding the exposed thermal pad dimensions.
  -  E. Pin 1 identifiers are located on both top and bottom of the package and within the zone indicated. The Pin 1 identifiers are either a molded, marked, or metal feature.
  - F. Package complies to JEDEC MO-241 variation BB.




## THERMAL INFORMATION

This package incorporates an exposed thermal pad that is designed to be attached directly to an external heatsink. The thermal pad must be soldered directly to the printed circuit board (PCB). After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For information on the Quad Flatpack No-Lead (QFN) package and its advantages, refer to Application Report, QFN/SON PCB Attachment, Texas Instruments Literature No. SLUA271. This document is available at [www.ti.com](http://www.ti.com).


The exposed thermal pad dimensions for this package are shown in the following illustration.



Bottom View

NOTE: All linear dimensions are in millimeters

Exposed Thermal Pad Dimensions



## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

| Products                    |  | Applications               |  |
|-----------------------------|--|----------------------------|--|
| Amplifiers                  | <a href="http://amplifier.ti.com">amplifier.ti.com</a>             | Audio                      | <a href="http://www.ti.com/audio">www.ti.com/audio</a>                                   |
| Data Converters             | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>     | Automotive                 | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>                         |
| DLP® Products               | <a href="http://www.dlp.com">www.dlp.com</a>                       | Communications and Telecom | <a href="http://www.ti.com/communications">www.ti.com/communications</a>                 |
| DSP                         | <a href="http://dsp.ti.com">dsp.ti.com</a>                         | Computers and Peripherals  | <a href="http://www.ti.com/computers">www.ti.com/computers</a>                           |
| Clocks and Timers           | <a href="http://www.ti.com/clocks">www.ti.com/clocks</a>           | Consumer Electronics       | <a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>                   |
| Interface                   | <a href="http://interface.ti.com">interface.ti.com</a>             | Energy                     | <a href="http://www.ti.com/energy">www.ti.com/energy</a>                                 |
| Logic                       | <a href="http://logic.ti.com">logic.ti.com</a>                     | Industrial                 | <a href="http://www.ti.com/industrial">www.ti.com/industrial</a>                         |
| Power Mgmt                  | <a href="http://power.ti.com">power.ti.com</a>                     | Medical                    | <a href="http://www.ti.com/medical">www.ti.com/medical</a>                               |
| Microcontrollers            | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a> | Security                   | <a href="http://www.ti.com/security">www.ti.com/security</a>                             |
| RFID                        | <a href="http://www.ti-rfid.com">www.ti-rfid.com</a>               | Space, Avionics & Defense  | <a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a> |
| RF/IF and ZigBee® Solutions | <a href="http://www.ti.com/lprf">www.ti.com/lprf</a>               | Video and Imaging          | <a href="http://www.ti.com/video">www.ti.com/video</a>                                   |
|                             |  | Wireless                   | <a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>                   |