




LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
J	-		O	RELEASED	FJD0-0280-04	27AUG2004	Y.K	D.M
			A	REVISED		30NOV2007	H.U	O.A


-1;本図
-1;AS SHOWN



断面 C-C
スケール 20:1



断面 D-D
スケール 20:1



- 1 材料; 黄銅。
- 2 仕上げ; 全面に1.27μm以上のニッケル下地めっき。
接触部及び圧着部に0.2μm以上の金めっき。
- 3 AWG#26, AWG#28対応;
対応電線: UL1508 AWG#26
素線数/素線径: 7/0.16mm²
絶縁被覆径: φ7.8(φ8.2も対応)
- 1 MATERIAL; Brass.
- 2 FINISH; Ni UNDER PLATING 1.27μm MIN. ALL SURFACE.
CONTACT AND CRIMP AREA; Au PLATING 0.2μm MIN.
- 3 WIRE SIZE AWG#26, AWG#28;
APPLICABLE WIRES: UL1508 AWG#26
NUMBER OF CONDUCTORS/
DIAMETER OF A CONDUCTOR: 7/0.16mm²
INSULATION DIAMETER: φ7.8(φ8.2)
- APPLICABLE WIRES: UL1508 AWG#28
NUMBER OF CONDUCTORS/
DIAMETER OF A CONDUCTOR: 7/0.127mm²
INSULATION DIAMETER: φ6.8

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: 単位: 概 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.2 0-PLC ± 1-PLC ±0.5 2-PLC ±0.13 3-PLC ±0.013 4-PLC ±0.000J ANGLES ±3	DWN Y.KATO 26AUG2004
		CHK D.MITSUGI 27AUG2004
		APVD D.MITSUGI 27AUG2004
		PRODUCT SPEC 108-5865-1
MATERIAL 材料	FINISH 仕上	APPLICATION SPEC 114-5334-1
		WEIGHT -
1	2	CUSTOMER DRAWING

		WIRE RANGE 組合電線断面積		INSULATION DIA 被覆外径	
		3		3	
DWN Y. KATO 26AUG2004		Tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan			
CHK D. MITSUGI 27AUG2004					
APVD D. MITSUGI 27AUG2004		NAME 名称 POST CONTACT MINI VP 1.0mm W to B CONN. -			
PRODUCT SPEC 製品規格 108-5865-1					
APPLICATION SPEC 取付適用規格 114-5334-1		SIZE A3			
WEIGHT -					
CUSTOMER DRAWING		CAGE CODE 00779		DRAWING NO 番号 C=1747469	
		RESTRICTED TO -		SCALE 尺度 10:1	
				SHEET 1	
				OF 1	
				REV A	