




- 1
- CONTACT AREA PLATED WITH .000762 [.000030] GOLD;
SOLDER LEADS PLATED WITH .003810 [.00015] MIN TIN-LEAD;
ALL OVER .001270 [.000050] MIN NICKEL
- 2
- POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3
- THE NOTED DIMENSION APPLIES AT THE
INTERSECTION OF THE POST AND HOUSING.
- 4
- CONTACT AREA PLATED WITH .000762 [.000030] GOLD;
SOLDER LEADS PLATED WITH .003810 [.00015] MIN TIN;
ALL OVER .001270 [.000050] MIN NICKEL
- 5
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI
- 6
- FINISH: 0.00002[.000001] MIN. GOLD ON GOLD PLATED AREA,
0.00381-0.00635[.000150-.000250] MATTE TIN LEAD ON TIN PLATE
AREA, UNDER PLATING SHOULD BE 0.00127-0.00254[.000050-.000100]
NICKEL ON ENTIRE CONTACT, GOLD AND TIN PLATING MAY NOT OVERLAP.
- 7
- FINISH: 0.00002[.000001] MIN GOLD ON GOLD PLATED AREA,
0.00381-0.00635[.000150-.000250] MATTE TIN ON TIN PLATE AREA,
UNDER PLATING TO BE 0.00127-0.00254[.000050-.000100] NICKEL ON
ENTIRE CONTACT, GOLD AND TIN PLATING MAY NOT OVERLAP.
- 8
- SUPERCEDED
- 9
- PRELIMINARY-NOT FOR PRODUCTION
- 10
- OBSOLETE

8		7		6		5		4		3		2		1	
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION											
(C) COPYRIGHT -- By --				ALL RIGHTS RESERVED.											

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC ± -

1. PLC ± -

2. PLC ± -

3. PLC ± 0.13[.005]

4. PLC ± -

ANGLES ± ± -

DWN
D. CLOUSER
10-3-88

CHK
T. ZOLA
10-3-88

APVD
T. ZOLA
10-3-88

PRODUCT SPEC
108-1093

APPLICATION SPEC
114-25031

WEIGHT
-

NAME
HEADER ASSEMBLY, RIGHT ANGLE,
UNSHROUDED, SINGLE ROW,
AMPMODU System 50

SIZE
A1

CAGE CODE
00779

DRAWING NO
104186

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
5:1

SHEET
2

OF
2

REV
S