

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

E

ADDED PACKING INFORMATION

27JUN2012

Y.U

T.K

NOTES:



CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1,27 CENTERS .
FOR CABLE REQUIREMENTS SEE AMP APPLICATION SPECIFICATION 114-19022.



THESE RECEPTACLE CONNECTORS MATE WITH 0,64^{±0,05} mm SQUARE OR ROUND POSTS
ON 2,54mm GRID.



MARK INDICATING FIRST CABLE POSITION REFERRING TO CONTACT POSITION.



THERE IS NO POLARIZATION-SLOT AT THIS END IN 6, 10 AND 14 POS CONNECTORS.



THESE CONNECTORS CAN BE USED IN CONJUNCTION WITH STRAIN-RELIEF COVERS
OF PARTNR: 182762.





THERE IS NO POLARIZATION-SLOT AT THIS END IN 6 POS CONNECTORS.





PRODUCT SPECIFICATION 108-19033.



OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



CONNECTOR HEIGHT
AFTER CABLE
TERMINATION.



OBSOLETE	85,9	64	32	6-215911-4	D
	80,8	60	30	6-215911-0	D
	68,1	50	25	5-215911-0	D
	60,5	44	22	4-215911-4	D
	55,4	40	20	4-215911-0	D
	47,8	34	17	3-215911-4	D
	42,7	30	15	3-215911-0	D
	37,6	26	13	2-215911-6	D
	30,0	20	10	2-215911-0	D
	24,9	16	8	1-215911-6	D
OBSOLETE	22,4	14	7	1-215911-4	D
	17,3	10	5	1-215911-0	D
	14,8	8	4	0-215911-8	C
OBSOLETE	12,2	6	3	0-215911-6	D
OBSOLETE	9,7	4	2	0-215911-4	C
DIM."C"	"B" CABLE POS.	"A" DUAL POS.	PARTNUMBER	PART REV.	

3 RECEPTACLE CONTACT	PHOSPHORBRONZE Cu Sn6	AT CONTACT-PLACE: 0,2µmGOLD AT WIRING END: 2,5µmTIN ENTIRE UNDERCOATING: 1,27µmNICKEL
2 COVER	THERMOPLASTIC POLYESTER UL 94 -V0	GREY RAL 7032 (ONLY FOR REF.)
1 HOUSING		
COMPONENT NAME	MATERIAL	PLATING / COLOUR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.R.VERBEET 04FEB1988	 TE Connectivity		
		CHK R.VERSTIJNEN 05FEB1988			
		APVD L.V.SOEST 05FEB1988	NAME AMP-LATCH_MIL-TYPE RECEPTACLE_CONNECTOR ASSEMBLY_(SYMMETRIC_COVER)		
DIMENSIONS: mm		PRODUCT SPEC			
		APPLICATION SPEC			
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-215911
MATERIAL SEE TABLE		FINISH SEE TABLE	RESTRICTED TO		
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 2
				REV E	

4

3

2


1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.


PACKAGING SPECIFICATION




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J	—	—	—	SEE SHEET 1	—	—




TRAY A COVER



TRAY B COVER



TRAY A BOTTOM



TRAY B BOTTOM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —

MATERIAL
—

FINISH
—

DWN W.R.VERBEET.	04FEB1988	 TE Connectivity			
CHK R.VERSTIJNEN	05FEB1988				
APVD L.V.SOEST	05FEB1988	NAME AMP-LATCH_MIL-TYPE RECEPTACLE_CONNECTOR ASSEMBLY_(SYMMETRIC_COVER)			
PRODUCT SPEC —					
APPLICATION SPEC —					
WEIGHT —	—	SIZE A3	CAGE CODE 00779	DRAWING NO C-215911	RESTRICTED TO —
CUSTOMER DRAWING			SCALE —	SHEET 2 of 2	REV E